



Revision Number: 004.0

Issue date: 02/17/2017

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	LOCTITE 370 SN60 5C 0.38MM R known as 60/40 370 5C 0.38MM 0.25KG AM	IDH number:	389261
Product type:	Solder Wire	Item number:	MM01019
Restriction of Use:	None identified	Region:	United States
Company address:	Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067	Contact information:	Telephone: (860) 571-5100 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887 Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

DANGER: CAUSES SKIN AND EYE IRRITATION.
MAY CAUSE DROWSINESS OR DIZZINESS.
SUSPECTED OF CAUSING CANCER.
MAY DAMAGE FERTILITY OR THE UNBORN CHILD.
CAUSES DAMAGE TO ORGANS THROUGH PROLONGED OR REPEATED EXPOSURE.

HAZARD CLASS	HAZARD CATEGORY
SKIN IRRITATION	2
EYE IRRITATION	2B
CARCINOGENICITY	2
REPRODUCTIVE TOXICITY	1B
SPECIFIC TARGET ORGAN TOXICITY - SINGLE EXPOSURE	3
SPECIFIC TARGET ORGAN TOXICITY - REPEATED EXPOSURE	1

PICTOGRAM(S)



Precautionary Statements

Prevention: Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Do not breathe dust or fumes. Wash affected area thoroughly after handling. Do not eat, drink or smoke when using this product. Use only outdoors or in a well-ventilated area. Wear protective gloves, clothing, eye and face protection.

Response: IF ON SKIN: Wash with plenty of water. IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or physician if you feel unwell. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. IF exposed or concerned: Get medical attention. If skin irritation occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.

Storage: Store in a well-ventilated place. Keep container tightly closed. Store locked up.

Disposal: Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Tin	7440-31-5	50 - 60
Lead	7439-92-1	30 - 40

* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation: Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. If symptoms develop and persist, get medical attention.

Skin contact: Remove contaminated clothing and footwear. Immediately flush skin with plenty of water (using soap, if available). If symptoms develop and persist, get medical attention. Wash clothing before reuse.

Eye contact: Immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.

Ingestion: DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. If symptoms develop and persist, get medical attention.

Symptoms: See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media: Water spray (fog), foam, dry chemical or carbon dioxide.

Special firefighting procedures: Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. Do not use water on fires where molten metal is present.

Unusual fire or explosion hazards: In case of fire, keep containers cool with water spray.

Hazardous combustion products: Oxides of carbon. Oxides of Metals in Section 3. Formaldehyde. High temperatures may produce heavy metal dust, fumes or vapours. The flux medium will give rise to irritating fumes.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions: Do not allow product to enter sewer or waterways.

Clean-up methods: Ensure adequate ventilation. Wear suitable protective clothing, gloves and eye/face protection. Scrape up spilled material and place in a closed container for disposal.

7. HANDLING AND STORAGE

Handling: Use only in well-ventilated areas. Wear suitable protective clothing, gloves and eye/face protection. Avoid contact with eyes, skin and clothing. When using do not eat, drink or smoke. Wash thoroughly after handling.

Storage: Store in a cool, dry, well-ventilated area. Store in original container until ready to use.

For information on product shelf life, please review labels on container or check the Technical Data Sheet.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Tin	2 mg/m3 TWA	2 mg/m3 PEL (as Sn)	None	None
Lead	0.05 mg/m3 TWA (as Pb)	0.05 mg/m3 TWA 0.03 mg/m3 OSHA_ACT	None	None

Engineering controls: Use adequate ventilation to remove molten vapors or fumes.

Respiratory protection: Use an organic vapor respirator for concentrations exceeding the Occupational Exposure Limit.

Eye/face protection: Safety goggles or safety glasses with side shields.

Skin protection: Disposable rubber or plastic gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Solid
Color:	Gray
Odor:	Metallic
Odor threshold:	Not available.
pH:	Not available.
Vapor pressure:	Not available.
Boiling point/range:	Not available.
Melting point/ range:	Not available.
Specific gravity:	8.5
Vapor density:	Not available.
Flash point:	Does not flash.
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not available.
Flammability:	Not applicable
Evaporation rate:	Not available.
Solubility in water:	Insoluble
Partition coefficient (n-octanol/water):	Not available.
VOC content:	0.00 %; 0 g/l
Viscosity:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	Will not occur.
Hazardous decomposition products:	Oxides of carbon. Oxides of Metals in Section 3. Formaldehyde. Thermal decomposition can lead to release of irritating gases and vapors.
Incompatible materials:	Strong oxidizing agents. Strong acids and strong bases.
Reactivity:	Not available.
Conditions to avoid:	Solder alloy will react with concentrated nitric acid to produce toxic fumes of nitrogen oxides.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure: Skin, Inhalation, Eyes, Ingestion

Potential Health Effects/Symptoms

Inhalation:	Inhalation of processing fumes may be harmful. Fumes and/or dust produced by this product may be hazardous in case of ingestion or inhalation. Rosin thermal decomposition product (as formaldehyde) is classified by NIOSH as a potential occupational carcinogen. Vapor overexposure may cause drowsiness. Dizziness. Excessive exposure to tin fumes or dust may cause Stannosis, a chronic respiratory disease resulting in reduced lung capacity and benign tumors. Lead is a cumulative poison and continuous exposure to small amounts over time can raise the body's content to toxic levels. Excessive inhalation of fumes from many metals can produce an acute reaction known as "metal fume fever". Symptoms consist of chills and fever (very similar to and easily confused with flu symptoms) which come on a few hours after large exposures.
Skin contact:	Causes skin irritation.
Eye contact:	Causes eye irritation.
Ingestion:	Lead is a cumulative poison and continuous exposure to small amounts over time can raise the body's content to toxic levels. Symptoms of lead poisoning include abdominal pain, nausea, vomiting, and headache.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Tin	None	Gastrointestinal, Irritant, Kidney, Liver, Lung, Nervous System
Lead	None	Behavioral, Blood, Developmental, Eyes, Gastrointestinal, Kidney, Liver, Muscle, Nervous System, Reproductive, Skin, Some evidence of carcinogenicity, Thyroid

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Tin	No	No	No
Lead	Reasonably Anticipated to be a Human Carcinogen.	Group 2B	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.
Hazardous waste number: D008: Lead

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/IMDG)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification: None above reporting de minimis
CERCLA/SARA Section 302 EHS: None above reporting de minimis.
CERCLA/SARA Section 311/312: Immediate Health, Delayed Health
CERCLA/SARA Section 313: This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Lead (CAS# 7439-92-1).
CERCLA Reportable quantity: Lead (CAS# 7439-92-1) 10 lbs. (4.54 kg)
California Proposition 65: This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

Prepared by: Alicia Griffin, Regulatory Affairs Specialist
Issue date: 02/17/2017

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.