

# **Grounding & Cleaning**

If the material is used on top of an already properly grounded surface, grounding hardware may not be necessary. Where no properly grounded surface is available, grounding hardware is required to provide a path-to-ground. Rtg compliance verification measurements must be made as outlined in ESD TR53 with a surface resistance meter.

**Black** 

See Tech Bulletin TB-7000 for Reztore® Surface & Mat Cleaner Application Instructions.

### **Limited Lifetime Warranty:**

Desco warrants for one year that Statfree® matting products will be free of defects in materials and workmanship and will quarantee dissipative/ conductive mat properties for the life of the mat. Damage to matting caused by misuse of any kind, including using inappropriate cleaners is not covered by Desco Limited Warranty.

RoHS 3. REACH, and Conflict Minerals Statement See the Desco Industries RoHS 3, REACH, and Conflict Minerals Statement:

http://www.descoindustries.com/ROHS.aspx

See the Desco Limited Warranty:

http://desco.descoindustries.com/Limited-Warranty.aspx

See the Desco Disclaimer:

http://desco.descoindustries.com/Disclaimer.aspx

Specifications and procedures subject to change without notice.





# **Specifications**

Standard Document Meets Requirements of:

ANSI/ESD S20.20

Test Procedures/Method

Worksurface

**Electrical Properties Color Dissipative Layer** 

Rtt Resistance:  $1 \times 10^6 \text{ to} < 1 \times 10^9 \text{ ohms}$ ANSI/ESD S4.1 and ESD TR53 Rtg Resistance:  $1 \times 10^6$  to  $< 1 \times 10^9$  ohms ANSI/ESD S4.1 and ESD TR53

**Typical Values** 

**Physical Properties** 

Construction: Cellular foam rubber Thickness: 0.125" (3.2mm) ±10% Surface\*: Textured surface

Hardness: 45 Shore "A", per ASTM-D412 Weight: 0.28 lbs. per square foot Density: Average - 24 lbs. per cubic foot

Corner Radius:

Tensile Strength (Machine Direction) 70 PSI Tensile Strength (Cross Machine Direction) 45 PSI Tensile Strength Die "b" (Machine Direction) 20 PSI Tensile Strength Die "b" (Cross Machine Direction) 15 PSI

# **Tolerances:**

Width ± 0.250"

Length ± 0.250" every 1 linear foot of running material.

Thickness ±10%


Matting materials have a tendency to shrink slightly when first unrolled. In applications where length is critical, allow the material to condition for at least 4 hours before cutting to size. Always using care trim with a sharp knife or razor blade.

\*Color and texture may vary between lots and mills.

For product listings, Click Here



STATFREE J<sup>™</sup> DISSIPATIVE SHOCK RESISTANT FOAM RUBBER, 0.125" (3.2MM)



STATFREE J™ DRAWING PM-114 DATE: June 2017



DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407

PHONE (781) 821-8370