



Revision Number: 005.1

Issue date: 03/13/2017

**1. PRODUCT AND COMPANY IDENTIFICATION**

<b>Product name:</b>	<b>LOCTITE LB 8065 known as Loctite 8065</b>	<b>IDH number:</b>	525382
<b>Product type:</b>	Lubricant	<b>Item number:</b>	37755
<b>Restriction of Use:</b>	None identified	<b>Region:</b>	United States
<b>Company address:</b>	<b>Contact information:</b>		
Henkel Corporation	Telephone: (860) 571-5100		
One Henkel Way	MEDICAL EMERGENCY Phone: Poison Control Center		
Rocky Hill, Connecticut 06067	1-877-671-4608 (toll free) or 1-303-592-1711		
	TRANSPORT EMERGENCY Phone: CHEMTREC		
	1-800-424-9300 (toll free) or 1-703-527-3887		
	Internet: www.henkelna.com		

**2. HAZARDS IDENTIFICATION**

**EMERGENCY OVERVIEW**

**WARNING:** CAUSES SKIN IRRITATION.  
MAY CAUSE AN ALLERGIC SKIN REACTION.  
CAUSES SERIOUS EYE IRRITATION.

HAZARD CLASS	HAZARD CATEGORY
SKIN IRRITATION	2
EYE IRRITATION	2A
SKIN SENSITIZATION	1

**PICTOGRAM(S)**



**Precautionary Statements**

<b>Prevention:</b>	Avoid breathing dust or fumes. Wash affected area thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves, eye protection, and face protection.
<b>Response:</b>	IF ON SKIN: Wash with plenty of water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If skin irritation or rash occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.
<b>Storage:</b>	Not prescribed
<b>Disposal:</b>	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

**3. COMPOSITION / INFORMATION ON INGREDIENTS**

Hazardous Component(s)	CAS Number	Percentage*
Copper	7440-50-8	10 - 20
Graphite	7782-42-5	10 - 20
Distillates (petroleum), hydrotreated heavy naphthenic	64742-52-5	10 - 20
Petroleum distillates, hydrotreated, light naphthenic	64742-53-6	10 - 20
Quartz (SiO <sub>2</sub> )	14808-60-7	0.1 - 1

\* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

#### 4. FIRST AID MEASURES

<b>Inhalation:</b>	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. If symptoms develop and persist, get medical attention.
<b>Skin contact:</b>	Wash with soap and water. If symptoms develop and persist, get medical attention.
<b>Eye contact:</b>	Immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
<b>Ingestion:</b>	Do not induce vomiting. Aspiration may cause pulmonary edema and pneumonitis. Get medical attention.
<b>Symptoms:</b>	See Section 11.

#### 5. FIRE FIGHTING MEASURES

<b>Extinguishing media:</b>	Water spray (fog), foam, dry chemical or carbon dioxide.
<b>Special firefighting procedures:</b>	None
<b>Unusual fire or explosion hazards:</b>	None
<b>Hazardous combustion products:</b>	Oxides of carbon.

#### 6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

<b>Environmental precautions:</b>	Do not allow product to enter sewer or waterways.
<b>Clean-up methods:</b>	Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up. For large spills absorb onto inert absorbent material and place in sealed container for disposal. For small spills wipe up with paper towel and place in container for disposal. Scrape up as much material as possible. Clean residue with soap and water.

#### 7. HANDLING AND STORAGE

<b>Handling:</b>	Wash thoroughly after handling. Avoid contact with eyes, skin and clothing. Keep container closed.
<b>Storage:</b>	Keep in a cool, well ventilated area.

For information on product shelf life, please review labels on container or check the Technical Data Sheet.

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Copper	0.2 mg/m <sup>3</sup> TWA (as Cu) Fume. 1 mg/m <sup>3</sup> TWA (as Cu) Dust and mist.	1 mg/m <sup>3</sup> PEL (as Cu) Dust and mist. 0.1 mg/m <sup>3</sup> PEL (as Cu) Fume.	None	None
Graphite	2 mg/m <sup>3</sup> TWA Respirable fraction.	5 mg/m <sup>3</sup> PEL Respirable fraction. 15 mg/m <sup>3</sup> PEL Total dust. 15 MPPCF TWA	None	None
Distillates (petroleum), hydrotreated heavy naphthenic	5 mg/m <sup>3</sup> TWA Inhalable fraction. 5 mg/m <sup>3</sup> TWA mist 10 mg/m <sup>3</sup> STEL mist	5 mg/m <sup>3</sup> TWA mist 500 ppm (2,000 mg/m <sup>3</sup> ) PEL 5 mg/m <sup>3</sup> PEL Mist.	None	None
Petroleum distillates, hydrotreated, light naphthenic	5 mg/m <sup>3</sup> TWA Inhalable fraction.	5 mg/m <sup>3</sup> PEL Mist. 500 ppm (2,000 mg/m <sup>3</sup> ) PEL	None	None
Quartz (SiO <sub>2</sub> )	0.025 mg/m <sup>3</sup> TWA Respirable fraction.	2.4 MPPCF TWA Respirable. 0.1 mg/m <sup>3</sup> TWA Respirable. 0.05 mg/m <sup>3</sup> TWA (Respirable dust.) (Respirable dust.) 0.025 mg/m <sup>3</sup> OSHA_ACT (Respirable dust.) 0.05 mg/m <sup>3</sup> PEL Respirable dust.	None	None

**Engineering controls:**

Use only with adequate ventilation. Local exhaust ventilation is recommended when general ventilation is not sufficient to control airborne contamination below occupational exposure limits.

**Respiratory protection:**

Use NIOSH approved respirator if there is potential to exceed exposure limit(s). Observe OSHA regulations for respirator use (29 CFR 1910.134).

**Eye/face protection:**

Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists.

**Skin protection:**

Use impermeable gloves and protective clothing as necessary to prevent skin contact.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Physical state:</b>	Solid
<b>Color:</b>	Copper
<b>Odor:</b>	Mild, Petroleum
<b>Odor threshold:</b>	Not available.
<b>pH:</b>	Not applicable
<b>Vapor pressure:</b>	Not determined
<b>Boiling point/range:</b>	Not available.
<b>Melting point/ range:</b>	Not available.
<b>Specific gravity:</b>	1.18
<b>Vapor density:</b>	Not determined
<b>Flash point:</b>	Product is a solid. Burn Rate: Approx 14 mm/2 minutes
<b>Flammable/Explosive limits - lower:</b>	Not determined
<b>Flammable/Explosive limits - upper:</b>	Not determined
<b>Autoignition temperature:</b>	Not determined
<b>Flammability:</b>	Not applicable

<b>Evaporation rate:</b>	Not determined
<b>Solubility in water:</b>	Insoluble
<b>Partition coefficient (n-octanol/water):</b>	Not determined
<b>VOC content:</b>	0 %
<b>Viscosity:</b>	Not available.
<b>Decomposition temperature:</b>	Not available.

## 10. STABILITY AND REACTIVITY

<b>Stability:</b>	Stable at normal conditions.
<b>Hazardous reactions:</b>	Will not occur.
<b>Hazardous decomposition products:</b>	Oxides of carbon.
<b>Incompatible materials:</b>	Oxidizing agents.
<b>Reactivity:</b>	Not available.
<b>Conditions to avoid:</b>	None known

## 11. TOXICOLOGICAL INFORMATION

<b>Relevant routes of exposure:</b>	Skin, Inhalation, Eyes, Ingestion
-------------------------------------	-----------------------------------

### Potential Health Effects/Symptoms

**Inhalation:** Inhalation of copper fumes may result in metal fume fever. Symptoms include metallic taste, discoloration of skin or hair. This product has low volatility and is not expected to cause respiratory tract irritation during normal conditions of use. May cause respiratory tract irritation. Abrasion of cured material such as by sanding or grinding could release respirable particles of silica quartz, a cancer hazard by inhalation. Normal use of this product causes no such release.

**Skin contact:** Causes skin irritation. May cause allergic skin reaction.

**Eye contact:** Causes serious eye irritation.

**Ingestion:** May cause gastrointestinal tract irritation if swallowed. Principal hazard of ingestion is aspiration into the lungs and subsequent pneumonitis.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Copper	None	Allergen, Blood, Central nervous system, Developmental, Gastrointestinal, Immune system, Irritant, Kidney, Liver, Mutagen, Sensory, Skin
Graphite	None	Lung
Distillates (petroleum), hydrotreated heavy naphthenic	None	Irritant
Petroleum distillates, hydrotreated, light naphthenic	None	Irritant
Quartz (SiO <sub>2</sub> )	None	Immune system, Lung, Some evidence of carcinogenicity

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Copper	No	No	No
Graphite	No	No	No
Distillates (petroleum), hydrotreated heavy naphthenic	No	No	No
Petroleum distillates, hydrotreated, light naphthenic	No	No	No
Quartz (SiO <sub>2</sub> )	Known To Be Human Carcinogen.	Group 1	Yes

## 12. ECOLOGICAL INFORMATION

**Ecological information:** Not available.

## 13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

**Recommended method of disposal:** Follow all local, state, federal and provincial regulations for disposal.

**Hazardous waste number:** Not a RCRA hazardous waste.

## 14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

### U.S. Department of Transportation Ground (49 CFR)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

**International Air Transportation (ICAO/IATA)**

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

**Water Transportation (IMO/IMDG)**

**Proper shipping name:** ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Copper)  
**Hazard class or division:** 9  
**Identification number:** UN 3077  
**Packing group:** III  
**Marine pollutant:** Copper

<b>15. REGULATORY INFORMATION</b>
-----------------------------------

**United States Regulatory Information**

**TSCA 8 (b) Inventory Status:** All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.  
**TSCA 12 (b) Export Notification:** None above reporting de minimis  
**CERCLA/SARA Section 302 EHS:** None above reporting de minimis.  
**CERCLA/SARA Section 311/312:** Immediate Health  
**CERCLA/SARA Section 313:** This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Copper (CAS# 7440-50-8).  
**California Proposition 65:** This product contains a chemical known in the State of California to cause cancer.

**Canada Regulatory Information**

**CEPA DSL/NDL Status:** One or more components are not listed on, and are not exempt from listing on either the Domestic Substances List or the Non-Domestic Substances List.

<b>16. OTHER INFORMATION</b>
------------------------------

**This safety data sheet contains changes from the previous version in sections:** New Safety Data Sheet format.

**Prepared by:** Regulatory Affairs

**Issue date:** 03/13/2017

**DISCLAIMER:** The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.