



Revision Number: 006.0

Issue date: 08/01/2014

**1. PRODUCT AND COMPANY IDENTIFICATION**

<b>Product name:</b>	<b>LOCTITE AA 3526 LC known as Loctite 3526 Heat/ UV</b>	<b>IDH number:</b>	1170630
<b>Product type:</b>	Light Curing Adhesive	<b>Item number:</b>	43362
<b>Restriction of Use:</b>	None identified	<b>Region:</b>	United States
<b>Company address:</b>	Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067	<b>Contact information:</b>	Telephone: (860) 571-5100 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887 Internet: www.henkelna.com

**2. HAZARDS IDENTIFICATION**

**EMERGENCY OVERVIEW**

**DANGER:** CAUSES SKIN IRRITATION.  
MAY CAUSE AN ALLERGIC SKIN REACTION.  
CAUSES SERIOUS EYE DAMAGE.

HAZARD CLASS	HAZARD CATEGORY
SKIN IRRITATION	2
SERIOUS EYE DAMAGE	1
SKIN SENSITIZATION	1

**PICTOGRAM(S)**



**Precautionary Statements**

<b>Prevention:</b>	Avoid breathing vapors, mist, or spray. Wash thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear eye and face protection. Wear protective gloves.
<b>Response:</b>	IF ON SKIN: Wash with plenty of soap and water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to remove. Continue rinsing. Immediately call a poison control center or physician. If skin irritation or rash occurs: Get medical attention. Take off contaminated clothing.
<b>Storage:</b>	Not prescribed
<b>Disposal:</b>	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

**3. COMPOSITION / INFORMATION ON INGREDIENTS**

Hazardous Component(s)	CAS Number	Percentage*
Polyurethane Methacrylate Resin	Unknown	30 - 60
2-Hydroxyethyl methacrylate	868-77-9	10 - 30
High boiling methacrylate	Proprietary	10 - 30
Acrylate monomer	Proprietary	5 - 10
Urethane Acrylate Prepolymer	Unknown	1 - 5
Diacrylate ester	Proprietary	1 - 5
Hydroxyalkyl methacrylate	27813-02-1	1 - 5
Tert-butyl perbenzoate	614-45-9	1 - 5
Diphenyl-2,4,6-trimethylbenzoyl phosphine oxide	75980-60-8	1 - 5
Acrylic acid	79-10-7	1 - 5
Methacrylic acid	79-41-4	0.1 - 1
Ethylene glycol	107-21-1	0.1 - 1

\* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

#### 4. FIRST AID MEASURES

<b>Inhalation:</b>	Move to fresh air. If breathing is difficult, give oxygen. If not breathing, give artificial respiration. Get medical attention.
<b>Skin contact:</b>	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. Get medical attention. Wash clothing before reuse.
<b>Eye contact:</b>	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
<b>Ingestion:</b>	DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention.
<b>Symptoms:</b>	See Section 11.

#### 5. FIRE FIGHTING MEASURES

<b>Extinguishing media:</b>	Water spray (fog), foam, dry chemical or carbon dioxide.
<b>Special firefighting procedures:</b>	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.
<b>Unusual fire or explosion hazards:</b>	Uncontrolled polymerization may occur at high temperatures resulting in explosions or rupture of storage containers. In case of fire, keep containers cool with water spray.
<b>Hazardous combustion products:</b>	Oxides of carbon. Oxides of nitrogen. Irritating organic vapours. Isocyanates. Hydrogen cyanide. Amines.

#### 6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

<b>Environmental precautions:</b>	Do not allow product to enter sewer or waterways.
-----------------------------------	---

**Clean-up methods:**

Remove all sources of ignition. Evacuate and ventilate spill area; dike spill to prevent entry into water system; wear full protective equipment during clean-up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Scrape up as much material as possible. Store in a partly filled, closed container until disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

## 7. HANDLING AND STORAGE

**Handling:**

Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Do not taste or swallow. Use only with adequate ventilation. Refer to Section 8.

**Storage:**

For safe storage, store at or below 38 °C (100.4 °F)  
Keep in a cool, well ventilated area away from heat, sparks and open flame.  
Keep container tightly closed until ready for use.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Polyurethane Methacrylate Resin	None	None	None	None
2-Hydroxyethyl methacrylate	None	None	None	3 ppm Ceiling
High boiling methacrylate	None	None	None	None
Acrylate monomer	None	None	None	None
Urethane Acrylate Prepolymer	None	None	None	None
Diacrylate ester	None	None	None	None
Hydroxyalkyl methacrylate	None	None	None	1 ppm TWA 3 ppm STEL
Tert-butyl perbenzoate	None	None	None	None
Diphenyl-2,4,6-trimethylbenzoyl phosphine oxide	None	None	None	None
Acrylic acid	2 ppm TWA (SKIN)	None	None	1 ppm TWA 3 ppm STEL (SKIN)
Methacrylic acid	20 ppm TWA	None	None	None
Ethylene glycol	100 mg/m <sup>3</sup> Ceiling Aerosol.	None	None	None

**Engineering controls:**

Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.

**Respiratory protection:**

Use NIOSH approved respirator if there is potential to exceed exposure limit(s).

**Eye/face protection:**

Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.

**Skin protection:**

Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact. Neoprene gloves. Butyl rubber gloves. Natural rubber gloves.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

**Physical state:**

Liquid

**Color:**

Light, Straw

**Odor:**

Sharp, Irritating

**Odor threshold:**

Not available.

<b>pH:</b>	Not applicable
<b>Vapor pressure:</b>	< 10 mm hg (75 °F (23.9 °C))
<b>Boiling point/range:</b>	> 300 °F (> 148.9 °C)
<b>Melting point/ range:</b>	Not available.
<b>Specific gravity:</b>	1.0633
<b>Vapor density:</b>	Not available.
<b>Flash point:</b>	> 93.4 °C (> 200.12 °F) Tagliabue closed cup
<b>Flammable/Explosive limits - lower:</b>	Not available.
<b>Flammable/Explosive limits - upper:</b>	Not available.
<b>Autoignition temperature:</b>	Not available.
<b>Evaporation rate:</b>	Not available.
<b>Solubility in water:</b>	Slight
<b>Partition coefficient (n-octanol/water):</b>	Not available.
<b>VOC content:</b>	1.39 %; 14.78 g/l (process) 0.91 %; 9.68 g/l (potential) 2.30 %; 24.46 g/l (total) (ASTM D5403)
<b>Viscosity:</b>	Not available.
<b>Decomposition temperature:</b>	Not available.

## 10. STABILITY AND REACTIVITY

<b>Stability:</b>	Stable under normal conditions of storage and use.
<b>Hazardous reactions:</b>	None under normal processing. Polymerization may occur at elevated temperature or in the presence of incompatible materials.
<b>Hazardous decomposition products:</b>	Oxides of carbon. Oxides of nitrogen. Irritating organic vapours. Isocyanates. Hydrogen cyanide. Amines.
<b>Incompatible materials:</b>	Strong oxidizing agents. Reducing agents. Strong acids and strong bases. Peroxides. Free radical initiators.
<b>Reactivity:</b>	Not available.
<b>Conditions to avoid:</b>	Elevated temperatures. Heat, flames, sparks and other sources of ignition. Store away from incompatible materials.

## 11. TOXICOLOGICAL INFORMATION

<b>Relevant routes of exposure:</b>	Skin, Inhalation, Eyes, Ingestion
-------------------------------------	-----------------------------------

### Potential Health Effects/Symptoms

**Inhalation:** Inhalation of vapors or mists of the product may be irritating to the respiratory system.  
**Skin contact:** Causes skin irritation. May cause allergic skin reaction.  
**Eye contact:** Causes serious eye damage.  
**Ingestion:** May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Polyurethane Methacrylate Resin	None	Irritant, Allergen
2-Hydroxyethyl methacrylate	Oral LD50 (RAT) = 11.2 g/kg Oral LD50 (RAT) = 5,050 mg/kg	Irritant, Allergen
High boiling methacrylate	None	Irritant, Allergen
Acrylate monomer	None	Irritant, Allergen
Urethane Acrylate Prepolymer	None	Irritant, Allergen
Diacylate ester	None	Irritant, Allergen, Eyes
Hydroxyalkyl methacrylate	None	Irritant, Allergen
Tert-butyl perbenzoate	None	Central nervous system, Irritant, Mutagen
Diphenyl-2,4,6-trimethylbenzoyl phosphine oxide	None	No Records
Acrylic acid	Oral LD50 (RAT) = 33.5 mg/kg Oral LD50 (RAT) = 2.5 g/kg Oral LD50 (RAT) = 193 mg/kg Oral LD50 (RAT) = 1,250 mg/kg Inhalation LC50 (RAT, 4 h) = 1,200 mg/l	Allergen, Corrosive, Irritant, Kidney, Liver
Methacrylic acid	Oral LD50 (RABBIT) = 1,200 mg/kg Oral LD50 (RAT) = 1,060 mg/kg Oral LD50 (RAT) = 2,224 mg/kg Dermal LD50 (RABBIT) = 500 mg/kg Inhalation LC50 (RAT, 4 h) = 7.1 mg/l	Corrosive, Irritant, Allergen
Ethylene glycol	Oral LD50 (RAT) = 5.89 g/kg Dermal LD50 (RABBIT) = 9,530 mg/kg	Blood, Bone Marrow, Central nervous system, Developmental, Eyes, Irritant, Kidney, Liver, Metabolic

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Polyurethane Methacrylate Resin	No	No	No
2-Hydroxyethyl methacrylate	No	No	No
High boiling methacrylate	No	No	No
Acrylate monomer	No	No	No
Urethane Acrylate Prepolymer	No	No	No
Diacylate ester	No	No	No
Hydroxyalkyl methacrylate	No	No	No
Tert-butyl perbenzoate	No	No	No
Diphenyl-2,4,6-trimethylbenzoyl phosphine oxide	No	No	No
Acrylic acid	No	No	No
Methacrylic acid	No	No	No
Ethylene glycol	No	No	No

## 12. ECOLOGICAL INFORMATION

**Ecological information:** Not available.

## 13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

**Recommended method of disposal:** Follow all local, state, federal and provincial regulations for disposal.  
**Hazardous waste number:** Not a RCRA hazardous waste.

## 14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

### U.S. Department of Transportation Ground (49 CFR)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

### International Air Transportation (ICAO/IATA)

**Proper shipping name:** Environmentally hazardous substance, liquid, n.o.s. (Isobornyl methacrylate, Isobornyl acrylate)  
**Hazard class or division:** 9  
**Identification number:** UN 3082  
**Packing group:** III

### Water Transportation (IMO/IMDG)

**Proper shipping name:** ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Isobornyl methacrylate, Isobornyl acrylate)  
**Hazard class or division:** 9  
**Identification number:** UN 3082  
**Packing group:** III  
**Marine pollutant:** Isobornyl methacrylate, Isobornyl acrylate

## 15. REGULATORY INFORMATION

### United States Regulatory Information

**TSCA 8 (b) Inventory Status:** All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.  
**TSCA 12 (b) Export Notification:** None above reporting de minimis  
**CERCLA/SARA Section 302 EHS:** None above reporting de minimis  
**CERCLA/SARA Section 311/312:** Immediate Health, Delayed Health  
**CERCLA/SARA Section 313:** This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Acrylic acid (CAS# 79-10-7).  
**CERCLA Reportable quantity:** Tert-butyl perbenzoate (CAS# 614-45-9) 100 lbs. (45.4 kg)  
**California Proposition 65:** This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

### Canada Regulatory Information

**CEPA DSL/NDL Status:** One or more components are not listed on, and are not exempt from listing on either the Domestic Substances List or the Non-Domestic Substances List.

## 16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

**Prepared by:** Sheila Gines, Regulatory Affairs Specialist

**Issue date:** 08/01/2014

**DISCLAIMER:** The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.