



Revision Number: 004.0

Issue date: 09/05/2014

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	LOCTITE AA 3491 LC known as LOCTITE UV ADHESIVE	IDH number:	1170398
Product type:	Ultraviolet adhesive	Item number:	43350
Restriction of Use:	None identified	Region:	United States
Company address:	Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067	Contact information:	Telephone: (860) 571-5100 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887 Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

DANGER: CAUSES SEVERE SKIN BURNS AND EYE DAMAGE.
MAY CAUSE AN ALLERGIC SKIN REACTION.

HAZARD CLASS	HAZARD CATEGORY
SKIN CORROSION	1B
SERIOUS EYE DAMAGE	1
SKIN SENSITIZATION	1

PICTOGRAM(S)



Precautionary Statements

Prevention:	Do not breathe vapors, mist, or spray. Wash thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves, eye protection, and face protection.
Response:	IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. If on skin (or hair): Take off immediately all contaminated clothing. IF INHALED: Remove person to fresh air and keep comfortable for breathing. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to remove. Continue rinsing. Immediately call a poison control center or physician. If skin irritation or rash occurs: Get medical attention. Wash contaminated clothing before reuse.
Storage:	Store locked up.
Disposal:	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Acrylate monomer	Proprietary	30 - 60
Polyurethane Methacrylate Resin	Proprietary	30 - 60
2-Hydroxyethyl methacrylate	868-77-9	5 - 10
Isobornyl methacrylate	7534-94-3	5 - 10
Acrylic acid	79-10-7	1 - 5
Hydroxyalkyl methacrylate	27813-02-1	1 - 5
Substituted silane	Proprietary	1 - 5
Adhesion Promoter	Proprietary	0.1 - 1

* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If breathing is difficult, give oxygen. If not breathing, give artificial respiration. Get immediate medical attention.
Skin contact:	Immediately wash skin thoroughly with soap and water. Remove contaminated clothing and footwear. If symptoms develop and persist, get medical attention. Wash clothing before reuse.
Eye contact:	Flush with copious amounts of water, preferably, lukewarm water for at least 15 minutes, holding eyelids open all the time. Get medical attention.
Ingestion:	Do not induce vomiting. Never give anything by mouth to an unconscious person. Keep individual calm. Get medical attention.
Symptoms:	See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. Water may be unsuitable as an extinguishing media, but may be helpful in keeping adjacent containers cool.
Unusual fire or explosion hazards:	Uncontrolled polymerization may occur at high temperatures resulting in explosions or rupture of storage containers.
Hazardous combustion products:	Oxides of carbon. Oxides of nitrogen. Oxides of silicon. Isocyanates. Hydrogen cyanide. Amines. Formaldehyde. Irritating organic vapours.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Ensure adequate ventilation. Remove all sources of ignition. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Store in a partly filled, closed container until disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

7. HANDLING AND STORAGE

- Handling:** Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Do not taste or swallow. Refer to Section 8.
- Storage:** For safe storage, store at or below 38 °C (100.4 °F)
Keep in a cool, well ventilated area away from heat, sparks and open flame.
Keep container tightly closed until ready for use.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Acrylate monomer	None	None	None	None
Polyurethane Methacrylate Resin	None	None	None	None
2-Hydroxyethyl methacrylate	None	None	None	3 ppm Ceiling
Isobornyl methacrylate	None	None	None	None
Acrylic acid	2 ppm TWA (SKIN)	None	None	1 ppm TWA 3 ppm STEL (SKIN)
Hydroxyalkyl methacrylate	None	None	None	1 ppm TWA 3 ppm STEL
Substituted silane	None	None	None	None
Adhesion Promoter	20 ppm TWA	None	None	None

- Engineering controls:** Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.
- Respiratory protection:** Use NIOSH approved respirator if there is potential to exceed exposure limit(s).
- Eye/face protection:** Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.
- Skin protection:** Use impermeable gloves and protective clothing as necessary to prevent skin contact. Neoprene gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Liquid
Color:	Clear
Odor:	Sharp
Odor threshold:	Not available.
pH:	Not applicable
Vapor pressure:	< 10 mm hg (24 °C (75.2 °F))
Boiling point/range:	> 148.0 °C (> 298.4 °F) > 148.0 °C (> 298.4 °F)
Melting point/ range:	Not available.
Specific gravity:	1.02
Vapor density:	Not available.
Flash point:	> 93 °C (> 199.4 °F)
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not available.
Evaporation rate:	Not available.
Solubility in water:	Slight
Partition coefficient (n-octanol/water):	Not available.
VOC content:	1.65 %; 16.83 g/l ASTM D5403 Process volatiles 0.36 %; 3.67 g/l (potential)

Viscosity: 2.01 %; 20.50 g/l (total)
Decomposition temperature: Not available.
 Not available.

10. STABILITY AND REACTIVITY

Stability: Stable under normal conditions of storage and use.
Hazardous reactions: May occur.
Hazardous decomposition products: Oxides of carbon. Oxides of nitrogen. Oxides of silicon. Isocyanates. Hydrogen cyanide. Amines. Formaldehyde. Irritating organic vapours.
Incompatible materials: Strong oxidizing agents. Strong reducing agents. Water. Humid air.
Reactivity: Not available.
Conditions to avoid: Heat, flames, sparks and other sources of ignition. Direct sunlight. Ultraviolet radiation. Freezing conditions. Store away from incompatible materials.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure: Skin, Inhalation, Eyes

Potential Health Effects/Symptoms

Inhalation: May cause respiratory tract irritation.
Skin contact: Causes skin burns. May cause allergic skin reaction.
Eye contact: Causes serious eye damage.
Ingestion: May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Acrylate monomer	None	Irritant, Allergen
Polyurethane Methacrylate Resin	None	Irritant, Allergen
2-Hydroxyethyl methacrylate	Oral LD50 (RAT) = 11.2 g/kg Oral LD50 (RAT) = 5,050 mg/kg	Irritant, Allergen
Isobornyl methacrylate	None	Irritant, Allergen
Acrylic acid	Oral LD50 (RAT) = 33.5 mg/kg Oral LD50 (RAT) = 2.5 g/kg Oral LD50 (RAT) = 193 mg/kg Oral LD50 (RAT) = 1,250 mg/kg Inhalation LC50 (RAT, 4 h) = 1,200 mg/l	Allergen, Corrosive, Irritant, Kidney, Liver
Hydroxyalkyl methacrylate	None	Irritant, Allergen
Substituted silane	None	Allergen, Irritant
Adhesion Promoter	Oral LD50 (RABBIT) = 1,200 mg/kg Oral LD50 (RAT) = 1,060 mg/kg Oral LD50 (RAT) = 2,224 mg/kg Dermal LD50 (RABBIT) = 500 mg/kg Inhalation LC50 (RAT, 4 h) = 7.1 mg/l	Corrosive, Irritant, Allergen

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Acrylate monomer	No	No	No
Polyurethane Methacrylate Resin	No	No	No
2-Hydroxyethyl methacrylate	No	No	No
Isobornyl methacrylate	No	No	No
Acrylic acid	No	No	No
Hydroxyalkyl methacrylate	No	No	No
Substituted silane	No	No	No
Adhesion Promoter	No	No	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Dispose of according to Federal, State and local governmental regulations.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Environmentally hazardous substance, liquid, n.o.s. (Isobornyl acrylate)
Hazard class or division: 9
Identification number: UN 3082
Packing group: III

Water Transportation (IMO/IMDG)

Proper shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Isobornyl acrylate)
Hazard class or division: 9
Identification number: UN 3082
Packing group: III
Marine pollutant: Isobornyl acrylate

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.

TSCA 12 (b) Export Notification: None above reporting de minimis

CERCLA/SARA Section 302 EHS: None above reporting de minimis
CERCLA/SARA Section 311/312: Immediate Health, Delayed Health

CERCLA/SARA Section 313: This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Acrylic acid (CAS# 79-10-7).

California Proposition 65: This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDSL Status: One or more components are not listed on, and are not exempt from listing on either the Domestic Substances List or the Non-Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

Prepared by: Catherine Bimler, Regulatory Affairs Specialist

Issue date: 09/05/2014

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.