



Revision Number: 002.1

Issue date: 01/08/2015

**1. PRODUCT AND COMPANY IDENTIFICATION**

<b>Product name:</b>	<b>LOCTITE SF 768 CLEAN UP SOLVENT</b> known as <b>LOCTITE® X-NMS CLEAN UP SOLVEN</b>	<b>IDH number:</b>	235018
<b>Product type:</b>	Solvent	<b>Item number:</b>	76820
<b>Restriction of Use:</b>	None identified	<b>Region:</b>	United States
<b>Company address:</b>	Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067	<b>Contact information:</b>	Telephone: (860) 571-5100 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887 Internet: www.henkelna.com

**2. HAZARDS IDENTIFICATION**

**EMERGENCY OVERVIEW**

**WARNING:** FLAMMABLE LIQUID AND VAPOR.  
HARMFUL IF SWALLOWED.  
CAUSES SKIN IRRITATION.  
CAUSES SERIOUS EYE IRRITATION.

HAZARD CLASS	HAZARD CATEGORY
FLAMMABLE LIQUID	3
ACUTE TOXICITY ORAL	4
SKIN IRRITATION	2
EYE IRRITATION	2A

**PICTOGRAM(S)**



**Precautionary Statements**

<b>Prevention:</b>	Keep away from heat, sparks, open flames, hot surfaces - no smoking. Keep container tightly closed. No release into water. Use explosion-proof equipment. Use only non-sparking tools. Take precautionary measures against static discharge. Wash thoroughly after handling. Do not eat, drink or smoke when using this product. Wear protective gloves, eye protection, and face protection.
<b>Response:</b>	If SWALLOWED: Immediately call poison control or physician if you feel unwell. If on skin (or hair): Take off immediately all contaminated clothing. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to remove. Continue rinsing. Rinse mouth. If skin irritation occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing. In case of fire: Use foam, dry chemical or carbon dioxide to extinguish.
<b>Storage:</b>	Store in a well-ventilated place. Keep cool.
<b>Disposal:</b>	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

### 3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Nitromethane	75-52-5	60 - 100
Toluene	108-88-3	5 - 10

\* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

### 4. FIRST AID MEASURES

<b>Inhalation:</b>	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. If symptoms develop and persist, get medical attention.
<b>Skin contact:</b>	Remove contaminated clothing and footwear. Immediately flush skin with plenty of water (using soap, if available). Get medical attention. Wash clothing before reuse.
<b>Eye contact:</b>	Immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
<b>Ingestion:</b>	Do not induce vomiting. Drink 1-2 glasses of water, seek medical advice. Never give anything by mouth to an unconscious person.
<b>Symptoms:</b>	See Section 11.

### 5. FIRE FIGHTING MEASURES

<b>Extinguishing media:</b>	Carbon dioxide. Water spray mist or foam.
<b>Special firefighting procedures:</b>	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.
<b>Unusual fire or explosion hazards:</b>	Closed containers may explode when exposed to extreme heat. Vapors may form explosive mixtures with air.
<b>Hazardous combustion products:</b>	Oxides of carbon. Oxides of nitrogen.

### 6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

<b>Environmental precautions:</b>	Do not allow product to enter sewer or waterways.
<b>Clean-up methods:</b>	Remove all sources of ignition. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Store in a closed container until ready for disposal. Rinse spill area with water.

## 7. HANDLING AND STORAGE

- Handling:** Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Keep container closed.
- Storage:** Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Nitromethane	20 ppm TWA	100 ppm (250 mg/m <sup>3</sup> ) PEL	None	None
Toluene	20 ppm TWA	200 ppm TWA 300 ppm Ceiling 500 ppm MAX. CONC 10 minutes	None	None

- Engineering controls:** Ensure adequate ventilation. Local exhaust ventilation is recommended when general ventilation is not sufficient to control airborne contamination.
- Respiratory protection:** Use an organic vapor respirator for concentrations exceeding the Occupational Exposure Limit. Observe OSHA regulations for respirator use (29 CFR 1910.134).
- Eye/face protection:** Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.
- Skin protection:** Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact. Neoprene gloves.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

- Physical state:** Liquid  
**Color:** Clear  
**Odor:** Slight  
**Odor threshold:** Not available.  
**pH:** Not available.  
**Vapor pressure:** 25 mm hg (20 °C (68°F))  
**Boiling point/range:** 111 °C (231.8 °F) Approximately  
**Melting point/ range:** Not available.  
**Specific gravity:** 1.1  
**Vapor density:** 2.1 (Air = 1)  
**Flash point:** 32 °C (89.6 °F) Closed cup  
**Flammable/Explosive limits - lower:** 7.3 %  
**Flammable/Explosive limits - upper:** Not available.  
**Autoignition temperature:** Not available.  
**Evaporation rate:** 6 Approximately, (Ether = 1)  
**Solubility in water:** Slight  
**Partition coefficient (n-octanol/water):** Not available.  
**VOC content:** 100 %; 1,100 g/l EPA Method 24  
**Viscosity:** Not available.  
**Decomposition temperature:** Not available.

## 10. STABILITY AND REACTIVITY

<b>Stability:</b>	Stable under normal conditions of storage and use.
<b>Hazardous reactions:</b>	Will not occur.
<b>Hazardous decomposition products:</b>	Oxides of carbon. Oxides of nitrogen.
<b>Incompatible materials:</b>	Amines. Alkalis. Acids. Reducing agents. Metal oxides. Combustible materials.
<b>Reactivity:</b>	Not available.
<b>Conditions to avoid:</b>	Keep away from open flames, hot surfaces and sources of ignition.

## 11. TOXICOLOGICAL INFORMATION

**Relevant routes of exposure:** Skin, Inhalation, Eyes, Ingestion

### Potential Health Effects/Symptoms

<b>Inhalation:</b>	May cause respiratory tract irritation. Excessive inhalation of this material causes headache, dizziness, nausea and incoordination. This product may be harmful by inhalation.
<b>Skin contact:</b>	Causes skin irritation. Redness.
<b>Eye contact:</b>	Causes serious eye irritation. May cause corneal injury.
<b>Ingestion:</b>	Harmful if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Nitromethane	Oral LD50 (RAT) = 940 mg/kg Dermal LD50 (RABBIT) = > 2,000 mg/kg	Blood, Bone Marrow, Irritant, Kidney, Liver, Nervous System, Reproductive, Some evidence of carcinogenicity
Toluene	Oral LD50 (RAT) = 2.6 g/kg Oral LD50 (RAT) = 5,000 mg/kg Dermal LD50 (RABBIT) = 12,124 mg/kg Inhalation LC50 (RAT, 1 h) = 26700 ppm Inhalation LC50 (RAT, 2 h) = 12200 ppm Inhalation LC50 (RAT, 4 h) = 8000 ppm	Behavioral, Cardiac, Central nervous system, Developmental, Ear, Irritant

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Nitromethane	Reasonably Anticipated to be a Human Carcinogen.	Group 2B	No
Toluene	No	No	No

## 12. ECOLOGICAL INFORMATION

**Ecological information:** Not available.

## 13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

**Recommended method of disposal:** Follow all local, state, federal and provincial regulations for disposal.

**Hazardous waste number:** D001: Ignitable.

## 14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

### U.S. Department of Transportation Ground (49 CFR)

**Proper shipping name:** Nitromethane  
**Hazard class or division:** 3  
**Identification number:** UN 1261  
**Packing group:** II

### International Air Transportation (ICAO/IATA)

**Proper shipping name:** Nitromethane  
**Hazard class or division:** 3  
**Identification number:** UN 1261  
**Packing group:** II

### Water Transportation (IMO/IMDG)

**Proper shipping name:** NITROMETHANE  
**Hazard class or division:** 3  
**Identification number:** UN 1261  
**Packing group:** II

## 15. REGULATORY INFORMATION

### United States Regulatory Information

**TSCA 8 (b) Inventory Status:** All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.

**TSCA 12 (b) Export Notification:** None above reporting de minimis

**CERCLA/SARA Section 302 EHS:** None above reporting de minimis  
**CERCLA/SARA Section 311/312:** Immediate Health, Delayed Health

**CERCLA/SARA Section 313:** This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Nitromethane (CAS# 75-52-5). Toluene (CAS# 108-88-3).

**CERCLA Reportable quantity:** Nitromethane (CAS# 75-52-5) 100 lbs. (45.4 kg)  
Toluene (CAS# 108-88-3) 1,000 lbs. (454 kg)

**California Proposition 65:** This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

### Canada Regulatory Information

**CEPA DSL/NDL Status:** All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

## 16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

**Prepared by:** Catherine Bimler, Regulatory Affairs Specialist

**Issue date:** 01/08/2015

**DISCLAIMER:** The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.