

# Reztore® Surface & Mat Cleaner

## Application Instructions



Made in the  
United States of America



Figure 1. Reztore® Surface & Mat Cleaner:  
16 Ounces (500 mL) Spray Bottle  
1 Quart (1 liter) Spray Bottle  
2.5 Gallons (10 liters) Bag-in-Box

### Description

Reztore® Surface & Mat Cleaner is a non-toxic liquid cleaner used to remove dust, grease, grime, fingerprints, and solder flux from all surfaces used in a static sensitive area. Reztore® Surface & Mat Cleaner leaves no insulative residue, contains no alkali or ammonia, and is nonflammable.

### General Guidelines

Reztore® Surface & Mat Cleaner is a liquid cleaner which can be used on a variety of surfaces, especially surfaces used in a static sensitive environment. Surfaces include but are not limited to: rubber, vinyl and polyethylene table and floor mats, field service kits, laminated table tops, tote boxes, epoxy, painted surfaces, plexiglass, glass, metal, 3-ring binders, computer screens, computer keyboards, shelving, push carts, conveyor belts, etc.

**NOTE:** Cleaners with silicone leave an insulative residue on surfaces and solvents such as 2-Butoxyethanol or Ethanolamine used in cleaners can dry out the material; both can prevent conductive or dissipative mats from functioning properly.

“Periodic cleaning, following the manufacturer’s recommendations, is required to maintain proper electrical function on all work surfaces. Ensure that cleaners that are used do not leave an electrically insulative residue common with some household cleaners that contain silicone.” (ESD Handbook ESD TR20.20 section 5.3.1.14 Worksurface Maintenance)

“Only cleaning materials or processes which do not degrade the properties of the ESD protective items, shall be used.” (EN 61340-5-1 clause 5.5 EPA working practices)

### Directions

#### Smooth Surfaces:

Apply Reztore® Surface & Mat Cleaner to the entire surface to be treated using either the pump or trigger spray bottle. Use a lint-free cloth to wipe the surface until dry. For set stains, let Reztore® Surface & Mat Cleaner soak on the surface for 30 seconds before wiping clean.




Figure 2. Applying Reztore® to the mat

#### Other Surfaces - Keyboards:

Dampen a lint-free cloth or a lint-free swab with Reztore® Surface & Mat Cleaner. Wipe surface to be cleaned using either the cloth or swab. The swab will work best for tight spots like between keyboard keys. Use the cloth to wipe clean the remaining surfaces of the keyboard.




Figure 3. Cleaning a keyboard or computer screen with Reztore® Surface & Mat Cleaner

On non-ESD surfaces, we recommend using Reztore® Topical Antistat static dissipative coating. While coating is on the surface it will enhance existing ESD surfaces and will give dissipative electrical properties to insulative surfaces.

## Specifications

<b>Appearance of Solution</b>	Transparent violet
<b>pH</b>	6.0 - 8.0
<b>Odor</b>	Slight floral
<b>Solubility</b>	Water, acetone, alcohols
<b>Toxicity, Irritation, Sensitivity</b>	Non-toxic by dermal contact, or inhalation
<b>Flammability</b>	Classification according to NFPA and OSHA as "non-flammable", Flammable Category 3
<b>Ion Level (mg/L)</b>	Fluoride 0.3 Sulfate <0.5 Nitrate 1.2 Bromide <0.5 Phosphate <0.5
<b>Electrical Properties (Dry Film)</b>	$1 \times 10^7$ to $< 1 \times 10^9$ ohms (ref. ANSI/ESD S4.1)
<b>Static Decay Rate</b>	<0.01 seconds (per FTMS 101C Method 4046)

## Testing

It is recommended to test the surface after cleaning to ensure that all insulative contaminants such as dirt and grime have been removed. Reztore® Surface & Mat Cleaner will only leave behind a coating with a surface resistance of less than  $1 \times 10^9$  ohms.

## Storage

Reztore® Surface & Mat Cleaner product does not have a set life span. The chemicals are not known to degrade over time when stored at the proper temperature conditions as stated in the Safety Data Sheet. We also recommend that this product be stored in its original container and be sealed when not in use.

### RoHS 3, REACH, and Conflict Minerals Statement

See the Desco Industries RoHS 3, REACH, and Conflict Minerals Statement:

<http://www.descoindustries.com/ROHS.aspx>

### Desco Industries Limited Warranty

See the Desco Industries Limited Warranty:

<http://www.descoindustries.com/Warranty.aspx>

Reztore® Surface and Mat Cleaner is available from these Desco Industries brands:

## DESCO

for service and support in North America

16 Oz.	<a href="#">10439</a>
1 Quart	<a href="#">10435</a>
2.5 Gallons	<a href="#">10438</a>

## DESCO EUROPE

for service and support in United Kingdom and Europe

1 Litre	<a href="#">229021</a>
1 Litre 12 Packs	<a href="#">229022</a>
10 Litres	<a href="#">229023</a>

## DESCO ASIA

for service and support in Asia

0.5 Liter	<a href="#">10439</a>
1 Liter	<a href="#">10435</a>
10 Liters	<a href="#">10438</a>

## Safety Data Sheet

May be used to comply with ANSI Z400.1-2004, 29 CFR 1910.1200, Regulation (EC) No 1272/2008 (CLP Regulation) and GHS. Standards must be consulted for specific requirements.

## NFPA Designation 704

Degree of Hazard

4 = Extreme


3 = High

2 = Moderate

1 = Slight

0 = Insignificant

Special Hazard



Revision Date: 2017-06-08

HMIS RATING: Health 1, Flammability 1, Reactivity 0, Personal Protection B

## SECTION 1 — IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

### 1.1 Product identifiers

Product Name: Reztore® Surface and Mat Cleaner  
EC No.: None  
REACH Registration No.: None  
CAS No.: None

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified use: Cleaner, ESD Surface & Mat

### 1.3 Details of the supplier of the safety data sheet

Manufacturer: Desco Industries, Inc.  
One Colgate Way.  
Canton, MA 02021  
781-821-8370

Email Address: [Service@DescoIndustries.com](mailto:Service@DescoIndustries.com)

### 1.4 Emergency telephone number

Emergency Number: 781-821-8370

## SECTION 2 — HAZARDS IDENTIFICATION

### 2.1 Classification of substance or mixture

Flammable liquid	Category 2
Eye irritation	Category 2
Specific target organ toxicity (Single exposure)	Category 3

### 2.2 Label elements

Symbol: Flame, Exclamation mark.

Signal word: Danger.

Hazard statement: (H225): Highly flammable liquid and vapour.  
(H319): Causes serious eye irritation.  
(H336): May cause drowsiness or dizziness.

Precautionary statements: (P210): Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  
(P240): Ground/bond container and receiving equipment.  
(P241): Use explosion-proof electrical/ventilating/lighting equipment.  
(P242): Use only non-sparking tools.  
(P261): Avoid breathing dust/fume/gas/mist/vapours/spray.  
(P264): Wash hands thoroughly after handling.  
(P271): Use only outdoors or in a well-ventilated area.  
(P280): Wear protective gloves/protective clothing/eye protection/face protection.  
(P303+P361+P353): IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.  
(P304+P340+P312): IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER/doctor if you feel unwell.  
(P305+P351+P338): IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
(P337+P313): If eye irritation persists: Get medical advice/attention.

(P403+P235): Store in a well-ventilated place. Keep cool.  
(P233): Keep container tightly closed.  
(P405): Store locked up.  
(P501): Dispose of contents/container in compliance with all Federal, National and Local laws and regulations.

**2.3 Other hazards** N/A

---

### SECTION 3 — COMPOSITION/INFORMATION ON INGREDIENTS

**3.1 Substances** N/A

**3.2 Mixtures**

Hazardous Ingredients	CAS No.	Weight %
Isopropanol	67-63-0	5 - 25 %

---

### SECTION 4 — FIRST AID MEASURES

**4.1 Description of first aid measures**

Eye Contact	Flush with water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Skin Contact	Wash with soap and water. If skin irritation occurs: Get medical advice/attention.
Ingestion	Drink several glasses of water. DO NOT induce vomiting. Contact a physician.
Inhalation	Move subject to fresh air.

**4.2 Most important symptoms and effects, both acute and delayed**

N/A

**4.3 Indication of any immediate medical attention and special treatment needed**

N/A

---

### SECTION 5 — FIRE FIGHTING MEASURES

**5.1 Extinguishing media**

Suitable Extinguishing Media	Water
Unsuitable Extinguishing Methods	N/A

**5.2 Special hazards arising from the substance or mixture**

N/A

**5.3 Advice for firefighters**

In the event of fire wear self-contained breathing apparatus.  
Cool containers with water.

---

### SECTION 6 — ACCIDENTAL RELEASE MEASURES

**6.1 Personal precautions, protective equipment and emergency procedures**

Wearing protective clothing. Inhalation protection. Extinguish all ignition sources.

**6.2 Environmental precautions**

Biodegradable.

**6.3 Methods and materials for containment and cleaning up**

Contain and collect material into plastic container. Water rinse and drain, flush small amounts. Use sanitary landfill disposal. Follow national and local regulations (RCRA; Subtitle D).  
If Material is Released/Spilled: Keep spectators away. Contain spill with inert material (e.g. sand, earth). Keep spills and cleaning runoffs out of municipal sewers and open bodies of water.

**6.4 Reference to other sections**

See SECTION 13, Disposal Considerations, for information regarding the disposal of contained spills.

## SECTION 7 — HANDLING AND STORAGE

### 7.1 Precautions for safe handling

Use in well-ventilated areas; avoid breathing vapors. Keep containers closed when not in use. Avoid from freezing.

### 7.2 Conditions for safe storage, including any incompatibilities

Store in a cool, dry place with adequate ventilation. Keep from freezing - product may coagulate.

Storage temperature: Max. 49°C/120°F 1°C/34°F

### 7.3 Specific end uses

N/A

## SECTION 8 — EXPOSURE CONTROL / PERSONAL PROTECTION

### 8.1 Control parameters

TLV-value 400 ppm maximum for Isopropanol.

Hazardous Ingredients	CAS No.	TLV-value
Isopropanol*	67-63-0	400 ppm

### 8.2 Exposure controls

Technical Control Measures Preferences of technical measure to prevent or control contact with the product. Isolating process and personnel, mechanical ventilation (dilution and local exhaust) and the regulation of process conditions. In case of non-prevention or non-control, a proper protective wearing should be used.

Hygiene Measures Wash hands before eating, smoking, or using washroom facilities

#### Individual protection measures

Eye/Face Protection Safety glasses or Chemical splash goggles as defined in ANSI Z-87.1 or a similar standard.

Skin Protection No precautions other than clean body covering clothing should be needed.

Hand Protection Impervious/Neoprene Gloves.

Respiratory Protection Wear MSHA/NIOSH approved respirator where exposure limits are exceeded.

Ingestion Use good personal hygiene. Do not consume or store food in the work area. Wash hands before smoking or eating.

## SECTION 9 — PHYSICAL AND CHEMICAL PROPERTIES

### 9.1 Information on basic physical and chemical properties

Appearance:	Liquid.
Color:	Clear violet.
Odor:	Floral Alcohol.
Odor Threshold:	N/A.
pH:	6.0 - 8.0
Melting Point:	N/A.
Boiling Point:	>200°F (93.3°C)
Flash Point:	106°F (41°C)
Evaporation rate:	0.28
Flammability:	Classification according to NFPA and OSHA as "non-flammable". Flammable Category 3 according to EU and GHS.
Upper flammability or explosive limits:	N/A
Lower flammability or explosive limits:	N/A
Vapor Pressure (mm Hg):	18.0
Vapor Density (air=1):	1.06
Relative Density:	8.17 lbs./gal at 20°C
Specific Gravity (H <sub>2</sub> O = 1) :	0.98
Solubility:	Completely
Partition coefficient:	N/A
Auto-ignition temperature:	N/A
Decomposition temperature:	N/A
Viscosity:	N/A

Explosive properties: N/A  
Oxidizing properties: N/A

## 9.2 Other information

VOC per Method 24 of EPA: 1% VOC by wt.

---

## SECTION 10 — STABILITY AND REACTIVITY

10.1 Reactivity N/A

### 10.2 Chemical stability

Stable product at normal conditions.

10.3 Possibility of hazardous reactions N/A

### 10.4 Conditions to avoid

Temperatures above 100°F (38°C) and below 34°F (1°C)

### 10.5 Incompatible materials

Strong Oxidizers.

### 10.6 Hazardous decomposition products

Thermal decomposition may yield carbon monoxide.

---

## SECTION 11 — TOXICOLOGICAL INFORMATION

### 11.1 Information on toxicological effects

All information refers to the main component Isopropanol

Acute toxicity: None known.

Special Effects: None known.

---

## SECTION 12 — ECOLOGICAL INFORMATION

12.1 Toxicity N/A

12.2 Persistence and degradability N/A

### 12.3 Bioaccumulative potential

Not likely.

### 12.4 Mobility in soil

The product is aqueous and will be separated in aqueous conditions.

12.5 Results of PBT and vPvB assessment N/A

12.6 Other adverse effects N/A

### 12.7 Additional Information

No environmental hazards have been reported or known.

---

## SECTION 13 — DISPOSAL CONSIDERATIONS

### 13.1 Waste treatment methods

Product: Contain and collect material into plastic container. Water rinse and drain, flush small amounts. Use sanitary landfill disposal. Follow state and local regulations (RCRA; Subtitle D).

13.2 Additional information N/A



## SECTION 14 — TRANSPORT INFORMATION

This product is not classified for transport under ADR/IMDG regulations.

This product is not classified as a flammable liquid according to DOT and IATA transportation standards and is not regulated as such.

14.1 UN Number	N/A
14.2 UN proper shipping name	N/A
14.3 Transport hazard class(es)	N/A
14.4 Packing group	N/A
14.5 Environmental hazards	N/A
14.6 Special precautions for user	N/A
14.7 Transport in bulk according to Annex II of MARPOL and the IBC Code	N/A

## SECTION 15 — REGULATORY INFORMATION

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Physical/Chemical Indication                      Non-flammable (NFPA and OSHA), Flammable (EU and GHS)

**\*These items are listed and subjected to the reporting requirements of the SARA Title III Section 313 Inventory of the Emergency Planning and Community Right-To-Know Act of 1986 and of 40 CFR37.**

CAS Number: 67-63-0 with maximum weight 25%

EINECS Status    All components are included in the EINECS Inventories.

TSCA    All ingredients of this product are listed or are excluded from the listing on the U.S. Toxic substance.

REACH    This product does not required REACH registration.

15.2 Chemical Safety Assessment                      N/A

## SECTION 16 — OTHER INFORMATION

HMIS RATING    Health 1, Flammability 1, Reactivity 0, Personal Protection B

NFPA RATING    Special Hazard: N/A, Health: 1, Flammability: 1, Instability: 0

SDS Updated    2017-06-08

### Disclaimer

OTHER INFORMATION: This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any other process. Such information is to the best of the company's knowledge and believed accurate and reliable as of the date indicated. However, no representation, warranty or guarantee of any kind, express or implied, is made as to its accuracy, reliability or completeness and we assume no responsibility for any loss, damage or expense, direct or consequential, arising out of use. It is the user's responsibility to satisfy himself as to the suitability and completeness of such information for his own particular use.