# **Detailed Specifications & Technical Data**

#### **ENGLISH MEASUREMENT VERSION**



### 5302FE Multi-Conductor - Commercial Applications



For more Information please call

1-800-Belden1



#### **General Description:**

Security & Commercial Audio Cable, Riser-CMR, 4-18 AWG stranded bare copper conductors with polyolefin insulation. Beldfoil® shield and PVC jacket with ripcord

polyolelin insulation, belalolis shield and PVC	jacket with hpcord
Physical Characteristics (Overall) Conductor AWG:	
# ConductorsAWGStrandingConductor Material4187x26BC - Bare Copper	
Total Number of Conductors:	4
Insulation	
Insulation Material: Insulation Material Wall Thickness (in.) PP - Polypropylene   0.008	
Outer Shield	
Outer Shield Material: Outer Shield Trade Name Type Outer Shield Material	Coverage (%)
Beldfoil®   Tape   Aluminum Foil-Polyester Tape w/Sh	
Outer Shield Drain Wire AWG:	
AWG Stranding Drain Wire Conductor Material	
24 (7x32) TC - Tinned Copper	
Outer Jacket Outer Jacket Material:	
Outer Jacket Material Nom. Wall Thickness (in.)	
PVC - Polyvinyl Chloride 0.017	
Outer Jacket Ripcord:	Yes
Overall Cable	
Overall Cabling Lay Length & Direction:  Length (in.) Direction Twists (twist/ft)  3.000   Left Hand   4.000	
Overall Cabling Color Code Chart:	
Color Black	
Red	
White	
Green	
Overall Nominal Diameter:	0.188 in.
Mechanical Characteristics (Overall)	
Operating Temperature Range:	-20°C To +75°C
UL Temperature Rating:	75°C
Bulk Cable Weight:	30 lbs/1000 ft.
Max. Recommended Pulling Tension:	103.600 lbs.
Min. Bend Radius/Minor Axis:	1.800 in.
Applicable Specifications and Agency Compliance (Ov	rerall)
Applicable Standards & Environmental Programs	OND
NEC/(UL) Specification:	CMR
NEC Articles:	800
CEC/C(UL) Specification:	CMG

Page 1 of 2 01-05-2017

## **Detailed Specifications & Technical Data**

#### **ENGLISH MEASUREMENT VERSION**



#### 5302FE Multi-Conductor - Commercial Applications

Yes
Yes
Yes
Yes
04/01/2005
Yes
Yes
Yes
Yes
UL1666 Vertical Shaft
FT4
Yes
6302FE

#### **Electrical Characteristics (Overall)**

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft) 48.500

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

Max. Operating Voltage - UL:

Voltage 300 V RMS

Max. Recommended Current:

Description	Current
10C Temperature Rise	4 Amps per conductor @ 25°C ambient

#### **Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
5302FE 008U1000	1,000 FT	32.000 LB	GRAY		4 #18 PP FS FRPVC
5302FE 008U500	500 FT	18.000 LB	GRAY		4 #18 PP FS FRPVC
5302FE 0081000	1,000 FT	33.000 LB	GRAY	С	4 #18 PP FS FRPVC
5302FE 008500	500 FT	19.500 LB	GRAY		4 #18 PP FS FRPVC

#### Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 01-20-2015

© 2017 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its bublication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

Page 2 of 2