

For more Information  
please call

1-800-Belden1



## General Description:

Surveillance & CCTV Cable, RG6, Rated-CMG, 18 AWG solid bare copper, foamed polyolefin core, 95% bare copper braid, PVC jacket

## Usage (Overall)

Suitable Applications: Analog Video/CCTV

## Physical Characteristics (Overall)

### Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	18	Solid	BC - Bare Copper	.040

### Insulation

Insulation Material:

Insulation Material	Dia. (in.)
Gas-injected FPE - Foam Polyethylene	.180

### Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	95.000

### Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

### Overall Cable

Overall Nominal Diameter: 0.266 in.

## Mechanical Characteristics (Overall)

UL Temperature Rating:	75°C
Bulk Cable Weight:	36 lbs/1000 ft.
Max. Recommended Pulling Tension:	69 lbs.
Min. Bend Radius/Minor Axis:	2.750 in.

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
NEC Articles:	800
CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
PMSHA Specification:	P-07-KA110035-MSHA

## 533945 Coax - Surveillance and CCTV Applications

RG Type: 6/U

Series Type: Series 6

### Flame Test

UL Flame Test: UL1685 FT4 Loading

C(UL) Flame Test: FT4

### Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes - Black only.

Suitability - Aerial: Yes - Black only.

### Plenum/Non-Plenum

Plenum (Y/N): No

## Electrical Characteristics (Overall)

### Nom. Characteristic Impedance:

Impedance (Ohm)

75

### Nom. Inductance:

Inductance (µH/ft)

.097

### Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

16.3

### Nominal Velocity of Propagation:

VP (%)

83

### Nominal Delay:

Delay (ns/ft)

1.21

### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

6.4

### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

2.700

### Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	.24
10	.72
50	1.5
100	2.0
200	2.9
400	4.2
700	5.6
900	6.4
1000	7.0

### Max. Operating Voltage - UL:

Voltage

300 V RMS

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
533945 009U1000	1,000 FT	39.000 LB	WHITE		RG-6/U COAX
533945 0091000	1,000 FT	41.000 LB	WHITE	C	RG-6/U COAX
533945 010U1000	1,000 FT	39.000 LB	BLACK		RG-6/U COAX
533945 0101000	1,000 FT	41.000 LB	BLACK	C	RG-6/U COAX
533945 010500	500 FT	21.000 LB	BLACK	C	RG-6/U COAX

### Notes:

C = CRATE REEL PUT-UP.

## 533945 Coax - Surveillance and CCTV Applications

Revision Number: 5    Revision Date: 03-11-2013

© 2017 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).