

8405 Multi-Conductor - Microphone/Musical Instrument Cable



For more Information
please call

1-800-Belden1



General Description:

Mic, 20 AWG stranded (19x32) high-conductivity TC conductors, cabled, polyethylene insulation, rayon braid, TC braid shield (85% coverage), PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material	Dia. (in.)
5	20	19x32	High Conductivity TC - Tinned Copper	.037

Total Number of Conductors: 5

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)	Dia. (in.)
PE - Polyethylene	.016	.069

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	85.000

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.035

Overall Cable

Overall Cabling Fillers: Jute

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Clear
3	Green
4	Red
5	Blue

Overall Cabling Separator Material: Rayon Braid

Overall Cabling Separator Thickness: 0.005 in.

Overall Nominal Diameter: 0.281 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +60°C

UL Temperature Rating: 60°C (UL AWM Style 2094)

Bulk Cable Weight: 59 lbs/1000 ft.

Max. Recommended Pulling Tension: 139 lbs.

Min. Bend Radius/Minor Axis: 2.800 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

AWM Specification: UL Style 2094 (300 V 60°C)

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

8405 Multi-Conductor - Microphone/Musical Instrument Cable

EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MIL Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading, VW-1
----------------	-------------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

23

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)

40

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

10.2

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

3.47

Max. Operating Voltage - UL:

Voltage

300 V RMS (UL AWM Style 2094)

Max. Recommended Current:

Current

3.2 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8405 0601000	1,000 FT	63.000 LB	CHROME	C	5 #20 PE SHLD PVC
8405 060250	250 FT	16.500 LB	CHROME	C	5 #20 PE SHLD PVC
8405 060500	500 FT	31.000 LB	CHROME		5 #20 PE SHLD PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 08-15-2012

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).