



**marathon**<sup>™</sup>  
Special Products

Product Data Sheet

**132X122**

*Replace "x" with 1, 2, or 3 for number of poles*

Power Terminal Block

## 200 Amps 600 Volts AC/DC

### Wire Range

- Line: 1/4 - 20 X 9/16 Stud
- Load: 1/4 - 20 X 9/16 Stud

### Electrical Ratings

- 200 Amps
- 600V per UL 1059 & CSA 22.2 No.158, class B & C application
- SCCR of 10,000 A (default for terminal blocks).
- Factory & Field Wiring with UL Listed crimp terminals

### Agency Compliance

- UR - UL Recognized Terminal Block, Evaluated to UL 1059, File No.XCFR2.E62806
- CSA - certified to C22.2 No. 158, File No. LR19766


### Material Information

- Insulator base:
  - Thermoplastic
  - Flammability rating of insulator base UL94V0
  - Insulator base temperature rating: -40°C to 125°C (UL RTI)
- Bus bar: copper, tin plated
- Threaded studs: steel, zinc plated
- Nuts: steel, zinc plated with captive washer
- Connector mounting screws: steel, zinc plated
- RoHS compliant

A Regal Brand

**REGAL**

## Termination Specifications

Line & Load Side	Termination Type	Torque	Stud Length	Maximum Lug/Bar Width
	Listed lugs on 1/4 - 20 stud	6.9 N·m (61 lbf·in)	9/16" (14mm)	.63" (16mm)

- For use with conductors prepared with listed connectors such as single hole compression/crimp lugs or listed ring, fork or spade terminals.
- Conductor size, ampacity, temperature rating and type are dictated by the ratings of the listed lugs utilized and applicable code requirements.

## Installation & Accessories

- Mounting (Panel or Din):
  - For use with #10 fastener.
  - Torque mounting fastener to 25-30 lbf·in (2.8 - 3.4 N·m).
  - 7.5 X 35 mm din rail mountable
- Covers:
  - Snap on, hinge covers available upon request
  - Catalog Number: CH132x (replace "x" with number of poles)
  - Covers are black thermoplastic
  - Accessory covers are not intended to provide insulation for electrical spacings.
- Insulator base adders and 1 pole product can be snapped together through integral dovetails to create variable pole power blocks
- Marker Strip: white vinyl strip with mounting screws available.
- Printing options available, consult customer service for specifications
- End bracket for din rail mounting: MSK35

**Drawing**

