


9554 Multi-Conductor - 300V Power-Limited Tray Cable



For more Information
please call

1-800-Belden1

**General Description:**

18 AWG pairs stranded (19x30) tinned copper conductors, twisted pairs, PVC insulation, overall Beldfoil® shield (100% coverage), PVC jacket.

Physical Characteristics (Overall)**Conductor**

AWG:

# Conductors	# Pairs	AWG	Stranding	Conductor Material
8	4	18	19x30	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.017

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
18	7x26	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.053

Outer Jacket Ripcord: Yes

Overall Cable

Overall Cabling Lay Length & Direction:

Direction
Left-hand Lay

Overall Nominal Diameter: 0.451 in.

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red and Numbered 1
2	Black & Red and Numbered 2
3	Black & Red and Numbered 3
4	Black & Red and Numbered 4

Mechanical Characteristics (Overall)

Operating Temperature Range:	-30°C To +105°C
UL Temperature Rating:	105°C
Bulk Cable Weight:	100 lbs/1000 ft.
Max. Recommended Pulling Tension:	104 lbs.
Min. Bend Radius/Minor Axis:	4.500 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMG, ITC-ER, PLTC-ER
CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2464 (300 V 80°C)

9554 Multi-Conductor - 300V Power-Limited Tray Cable

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MIL Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1685 Vertical Tray Flame Test

CSA Flame Test: FT4

IEEE Flame Test: 1202

Suitability

Suitability - Indoor: Yes

Suitability - Outdoor: Yes

Suitability - Burial: Yes

Sunlight Resistance: Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Surface Printing (Overall)

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/ft)
.17

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
54

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
35

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
5.860

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
5.860

Max. Operating Voltage - UL:

Voltage
300 V RMS (PLTC, CMG)
150 V RMS (ITC)

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9554 0601000	1,000 FT	112.000 LB	CHROME	C	4 PR #18 PVC SHLD PVC
9554 060500	500 FT	57.000 LB	CHROME	C	4 PR #18 PVC SHLD PVC
9554 0605000	5,000 FT	585.000 LB	CHROME	C	4 PR #18 PVC SHLD PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 05-17-2015

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

9554 Multi-Conductor - 300V Power-Limited Tray Cable

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).