

83900 Multi-Conductor - High-Temperature Thermocouple Wire

For more Information
please call

1-800-Belden1



General Description:

20 AWG solid conductors, FEP insulation, unshielded, FEP jacket.

Physical Characteristics (Overall)

Conductor

AWG:

| # Conductors | AWG | Stranding | Conductor Material |
|--------------|-----|-----------|--------------------|
| 1 | 20 | Solid | Iron |
| 1 | 20 | Solid | Constantan |

Total Number of Conductors: 2

Insulation

Insulation Material:

| Insulation Material | Wall Thickness (in.) |
|--------------------------------------|----------------------|
| FEP - Fluorinated Ethylene Propylene | .010 |

Outer Shield

Outer Shield Material:

| Outer Shield Material |
|-----------------------|
| Unshielded |

Outer Jacket

Outer Jacket Material:

| Outer Jacket Material |
|--------------------------------------|
| FEP - Fluorinated Ethylene Propylene |

Overall Cable

Overall Nominal Diameter: 0.076 x 0.128 in.

Mechanical Characteristics (Overall)

| | |
|------------------------------|-----------------|
| Operating Temperature Range: | -70°C To +200°C |
| Non-UL Temperature Rating: | 200°C |
| Bulk Cable Weight: | 13 lbs/1000 ft. |
| Min. Bend Radius/Minor Axis: | 1.250 in. |

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

| | |
|---------------------------------------|---------------------|
| NEC/(UL) Specification: | PLTC, CL3P |
| EU Directive 2011/65/EU (ROHS II): | Yes |
| EU CE Mark: | Yes |
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2002/95/EC (RoHS): | Yes |
| EU RoHS Compliance Date (mm/dd/yyyy): | 04/01/2005 |
| EU Directive 2002/96/EC (WEEE): | Yes |
| EU Directive 2003/11/EC (BFR): | Yes |
| CA Prop 65 (CJ for Wire & Cable): | Yes |
| MII Order #39 (China RoHS): | Yes |
| ANSI Specification: | MC 96.1-1982 Type J |

Flame Test

UL Flame Test: UL910 Steiner Tunnel

Plenum/Non-Plenum

Plenum (Y/N): Yes

83900 Multi-Conductor - High-Temperature Thermocouple Wire

Surface Printing (Overall)

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

| Description | DCR @ 20°C (Ohm/1000 ft) |
|-------------|--------------------------|
| IRON | 62 |
| CONSTANTAN | 308 |

Put Ups and Colors:

| Item # | Putup | Ship Weight | Color | Notes | Item Desc |
|---------------|----------|-------------|-------|-------|--------------------------|
| 83900 001100 | 100 FT | 2.000 LB | BROWN | | 2#20 TYPE J THERMOCOUPLE |
| 83900 0011000 | 1,000 FT | 14.000 LB | BROWN | C | 2#20 TYPE J THERMOCOUPLE |
| 83900 001500 | 500 FT | 7.000 LB | BROWN | | 2#20 TYPE J THERMOCOUPLE |

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 06-29-2011

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).