Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



83754 Multi-Conductor - Power-Limited Fire Protective, Control & Instru Cable





For more Information please call

1-800-Belden1



General Description:

14 AWG stranded (7x22) TC conductors, conductors cabled, plenum, FEP insulation, Beldfoil® (100% coverage) + TC braid shield (85% coverage), FEP jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
4	14	7x22	TC - Tinned Copper

Total Number of Conductors:

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (in.)
Teflon®	FEP - Fluorinated Ethylene Propylene	.016

Outer Shield

Outer Shield Material:

Layer #	ayer # Outer Shield Trade Name		Outer Shield Material	Coverage (%)
1	Beldfoil®	Таре	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	85

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material	Nom. Wall Thickness (in.)	
Teflon®	FEP - Fluorinated Ethylene Propylene	.015	

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White
3	Red
4	Green

Overall Nominal Diameter:

0.311 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-70°C To +200°C
UL Temperature Rating:	200°C
Bulk Cable Weight:	98 lbs/1000 ft.
Max. Recommended Pulling Tension:	270 lbs.
Min. Bend Radius/Minor Axis:	3.250 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP, FPLP
NEC Articles:	760
CEC/C(UL) Specification:	CMP
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005

Page 1 of 2 01-05-2017

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



83754 Multi-Conductor - Power-Limited Fire Protective, Control & Instru Cable

	EU Directive 2002/96/EC (WEEE):	Yes
	EU Directive 2003/11/EC (BFR):	Yes
	CA Prop 65 (CJ for Wire & Cable):	Yes
	MII Order #39 (China RoHS):	Yes
Flame Test		
	UL Flame Test:	NFPA 262
	CSA Flame Test:	FT6
Ple	num/Non-Plenum	
	Plenum (Y/N):	Yes

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

Nom. Capacitance Cond. to Other Conductor & Shield:

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

Max. Operating Voltage - UL:

300 V RMS

Max. Recommended Current:

Current 14.4 Amps per conductor @ 25°C

Notes (Overall)

Notes: Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
83754 0021000	1,000 FT	102.000 LB	RED	С	4#14 FEP SH FEP
83754 002500	500 FT	52.500 LB	RED	С	4#14 FEP SH FEP

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 09-07-2012

© 2017 Belden, Inc

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sales belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

Page 2 of 2