

ZCKE619  
limit switch head ZCKE - metal end plunger with  
protective boot



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJ41H7 ZCKJ11H7 ZCKJ9 ZCKJ4 ZCKJ5H7 ZCKJ1H7 ZCKJ11 ZCKJ2H29 ZCKJD35 ZCKJ6 ZCKJ2 ZCKJ21H7 ZCKJD35H7 ZCKJ1 ZCKJD31 ZCKJD31H29 ZCKJ8 ZCKJD37 ZCKJD39H29 ZCKJD35H29 ZCKJD39H7 ZCKJ4H7 ZCKJ1H29 ZCKJ7H7 ZCKJD31H7 ZCKJ21H29 ZCKJ7H29 ZCKJ41 ZCKJ41H29 ZCKJ9H29 ZCKJ8H29

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKJ4H29  
 ZCKJ21  
 ZCKJ5  
 ZCKJD37H7  
 ZCKJ7  
 ZCKJ6H7  
 ZCKJD37H29  
 ZCKJ6H29  
 ZCKJ8H7  
 ZCKJ5H29  
 ZCKJ9H7  
 ZCKJD39  
 ZCKJ11H29  
 ZCKJ2H7

Movement of operating head	Linear
Type of operator	End plunger spring return metal (with protective boot)
Type of approach	Vertical approach 1 direction


### Complementary

Switch actuation	On end
Positive opening	With
Head material	Metal

### Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1440 - Schneider Electric declaration of conformity  <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------