



Main

Range of product	Harmony XB5R
Product or component type	Wireless and batteryless range
Device short name	ZBRA
Product destination	Wireless access point
Colour of base of enclosure	Black RAL 9011

Complementary

Communication port protocol	Zigbee green power at 2.4 GHz conforming to IEEE 802.15.4
Kit composition	Antenna with cable 2 m
Input impedance	50 Ohm
Connector type	MCX female
Antenna gain	> 3 dBi 83...100 Hz
Maximum sensing distance	100 m access point in free field
Product weight	0.04 kg

Environment


Relative humidity	90 % at -20...55 °C without condensation conforming to ETSI EN 300 440-1
Class of protection against electric shock	Class II conforming to IEC 61140

Offer Sustainability

Sustainable offer status	Not Green Premium product
--------------------------	---------------------------

Clearances

Maximum Distance between Transmitter and the Access Point in a Metal Enclosure with an External Antenna



- (1) Transmitter
- (2) External Antenna
- (3) Access Point in a Metal enclosure

The range is reduced if the transmitter is placed in a metal enclosure (reduction factor : approx 10%)

Glass window	10...20 %
Plaster wall	30...45 %
Brick wall	60 %
Concrete wall	70...80 %
Metal structure	50...100 %