

SUM1500RMXL2U

APC Smart-UPS XL Modular 1500VA 120V Rackmount/Tower



Overview

Model Name	APC Smart-UPS XL Modular 1500VA 120V Rackmount/Tower
Includes	CD with software , Installation guide , Rack Mounting brackets , Rack Mounting support rails , Smart UPS signalling RS-232 cable , USB cable , User Manual , Web/SNMP Management Card
Standard Lead Time	Usually Ships within 4 Weeks
Product Distribution	Anguilla , Antigua And Barbuda , Argentina , Aruba , Bahamas , Barbados , Belize , Bermuda , Bolivia , Canada , Cayman Islands , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , El Salvador , Falkland Islands (Malvinas) , Grenada , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Paraguay , Peru , Puerto Rico , SAINT KITTS AND NEVIS , SAINT LUCIA , SAINT VINCENT AND THE GRENADINES , Trinidad And Tobago , United States , Uruguay , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Output Power Capacity	1425 Watts / 1440 VA
Max Configurable Power (Watts)	1425 Watts / 1440 VA
Nominal Output Voltage	120V
Nominal Output Voltage	Line Interactive
Output Connections	(8) NEMA 5-15R (Battery Backup)
Bypass	Internal Bypass (Automatic and Manual)

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA 5-15P
Cord Length	3.05 meters
Input voltage range for main operations	82 - 147 V
Input voltage adjustable range for mains operation	75 - 154V
Maximum Input Current	0 A
Input Breaker Capacity	0 A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Batteries & Runtime

Battery Type	VRLA
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 hour(s)
Replacement Battery	RBC43
RBC Quantity	1

Communications & Management

Interface Port(s)	DB-9 RS-232 , RJ-45 10/100 Base-T , USB
Available SmartSlot™ Interface Quantity	0
Pre-Installed SmartSlot™ Cards	AP9631
Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : Overload and Bypass Indicators
Audible Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency Power Off (EPO)	Optional

Surge Protection and Filtering

Surge energy rating	540 joules
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Physical

Maximum Height	86.0 mm
Maximum Width	432.0 mm
Maximum Depth	678.0 mm
Rack Height	2 U
Net Weight	46.82 kg
Shipping Weight	56.82 kg
Shipping Height	250.0 mm
Shipping Width	596.0 mm
Shipping Depth	980.0 mm
Master Carton Units	0.0
Master Carton Weight	0.0 lbs
Color	Black
Units per Pallet	8.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-5 - 55 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-9000 meters
Audible noise at 1 meter from surface of unit	55.000 dB
Online Thermal Dissipation	300.000 BTU/hr

Conformance

Approvals	BSMI , CSA , FCC Part 15 Class A , NOM , UL 1778 , VCCI
-----------	---------------------------------------------------------

Standard warranty	2 years repair or replace
Equipment protection policy	Lifetime : \$150000

Sustainable Offer Status

RoHS	Compliant
------	-----------
