

7107W Multi-Conductor - 300V C-TC+ Control Cables for Extreme Flexing



For more Information
please call

1-800-Belden1



General Description:

20 AWG stranded (74x38) bare copper conductors, PVC insulation, Unshielded, Oil- and Abrasion-resistant PVC Jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
17	20	74x38	BC - Bare Copper

Total Number of Conductors: 18

Ground Wire

Ground Wire (Y/N): Y

Ground Wire AWG: 20

Ground Wire Stranding: 74x38

Ground Wire Conductor Material: BC - Bare Copper

Ground Wire Insulation Material: PVC - Polyvinyl Chloride

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.015

Insulation Color Code Chart:

Color	Description
Red	Individually Numbered

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
TPE - Thermoplastic Elastomer	0.053

Overall Cable

Overall Nominal Diameter: 0.480 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -50°C To +90°C

Other Temperature Range: Flexing: -5°C To +90°C

UL Temperature Rating: 90°C (UL AWM Style 2587)

Bulk Cable Weight: 184 lbs/1000 ft.

Max. Recommended Pulling Tension: 260 lbs.

Min. Bend Radius (Continuous Flexing): 5.500 in.

Flex Cycle Rating: 10 Million Flexes

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: PLTC

AWM Specification: UL Style 2587 (600 V 90°C), UL Style 21486 (1000 V 90°C)

CSA Specification: AWM I/II A/B

7107W Multi-Conductor - 300V C-TC+ Control Cables for Extreme Flexing

EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU REACH SVHC Present:	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 FT4/IEEE 1202 Vertical Tray Flame Test
CSA Flame Test:	FT4
IEEE Flame Test:	1202

Suitability

Suitability - Burial:	Yes
Sunlight Resistance:	Yes
Oil Resistance:	Yes - Oil Res II
Non-halogenated:	No

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

8.8

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7107W 0031000	1,000 FT	147.000 LB	ORANGE	C	17 #20 + GRD PVC TPE
7107W 003250	250 FT	47.500 LB	ORANGE	C	17 #20 + GRD PVC TPE
7107W 0035000	5,000 FT	765.000 LB	ORANGE		17 #20 + GRD PVC TPE

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 10-02-2013

© 2017 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.