

# Fuseholders 5 x 20 mm



6.3A 250Vac (max fuse rating\*) T-55 to T+70 (ambient)

Maximum dissipation wattage: 1.5W

UL 94V2 UL file E92075 CSA file LR44770

These products comply with safety category PC2

\*Users should be aware of the de-rating factors published by specialist manufacturers of fuses


These fuseholders are fitted with combination (solder / 2.8) mid-body terminals  
It has not been possible to show both views here



**M520**  
Terminal Cover




**A0033 00**  
In-line 5 x 20 fuseholder  
Call factory for rating details




▶ TERMINAL	▶ BODY AND CAP	▶ PANEL HOLE
<p><b>T</b></p> <p>Solder</p>	<p><b>0332</b> Finger release</p> <p><b>0333</b> Tool release</p> <p><b>0340</b> Tool release</p> <p><b>0341</b> Tool release</p>	<p><b>RA</b></p> <p><b>RD</b></p>

## DIMENSIONS (mm)


**0332** (T terminal shown)




**0333** (T terminal shown)












**0340** (T terminal shown)




**0341** (T terminal shown)



TYPE	TERMINAL
<b>0721-P</b> (2k min order)  Inlet 	<b>S</b> Solder 
<b>0722-C</b> (2k min order)  Inlet 	<b>Q</b> 4.8 Solder  <b>W</b> 6.3 Tab 
<b>0723-C</b> (2k min order)  Outlet 	<b>Q</b> 4.8 Solder  <b>W</b> 6.3 Tab 

### DIMENSIONS (mm)

View below is at Y















### Technical data

Mouldings V2 (VO option)  
 Connectors Tin plated solid brass  
 Terminals Silver plated

### Terminal dimensions

#### For Connectors

#### For Switches

For Connectors									For Switches		
S	N	Q	W	P	L	LS	V12	V16	Slide T	Slide K	Rocker T
2.5mm Solder	4mm Solder	4.8mm Solder/ Fast on	6.3 Fast on	PCB	Solder	2.8mm Solder	12-14 AWG Solid Wire	16 AWG Solid Wire	Solder	2.8mm Solder	4.8mm Solder
											
1.5x2.5 4.5	2.0x3.2 5.5	2.8x3.3 6.5	Ø1.7 8.0	1.7x3.0 5.5	Ø3.0x6.0	1.5x3.0 10.0	1.35	0.8	2.5 6.0 1.6	2.5 7.0 1.3	R1.0 R0.8 3.5 8.5

Note: Designated solder terminals should not be fitted with "Push on", "OD" or "Fast on" type cable connectors