

SmartOnline 208/240V 16kVA 14.4kW Double-Conversion UPS, N+1, 12U, Network Card Slot, USB, DB9 Serial, Bypass, L6-20R

MODEL NUMBER: **SU16KRT8**



Description

Tripp Lite SU16KRT8 16,000VA / 16kVA / 14,400 watt online, double-conversion UPS system offers complete power protection for critical server, network and telecommunications equipment in a 12U rack/tower configuration. This system delivers complete N+1 redundancy when used at loads up to 8kVA, and non-redundant operation at loads between 8 and 16kVA. Fault-tolerant auto-bypass prevents unexpected service interruptions during UPS overload or internal fault conditions. Included parallel PDU with manual bypass switching enables hot-swappable replacement of all major UPS system components in both N+1 and combined operating modes. Enhanced availability, fault tolerance and simple hot-swap replacement options make this UPS ideal for advanced networking applications in data centers, computer rooms, network closets and rugged industrial locations.

Features

- Tripp Lite SU16KRT8 16kVA, 16,000VA / 14,400 watt on-line, double-conversion UPS system in 12U total rack/tower configuration
- Unique configuration offers 16kVA non-redundant operation and automatic N+1 redundancy at load levels of 8kVA and under
- Included Parallel PDU with manual bypass switch enables hot-swap replacement of power modules at any supported load level
- Hardwire input; 8 L6-20R and 2 L6-30R outlets
- Maintains full-time sine wave output within 2% of selectable 200/208/220/230/240V nominal
- Supports 50/60Hz operation for worldwide frequency compatibility
- Expandable runtime with optional external battery packs
- Some external battery configurations require the use of Tripp Lite's External Battery Configuration Software (see manual)
- Battery independent restart
- Intelligent battery management system with temperature-compensated charging extends battery life
- Highly efficient economy mode option
- Compatible with Tripp Lite UPS management card options [TLNETCARD](#), [WEBCARDLX](#), [SNMPWEBCARD](#), [MODBUSCARD](#) and [RELAYIOCARD](#)
- Also compatible with [RELAYIOMINI](#) module ([RELAYIOMINI](#) requires removal of USB interface module)

Highlights

- 16kVA / 16,000VA / 14,400W on-line double-conversion UPS, 0.9 power factor
- 200/208/220/230/240V 50/60Hz output, 96% Efficient Economy-mode option
- Hot-swap power & battery modules, N+1 fault tolerance at loads up to 8kVA
- USB, RS232, EPO ports, slot for network management card options
- Front panel LEDs with detailed LCD monitoring and control screen
- Expandable runtime with optional external battery packs
- Hardwire input (3 wire), L6-20R and L6-30R outlets

Package Includes

- Two [SU8000RT3UPM](#) UPS power modules
- Two [BP240V10RT3U](#) battery packs
- [SUPDMB20K8](#) Parallel PDU with Bypass switch
- 4-post rackmount installation rails
- USB, DB9 & EPO Cabling



- Applications utilizing the optional network communications card require two [SNMPWEBCARD](#) accessories (install one per included power module)
- HID-compliant USB interface
- USB & Serial ports enable data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert
- Optional [2POSTRMKITHD](#) supports installation in 2 post 19 inch racks (4 required)
- Optional [2-9USTAND](#) supports upright tower placement (2 required)
- Supports Emergency Power Off (EPO) via built-in interface
- Front panel LEDs and LCD readout with scroll controls
- LED / LCD display panel rotates for viewing in rackmount or tower configurations
- External battery packs are field replaceable and hot swappable
- Frequency conversion mode enables conversion of 60Hz to 50Hz or 50Hz to 60Hz (no de-rating)

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	16000
Output kVA Capacity (kVA)	16
Output Watt Capacity (Watts)	14400
Output kW Capacity (kW)	14.4
Output Capacity Details	Supports up to 105% load continuously in double conversion mode, 106 to 125% for 1 minute, 126% to 150% for 30 seconds; Loads over 150% trigger immediate bypass mode operation to support loads directly from mains power; Double conversion mode is automatically restored as load levels are reduced to 95% or less
Power Factor	0.9
Crest Factor	3:1
Nominal Output Voltage(s) Supported	200V; 208V; 240V
Nominal Voltage Details	Voltage selection via front panel LCD interface
Frequency Compatibility	50 / 60 Hz; Supports 50 to 60 Hz and 60 to 50 Hz conversion
Frequency Compatibility Details	Output frequency matches input nominal on startup; Frequency conversion mode enables conversion of 60Hz to 50Hz or 50Hz to 60Hz (no de-rating)
Output Voltage Regulation (Line Mode)	+/- 2%
Output Voltage Regulation (Economy Line Mode)	+/- 10%
Output Voltage Regulation (Battery Mode)	+/- 2%
Output Receptacles	(8) L6-20R; (2) L6-30R
Output Circuit Breakers	8 20A breakers protect one L6-20R outlet each, 2 30A breakers protect one L6-30R outlet each
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave



INPUT	
Rated input current (Maximum Load)	92A (200V), 88.4A (208V), 76.6A (240V)
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 240V AC
UPS Input Connection Type	Hardwire
UPS Input Connection Description	3 wire single phase input (L1, L2, G)
Recommended Electrical Service	100A @ 200V, 208V, or 240V (L1, L2, G)
Input Phase	Single-Phase
BATTERY	
Full Load Runtime (min.)	5.5 minutes (14,400 watts)
Half Load Runtime (min.)	13.5 minutes (7200 watts)
Expandable Battery Runtime	Runtime is expandable with external battery packs
External Battery Pack Compatibility	BP240V10RT3U ; BP240V557C-1PH; BP240V787C-1PH ; BP240V1037C-1PH; BP240V1407C-1PH
Expandable Runtime Description	For best results, add external batteries in multiples of two so that both included 8kVA power modules have an equal number and type of connected battery packs
DC System Voltage (VDC)	240
Battery Recharge Rate (Included Batteries)	Less than 6 hours from 10% to 90% (typical, full load discharge)
Battery Replacement Description	Hot-swappable, user replaceable external battery packs
Expandable Runtime	Yes
VOLTAGE REGULATION	
Voltage Regulation Description	2% output voltage regulation in standard online, double-conversion mode
Overvoltage Correction	Corrects overvoltages up to 300V
Undervoltage Correction	Corrects undervoltages as low as 100V
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Selectable LCD display with scroll and selection buttons enables UPS control and detailed monitoring options; LED/LCD panel rotates for viewing in rack/tower formats; LCD Display supports ENGLISH, FRENCH, GERMAN, ITALIAN, SPANISH and PORTUGUESE (see manual)
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; 2 additional switches support set and execute scrolling LCD functions; bundled PDU includes bypass switch to enable hot-swap UPS power module replacement
Alarm Cancel Operation	Alarm cancel switch
Audible Alarm	Unique audible alarms for all major UPS, environmental and power conditions (see manual)
LED Indicators	6 LEDs indicate line power, online mode, economy/bypass mode, on-battery, charger and AC output status; LCD screen offers additional information and control options
SURGE / NOISE SUPPRESSION	



UPS AC Suppression Response Time	Instantaneous
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Included Mounting Accessory Description	4 sets of adjustable 4 post rack rails included (one for each included 3U module)
Installation Form Factors Supported with Optional Accessories	2 post rackmount(2POSTRMKITHD); Tower(2-9USTAND)
Optional Mounting Accessory Notes	Qty 4 2POSTRMKITHD required for 2 post rackmount installation; Qty 2 2-9USTAND required for tower installation
Primary Form Factor	Rackmount
UPS Power Module Dimensions (hwd, in.)	5.14 x 17.5 x 25.82
UPS Power Module Dimensions (hwd, cm)	13.06 x 44.45 x 65.58
Rack Height (U Spaces)	12
Maximum Device Depth (in.)	32.5
Minimum Required Rack Depth (inches)	37.5
Maximum Device Depth (cm)	82.55
Minimum Required Rack Depth (cm)	95.25
UPS Power Module Weight (lbs.)	43
UPS Power Module Weight (kg)	19.50
UPS Dimensions Details	Includes 2 SU8000RT3UPM UPS/Power modules, 2 BP240V10RT3U Battery packs and SUPDMB20K8 parallel bypass PDU; Listed weights and dimensions for UPS/Power module and Included battery pack each refer to a single unit; MAXIMUM DEVICE DEPTH specification refers to the whole UPS installed depth with parallel bypass PDU installed
Included Battery Pack Dimensions (hwd / in.)	5.25 x 17.5 x 25
Included Battery Pack Weight (lbs.)	158.7
Included Battery Pack Weight (kg)	71.99
UPS Shipping Dimensions (hwd / in.)	36 x 40.25 x 51
UPS Shipping Dimensions (hwd / cm)	91.44 x 102.24 x 129.54
Shipping Weight (lbs.)	600
Shipping Weight (kg)	272.4
Cooling Method	Fans
UPS Housing Material	Steel
Maximum Device Depth (mm)	826
Minimum Required Rack Depth (mm)	952



Primary UPS Height (mm)	131
Primary UPS Width (mm)	444
Primary UPS Depth (mm)	656
Shipping Height (mm)	914
Shipping Width (mm)	1022
Shipping Depth (mm)	1295
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius.
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius.
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	5464
AC Economy Mode BTU / Hr. (Full Load)	2047
Battery Mode BTU / Hr. (Full Load)	4864
AC Mode Efficiency Rating (100% Load)	90%
AC Economy Mode Efficiency Rating (100% Load)	96%
Operating Elevation (ft.)	0-3000m (0 to 10,000 ft.)
Audible Noise	60 dBA at front side 1 meter
Operating Elevation (m)	0-3000 m
COMMUNICATIONS	
Communications Interface	USB (HID enabled); DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface
Network Management Cards	SNMPWEBCARD ; TLNETCARD ; WEBCARDLX ; MODBUSCARD ; RELAYIOCARD
Network Monitoring Port Description	Applications utilizing any supported network management card option, require the use of two network cards of the same-model (install one card per included UPS power module); RELAYIOMINI installation requires removal of panel containing USB ports on each included UPS power module
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at http://www.tripplite.com/poweralert
Communications Cable	USB, DB9 serial and EPO cables included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer Time	No transfer time (0 ms.) in online, double-conversion mode
Transfer Time (Economy Mode)	8 milliseconds typical power failure response in optional economy mode
Low Voltage Transfer to Battery Power (Setpoint)	100V



High Voltage Transfer to Battery Power (Setpoint)	300V
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
Economy Mode Operation	Optional economy mode enables high efficiency bypass operation with a maximum output voltage variation of +/-10%. Double conversion mode is automatically restored as mains voltage varies beyond +/-10% with less than 1 millisecond transfer time between modes.
High Availability UPS Features	Automatic inverter bypass; Hot swappable batteries; Hot swappable UPS power module; Manual bypass switch
Green Energy-Saving Features	High efficiency economy mode operation; Support for daily startup and shutoff; Schedulable daily hours of economy mode operation
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Meets FCC Part 15 Category A (EMI); ROHS (Restriction of Hazardous Substances)
UPS Certification Details	IEC 61000-4-5 1995 B Surge Immunity
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>