

AVR Series 230V 550VA 300W Ultra-Compact Line-Interactive UPS with USB port, C13 Outlets

MODEL NUMBER: AVRX550U











Highlights

- 550VA ultra-compact 230V line interactive UPS
- Corrects brownouts and overvoltages from 159V to 282V
- 3 UPS battery supported outlets,
 3 surge-only outlets
- USB port, TEL/DSL protection, Wall mountable
- C14 inlet and 6 C13 outlets

Package Includes

- AVRX550U UPS System
- USB cable
- Two C13 to C14 power cables
- Instruction manual

Description

Tripp Lite's AVRX550U Ultra-Compact Line Interactive UPS offers complete power protection for desktop PCs, network workstations and a wide variety of professional and consumer electronic devices. Uninterruptible Power Supply / UPS circuits switch to battery backup mode within milliseconds to keep connected equipment running without interruption or data loss during power failures. Automatic Voltage Regulation / AVR power conditioning maintains smooth, continuous operation of connected equipment during brownouts and overvoltages. Surge-only outlets offer convenient protection for printers and other desktop accessories not requiring battery support. AC and dataline surge suppression prevents connected equipment damage. USB communications port supports built-in power management and auto-shutdown features of Windows and Mac OS X or full featured monitoring and data-saving auto-shutdown options using Tripp Lite's free PowerAlert monitoring software.

Features

- AVRX550U ultra-compact 230V line interactive UPS offers complete AC power protection from blackouts, brownouts and transient surges
- 550VA / 300 watt UPS output capacity
- Uninterruptible Power Supply / UPS operation maintains battery-derived AC output during blackouts to prevent data loss and system downtime for connected equipment
- Built-in USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from www.tripplite.com/poweralert
- HID-compliant USB port also enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- Automatic Voltage Regulation / AVR corrects extended brownouts and overvoltages from 159 to 282V, without using battery power
- 5.1 minutes runtime at 50% load (150 watts)
- Up to 10 minutes runtime for a small desktop computer system consuming 80 watts continuous
- 6 total C13 outlets; Includes two 2m C13 to C14 power cables
- 3 UPS battery backup outlets, plus 3 additional surge-only outlets
- C14 inlet supports a variety of site specific input cordsets
- . Network grade AC surge and lightning protection is available from all outlets; Built-in data line surge suppression protects a single dialup or DSL line
- Supports Tripp Lite's Watchdog system service to restore operation to locked equipment through soft reboot of application/OS or hard power off/on reboot of connected equipment, ideal for unattended kiosk applications



- Built-in grounding lug
- Hot swappable user battery replacement supported via easy access battery access door
- Optional PDUBHV10 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- Space saving, ultra-compact housing with support for wall-mount, desktop or floor placement

Specifications

OUTPUT		
Output Volt Amp Capacity (VA)	550	
Output Watt Capacity (Watts)	300	
Nominal Output Voltage(s) Supported	220V; 230V; 240V	
Nominal Voltage Details	230V nominal output in battery mode	
Frequency Compatibility	50 / 60 Hz	
Frequency Compatibility Details	Automatic frequency selection	
Output Voltage Regulation (Line Mode)	+8%, -21%	
Output Voltage Regulation (Battery Mode)	+/- 5%	
Output Receptacles	(6) C13	
Included Output Power Cables	Includes 2 C13 to C14 output power cables	
UPS Output Receptacles (Surge Suppression Only)	3 UPS outlets, 3 surge-only outlets	
Hot-Swap PDU options	PDUBHV10 (2U / 8 C13 outlets)	
Output AC Waveform (AC Mode)	Sine wave	
Output AC Waveform (Battery Mode)	PWM sine wave	
INPUT		
Rated input current (Maximum Load)	10A	
Nominal Input Voltage(s) Supported	230V AC	
UPS Input Connection Type	C14 inlet	
UPS Input Connection Description	Attached 15cm line cord with C14 inlet. The C14 inlet accepts user-supplied AC power cord with country specific plug	
UPS Input Cord Length (ft.)	0.5	
UPS Input Cord Length (m)	0.2	
Input Phase	Single-Phase	
BATTERY		
Half Load Runtime (min.)	5.1 min. (150w)	





DC System Voltage (VDC)	12	
Battery Access	Battery access door	
Battery Replacement Description	Hot-swappable, user replaceable batteries	
Expandable Runtime	No	
VOLTAGE REGULATION		
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 159 to 282VAC	
Overvoltage Correction	Input voltages between 245 and 282 are reduced by 12%	
Undervoltage Correction	Input voltages between 159 and 205 are boosted by 14%	
USER INTERFACE, ALERTS & CONTROLS		
Switches	Combination switch controls on/off power status and self-test operation	
Audible Alarm	Audible alarm indicates power-failure and overload status	
LED Indicators	2 LEDs indicate power status and overload/check battery status	
SURGE / NOISE SUPPRESSION		
UPS AC Suppression Joule Rating	320	
UPS AC Suppression Response Time	Instantaneous	
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out)	
EMI / RFI AC Noise Suppression	Yes	
PHYSICAL		
Installation Form Factors Supported with Included Accessories	Tower; Ultra-compact desktop	
Primary Form Factor	Desktop	
UPS Power Module Dimensions (hwd, in.)	3.5 x 11 x 5.8	
UPS Power Module Dimensions (hwd, cm)	8.89 x 27.94 x 14.73	
UPS Power Module Weight (lbs.)	8.5	
UPS Power Module Weight (kg)	3.86	
UPS Shipping Dimensions (hwd / in.)	5.5 x 13.8 x 9	
UPS Shipping Dimensions (hwd / cm)	13.97 x 35.05 x 22.86	
Shipping Weight (lbs.)	10.2	
Shipping Weight (kg)	4.6	
UPS Housing Material	ABS	



Primary UPS Width (mm)	279	
Primary UPS Depth (mm)	147	
Shipping Height (mm)	140	
Shipping Width (mm)	351	
Shipping Depth (mm)	229	
ENVIRONMENTAL		
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius	
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius	
Relative Humidity	0 to 95%, non-condensing	
AC Mode BTU / Hr. (Full Load)	54	
Battery Mode BTU / Hr. (Full Load)	360	
AC Mode Efficiency Rating (100% Load)	95%	
COMMUNICATIONS		
Communications Interface	USB (HID enabled)	
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at http://www.tripplite.com/poweralert	
Communications Cable	USB interface cable included	
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications	
Network UPS Tools Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at http://www.networkupstools.org/stable-hcl.html?manufacturer=Tripp Lite	
LINE / BATTERY TRANSFER		
Transfer Time	4 milliseconds	
Low Voltage Transfer to Battery Power (Setpoint)	159	
High Voltage Transfer to Battery Power (Setpoint)	282	
SPECIAL FEATURES		
Grounding Lug	Included	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported	
High Availability UPS Features	Hot swappable batteries	
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS	
CERTIFICATIONS		



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPS Certifications	CE; Tested to GOST (Russia); Tested to SASO (Saudi Arabia); Meets FCC Part 15 Category B (EMI); ROHS (Restriction of Hazardous Substances)	
UPS Certification Details	EN62040	
WARRANTY		
Product Warranty Period (International)	2-year limited warranty	

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies