

## TAA-Compliant SmartPro 120V 3kVA 2.88kW Line-Interactive Sine Wave UPS, 2U Rack/Tower, Extended Run, Pre-installed Network Management Card, LCD, USB, DB9 Serial

MODEL NUMBER: **SM3000RMLNTAA**



### Description

Tripp Lite SmartPro Line Interactive UPS with enhanced LCD interface offers network-grade power protection for critical server, network and telecommunications equipment. Line Interactive Uninterruptible Power Supply (UPS) with built-in Auto-Voltage Regulation (AVR) actively corrects brownouts and overvoltages back to usable levels while maintaining a full battery charge in case of power failure. Tripp Lite's unique configuration excels in exceptionally poor-power environments with two separate levels of voltage boost to correct both slight undervoltages and severe brownout conditions. Interactive LCD interface reports UPS operating mode, detailed UPS and site-power data, plus enables a variety of UPS setup and configuration options. Super-fast switchover from line to battery power occurs within milliseconds to maintain operation of connected equipment without interruption or reboot. 96% line-mode efficiency offers reduced heat emissions and operating costs. Network management interfaces support communications via USB, RS-232 and pre-installed Network Management Card network interface. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Network communications ports enable detailed monitoring of equipment load levels, self-test data and utility power conditions. PowerAlert UPS monitoring and auto shutdown software is available via free download. Switched output load banks enable scheduled and real-time remote reboot and load shedding of select outlets. Emergency Power Off (EPO) interface. LCD display panel easily rotates for viewing in rackmount or tower configurations. Audible alarm with push-button momentary alarm-cancel and silent-mode configuration options. Programmable self-test. Field-replaceable, hot-swappable battery modules.

### Features

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- Tripp Lite SM3000RMLNTAA line interactive 2U rack/tower UPS with 3000VA / 3kVA capacity and extended runtime options
- Line interactive UPS with Automatic Voltage Regulation (AVR) corrects brownouts and overvoltages from 83 to 145V
- NEMA L5-30P input plug; 8 NEMA 5-15/20R and 1 L5-30R output receptacles, Two independently switchable output load banks
- Maintains uninterrupted operation of connected networking equipment during blackouts, surges, brownouts and overvoltages

### Highlights

- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases
- 3kVA / 3000VA / 2880W line interactive 2U rack/tower UPS; 0.96 power factor
- 120V nominal output during brownouts to 83V and overvoltages to 145V
- Interactive LCD provides UPS status information and advanced configuration options
- Expandable runtime, Hot-swap batteries, 96% efficiency, Sine wave output
- USB, RS232 & EPO ports, Pre-installed Network Management Card
- NEMA L5-30P input; 8 NEMA 5-15/20R & 1 L5-30R outlets
- **This product is ENERGY STAR qualified for its ability to save customers money while helping to protect the environment**

### Package Includes

- SM3000RMLNTAA UPS system with Pre-installed Network Management Card
- USB, Serial & EPO cabling
- 4 post rackmount installation kit
- Instruction manual



- High 96% efficiency rating in line-power mode offers reduced power consumption and BTU emissions
- Internal batteries offer 10 minutes at 50% load (1440W) and 3 minutes at 100% load (2880W)
- Extended runtime is available with optional [BP48V24-2U](#) (limit 1), [BP48V60RT-3U](#) (multi-pack compatible) and [BP48V27-2US](#) (multi-pack compatible) external battery packs
- External battery configurations require the use of Tripp Lite's External Battery Configuration Software (see manual)
- Hot-swappable, user-replaceable internal batteries and external battery packs can be replaced with no disruption to connected equipment
- Front panel LCD monitoring screen with MODE and ENTER buttons reports operating mode with 5-bar battery charge graphic, plus 7 selectable screens of detailed UPS and site power information
- LCD interface also supports a number of advanced user setup and operating preferences
- Ships with 4 post rackmount installation hardware; Optional [2POSTRMKITWM](#) enables 2 post rackmount/wallmount installation; Optional [2-9USTAND](#) enables tower placement
- Built-in USB, RS-232 and pre-installed Network Management Card accessory monitoring options
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- USB & Serial ports enable data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from [www.tripplite.com/poweralert](http://www.tripplite.com/poweralert)
- Built-in Emergency Power Off (EPO) interface with cable

## Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	3000
Output kVA Capacity (kVA)	3
Output Watt Capacity (Watts)	2880
Output kW Capacity (kW)	2.88
Power Factor	.96
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Nominal Voltage Details	120v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	+6%, -14%
Output Voltage Regulation (Battery Mode)	+/-5%
Output Receptacles	(8) 5-15/20R; (1) L5-30R
Load Management Receptacles	Two switchable single outlet 5-15/20R load banks
Output Circuit Breakers	Two 20A output breakers protect 4 5-15/20R outlets each
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
INPUT	



Rated input current (Maximum Load)	24A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	L5-30P
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.0
Recommended Electrical Service	30A 120V
Input Phase	Single-Phase
<b>BATTERY</b>	
Full Load Runtime (min.)	3 min. (2880w)
Half Load Runtime (min.)	10 min. (1440w)
Expandable Battery Runtime	Extended runtime supported via optional external battery packs
External Battery Pack Compatibility	<a href="#">BP48V24-2U</a> (limit 1); <a href="#">BP48V60RT-3U</a> (multi-pack compatible); <a href="#">BP48V27-2US</a> (multi-pack compatible)
DC System Voltage (VDC)	48
Battery Recharge Rate (Included Batteries)	Less than 5 hours from 10 to 90%
Internal UPS Replacement Battery Cartridge	<a href="#">RBC58-2U</a>
Battery Access	Front panel battery access door
Battery Replacement Description	Hot-swappable, replaceable batteries
Expandable Runtime	Yes
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 145
Overvoltage Correction	Input voltages between 127 and 145 are reduced by 12%
Undervoltage Correction	Input voltages between 108 and 96 are boosted by 12%
Severe Undervoltage Correction	Input voltages between 83 and 95 are boosted by 24%
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)
Switches	3 pushbutton switches control OFF / ON power status, MODE selection and MUTE / ENTER control functions
Alarm Cancel Operation	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	570



UPS Dataline Suppression	1 line TEL/DSL or Ethernet
EMI / RFI AC Noise Suppression	Yes
AC Suppression Response Time	Instantaneous
<b>PHYSICAL</b>	
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount
Installation Form Factors Supported with Optional Accessories	2 post rackmount(2POSTRMKITWM); Wallmount(2POSTRMKITWM); Tower(2-9USTAND)
Primary Form Factor	Rackmount
UPS Power Module Dimensions (hwd, in.)	3.5 x 17.5 x 19
UPS Power Module Dimensions (hwd, cm)	8.89 x 44.45 x 48.26
Rack Height (U Spaces)	2
Minimum Required Rack Depth (inches)	26
Minimum Required Rack Depth (cm)	66.04
UPS Power Module Weight (lbs.)	72.8
UPS Power Module Weight (kg)	33.02
UPS Shipping Dimensions (hwd / in.)	9 x 23.5 x 20
UPS Shipping Dimensions (hwd / cm)	22.86 x 59.69 x 50.80
Shipping Weight (lbs.)	84.6
Shipping Weight (kg)	38.4
Cooling Method	Fan
UPS Housing Material	Steel
Minimum Required Rack Depth (mm)	660
Primary UPS Height (mm)	89
Primary UPS Width (mm)	444
Primary UPS Depth (mm)	483
Shipping Height (mm)	229
Shipping Width (mm)	597
Shipping Depth (mm)	508
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius



Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	409
Battery Mode BTU / Hr. (Full Load)	1736
AC Mode Efficiency Rating (100% Load)	96%
<b>COMMUNICATIONS</b>	
Communications Interface	DB9 Serial; EPO (emergency power off); Pre-installed network card; Slot for SNMP/Web interface; USB (HID enabled)
Network Monitoring Port Description	Includes pre-installed Network Management Card interface
PowerAlert Software	For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at <a href="http://www.tripplite.com/poweralert">http://www.tripplite.com/poweralert</a>
Communications Cable	USB, DB9 and EPO cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	5 milliseconds (AC to battery mode), 1 millisecond (Battery to AC mode)
Low Voltage Transfer to Battery Power (Setpoint)	83
High Voltage Transfer to Battery Power (Setpoint)	145
<b>SPECIAL FEATURES</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Hot swappable batteries
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks; Schedulable daily hours of economy mode operation
<b>CERTIFICATIONS</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI); TAA Compliant; ENERGY STAR Qualified
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 <a href="#">Ultimate Lifetime Insurance</a>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)