



† Red band indicates fully mated

†† Blue band indicates rear release contact retention system

★ .059 dia min.

1.5 dia min., 3 lockwire holes formed lockwire hole design (6 holes) is optional

Note: -Drawing not to Scale

-Dimensions subject to change

-Dimensions are in Inches, Millimeters (MM) & Blue color

Property of Amphenol Aerospace.

All rights reserved.

Part No.:

D38999/24FD18BA

Amphenol[®]
Aerospace

40-60 Delaware Avenue

Sidney, NY 13838-1395

800-678-0141

Cage Code: 77820

www.amphenol-aerospace.com



Amphenol Aerospace
 40-60 Delaware Avenue
 Sidney, NY 13838-1395
Phone: 800-678-0141 - **Fax:** 607-563-5157
Email: info@amphenol-aerospace.com
Website: www.amphenol-aerospace.com

Joe Ryder
 Product Line Manager
 Core Products
Phone: 607-563-5001
Email: jryder@amphenol-ao.com

Specifications

Connector Type	D38999/
Shell Style	Jam Nut Receptacle
Shell Material	Aluminum
Shell Finish	Electroless Nickel
Insulation Resistance	5000 megohms min. @500 VDC25C
Operating Temperature [Min]	-65°C
Operating Temperature [Max]	+200°C
Shielding Effectiveness	65dB@10GHz
Durability	48 Hour Salt Spray
Contact Type	B
Contact Description	Less Sockets

Contacts

Insert Arrangement	
Front Face of Pin Insert Shown	
Shell Size	D
Insert Arrg	18
Service Rating	I
Total # Contacts	18
Test Current	7.5 AMPS
Wire Size for 20	24, 22, 20
Contact Size 20	18
Number of Contacts	