

Safety Data Sheet



1. Product and Company Identification

Product name

Manganese dioxide lithium battery

Details of the supplier of the safety data sheet

Premier Farnell
150 Armley Road
Leeds LS12 2QQ
Tel. : +44 (0) 870 129 8608

Emergency telephone number

+44 (0) 870 202530

2 Hazards Identification

GHS Classification : Not applicable
Hazard : Electrolyte and lithium metal are flammable. Risk of explosion by fire if batteries are disposed in fire or heated above 100°C.
Stacking or jumbling batteries may cause external short circuits, heat generation, fire or explosion.
Toxicity : Vapor generated from burning batteries, may irritate eyes, skin and throat.

3. Hazards identifications

Component	Material	CAS No.	Content
Positive electrode	Manganese dioxide	1313-13-9	12 ~ 50wt%
Negative electrode	Lithium metal	7439-93-2	0.5 ~ 6wt%
Electrolyte	1,2-dimethoxyethane	110-71-4	1.5 ~ 3.5wt%
	Lithium Perchlorate	7791-03-9	0.2 ~ 0.7wt%
	Organic electrolyte	-	2.5 ~ 7wt%
Others (Steel or Plastic parts)	Steel	7439-89-6, 7440-47-3	30 ~ 85wt%
	Polypropylene	9003-07-0	0.5 ~ 10wt%

Lithium content per cell

Model Number	Lithium Content(g)	Model Number	Lithium Content(g)	Model Number	Lithium Content(g)	Model Number	Lithium Content(g)
CR1025	0.008	CR1620	0.02	CR2330	0.08	CR2412	0.03
CR1216	0.008	CR1632	0.04	CR2354	0.17	CR2430	0.09
CR1220	0.01	CR2012	0.02			CR2450	0.18
CR1612	0.01	CR2016	0.03			CR2450A	0.17
CR1616	0.02	CR2025	0.05			CR2477	0.29
		CR2032	0.07			CR3032	0.15
		CR2050B	0.1				



4. First Aid Measures

The product contains organic electrolyte. In case of electrolyte leakage from the battery, actions described below are required.

- Eye contact : Flush the eyes with plenty of clean water for at least 15 minutes immediately, without rubbing. Get immediate medical treatment. If appropriate procedures are not taken, this may cause eye injury.
- Skin contact : Wash the contact areas off immediately with plenty of water and soap. If appropriate procedures are not taken, this may cause sores on the skin.
- Inhalation : Remove to fresh air immediately. Get medical treatment immediately.

5. Fire Fighting Measures

- Extinguishing method : Since vapor, generated from burning batteries may make eyes, nose and throat irritates, be sure to extinguish the fire on the windward side. Wear the respiratory protection equipment in some cases.
- Fire extinguishing agent : Alcohol-resistant foam and dry sand are effective.

6. Accidental Release Measures (in case of electrolyte leakage from the battery)

Take up with absorbent cloth, treat cloth as inflammable.
Move the battery away from the fire.

7. Handling and Storage

When packing the batteries, do not allow battery terminals to contact each other, or contact with other metals. Be sure to pack batteries by providing partitions in the packaging box, or in a separate plastic bag so that the single batteries are not mixed together.

Use strong material for packaging boxes so that they will not be damaged by vibration, impact, dropping and stacking during their transportation.

Do not recharge batteries. Do not deform batteries.

Do not mix different type of batteries.

Do not solder directly onto batteries.

Do not let water penetrate into packaging boxes during their storage and transportation.

Do not store the battery in places of the high temperature or under direct sunlight.

Please also avoid the places of high humidity. Be sure not to expose the battery to condensation, rain or frozen condition.

8. Exposure Controls and Personal Protection (in case of electrolyte leakage from the battery)

- Acceptable concentration : Not specified in ACGIH.
- Facilities : Provide appropriate ventilation system such as local ventilator in the storage place.
- Protective clothing : Self-Contained Breathing Apparatus for organic gases, safety goggle, and safety glove.

9. Physical and Chemical Properties

- Appearance : Coin shape
- Voltage : 3 volts

10. Stability and Reactivity

Since batteries utilize a chemical reaction they are actually considered a chemical product. As such, battery performance will deteriorate over time even if stored for a long period of time without being used. In addition, the various usage conditions such as discharge, ambient temperature, etc. are not maintained within the specified ranges the life expectancy of the battery may be shortened or the device in which the battery is used may be damaged by electrolyte leakage.

11. Toxicological Information (in case of electrolyte leakage from the battery)

Acute toxicity : Oral(rat) LD50 > 2,000mg/kg (estimated)
Irritation : Irritating to eye and skin.
Mutagenicity : Not specified.
Chronic toxicity : Not specified.

12. Ecological Information

In case the worn-out battery is disposed of on land, the battery case may corrode and leak electrolyte.

13. Disposal Considerations

When the battery is worn out, dispose of it under the ordinance of each local government.

14. Transport Information

During the transportation of a large amount of batteries by ship, trailer or railway, do not leave them in the places of high temperatures and do not allow them to be exposed to condensation.

During the transportation do not allow packages to be dropped or damaged.

Proper shipping name : Lithium metal batteries
UN Number, UN Class : UN3090, Class9 (for the Air transport by PI968 Section IA or IB)
: Exemption (for the Marine transport and the Air transport by Section II of PI 968, 969 or 970)
Even though the cells are classified as lithium metal batteries (UN3090 or 3091), they are not subject to some requirements of Dangerous Goods Regulations because they meet the following:
1. For cells, the lithium content is not more than 0.3g;
2. Each cell is of the type proven to meet the requirements of each test in the UN Manual of Tests and Criteria, Part III, sub-section 38.3.
3. Each cell is manufactured in ISO9001 certified factory.

Please refer to the following reference information about concrete ways of transportation. Actual content of packaging label and shipping documents varies by shipping companies. Make sure to confirm in advance with your shipping company.

Information of reference

	Reference	Packing Instruction(PI)/ Special provision(SP)	Note
Air transport	IATA (2)(5)	PI 968 Section I A	Cells, Cargo Aircraft only; Net quantity per package Max. 35kg
		PI 968 Section I B	Cells, Cargo Aircraft only; net quantity per package Max. 2.5kg
		PI 968 Section II	Cells, Cargo Aircraft only, not more than one package in any single consignment; net quantity per package Max. 2.5kg

Safety Data Sheet



	Reference	Packing Instruction(PI)/ Special provision(SP)	Note
Air transport	IATA (2)(5)	PI 969 Section II	Cells packed with equipment
		PI 970 Section II	Cells contained in equipment, button cell batteries
Marine transport	IMDG (3)	SP 188	

15. Regulatory Information

IATA Dangerous Goods Regulations

IMO International Maritime Dangerous Goods Code

16. Other Information

This data sheet is provided to customers as reference information in order to handle batteries safely. It is necessary for the customer to take appropriate measures depending on the actual situation such as the individual handling, based on this information.

In California only, packages that contain CR lithium coin cells and the Owners/Operating Instructions of products that contain CR lithium coin cells must include the following statement:

“Perchlorate Material - special handling may apply, See www.dtsc.ca.gov/hazardouswaste/perchlorate”.

The effective date for this Perchlorate label is July 1, 2006 for non-consumer products and January 1, 2007 for consumer products.

References : (1) UN Recommendations on the Transportation of Dangerous Goods, Model Regulations
(2) IATA Dangerous Goods Regulations 57th Edition (2016)
(3) IMO International Maritime Dangerous Goods Code 2014 Edition
(4) UN Recommendations on the Transportation of Dangerous Goods, Manual of Tests and Criteria
(5) IATA Dangerous Goods Regulations 57th edition Effective 1 January 2016 ADDENDUM

Important Notice : This data sheet and its contents (the “Information”) belong to the members of the Premier Farnell group of companies (the “Group”) or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group’s liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com
www.farnell.com
www.newark.com

