

LPS170 Series

175 Watts

Data Sheet

Total Power: 100 - 175 Watts Input Voltage: 85 - 264 Vac 120 - 300 Vdc

of Outputs: Single

SPECIAL FEATURES

- Active power factor correction
- IEC EN61000-3-2 compliance
- Wide range adjustable output: Remote sense on main output
- Single wire current sharing
- Power fail and remote inhibit
- Built-in EMI filter
- Low output ripple
- Overvoltage protection
- Overload protection
- Thermal overload protection
- DC power good
- 5 V standby output
- 12 V Aux output
- Optional cover (-C suffix)
- RoHS compliant

SAFETY

VDE 0805/EN60950 (IEC950)

UL UL1950

CB Certificate and report

CSA CSA 22.2-234 Level 3

CE Mark (LVD)

■ NEMKO EN 60950/EMKO-TUE



Electrical Specifications		
Input		
Input range	85 - 264 Vac; 120-300 Vdc	
Frequency	47 - 63 Hz	
Inrush current	38 A max, cold start @ 25°C	
Efficiency	75% typical at full load	
EMI filter	FCC Class B conducted CISPR 22 Class B conducted EN55022 Class B conducted VDE 0878 PT3 Class B conducted	
Power Factor	0.99 typical	
Safety ground leakage current	1.0 mA @ 50/60 Hz, 264 Vac input	
Output		
Maximum power	110 W convection (75 W with cover) 175 W with 30 CFM forced air (130 W with cover)	
Adjustment range	2:1 wide ratio minimum	
Standby outputs	5 V @ 2 A regulated ±5%	
Hold-up time	20 ms @175 W load at nominal line	
Overload protection	Short circuit protection on all outputs. Case overload protected @ 110-145% above peak rating	
Overvoltage protection	10% to 40% above nominal output	
Aux output	12 V @ 1 A -5 %, +10%	



Logic Control	
Power failure	TTL logic signal goes high 100 - 500 msec after V1 output; It goes low at least 4 msec before loss of regulation
Remote inhibit	Requires contact closure to inhibit outputs
Remote sense	Compensates for 0.5 V lead drop min. Will operate without remote sense connected. Reverse connection protected.
DC - OK	TTL logic signal goes high after main output is in regulation. It goes low when there is a loss of regulation


Environmental Specifications		
Operating temperature	0° to 50 °C ambient; derate each output at 2.5% per degree from 50° to 70 °C	
Low temperature start	-20 °C	
Temperature coefficient	±0.4% per °C	
Storage temperature	-40° to 85 °C	
Electromagnetic susceptibility	Designed to meet IEC EN61000-4, -2, -3, -4, -5, -6, -8, -11 Level 3	
Humidity	Operating; non-condensing 5% to 95%	
Vibration	Three orthogonal axes, sweep at 1 oct/min, 5 min. dwell at four major resonances 0.75G peak 5Hz to 500Hz, operational	
MTBF demonstrated	>550,000 hours at full load and 25 °C ambient conditions	

Ordering Information							
Model Number	Output Voltage	Minimum Load	Maximum Load with Convection Cooling	Maximum Load with 30CFM Forced Air	Peak Load ¹	Regulation ²	Ripple P/P(PARD) ³
LPS172	5 V (2.5 - 6 V)	0 A	22 A	35 A	38 A	±2%	50 mV
LPS173	12 V (6 - 12 V)	0 A	9.1 A	15 A	16.5 A	±2%	120 mV
LPS174	15 V (12 - 24 V)	0 A	7.3 A	12 A	13.2 A	±2%	<1%
LPS175	24 V (24 - 54 V)	0 A	4.5 A	7.5 A	8.2 A	±2%	<1%


- 1. Peak current lasting <30 seconds with a maximum 10% duty cycle.
- 2. At 25 °C including initial tolerance, line voltage, load currents and output voltages adjusted to factory settings.
- 3. Peak-to-peak with 20 MHz bandwidth and 10 μ F in parallel with a 0.1 μ F capacitor at rated line voltage and load ranges.
- 4. Remote inhibit resets OVP latch.
- 5. This product is a Component Power Supply and is only for inclusion by professional installers within other equipment and must not be operated as a standalone product. EMC compliance to appropriate standards must be verified at the system level. This product is for sale to OEMs and System Integrators, including through Distribution Channels. It is not intended for sale to End Users.


Note: -C suffix added to the model number indicates cover option.


Mechanical Drawing



tp tp tp







Pin Assignments				
Connector	LPS17x	LPS17x		
SK1	PIN 1	+12 V		
	PIN 2	5 V Standby		
	PIN 3	Common		
	PIN 4	V1 SWP		
	PIN 5	Common		
	PIN 6	+V1 sense		
	PIN 7	Sense common		
	PIN 8	Remote inhibit		
	PIN 9	DC power good		
	PIN 10	POK		
SK3	TB-1	COMMON		
	TB-2	Main output		
SK4	PIN 1	GROUND		
	PIN 3	LINE		
	Pin 5	NEUTRAL		

In the th

Mating Connectors		
AC Input (SK4)	Molex 09-50-8051 (USA) Molex 09-91-0500 (UK) PINS: 08-58-0111	
DC Outputs (SK3)	Molex 19141-0058	
Control Signals (SK1)	Molex 90142-0010 (USA) PINS: 90119-2110 or Amp: 87977-3 PINS: 87309-8	
Artesyn Embedded Technologies Connector Kit #70-841-016, includes all of the above		

- 1. Specifications subject to change without notice.
- 2. All dimensions in inches (mm), tolerance is ± 0.02 " (± 0.5 mm)
- 3. Mounting holes M1 and M2 should be grounded for EMI purposes.
- 4. Mounting hole M1 is safety ground connection.
- 5. Specifications are for convection rating at factory settings at 115 Vac input, 25 °C unless otherwise stated.
- 6. Warranty: 2 years
- 7. Weight: 1.8 lbs/0.85 kg

WORLDWIDE OFFICES

Americas

2900 S.Diablo Way Tempe, AZ 85282 USA +1 888 412 7832

Europe (UK)

Waterfront Business Park Merry Hill, Dudley West Midlands, DY5 1LX United Kingdom +44 (0) 1384 842 211

Asia (HK)

14/F, Lu Plaza 2 Wing Yip Street Kwun Tong, Kowloon Hong Kong +852 2176 3333



www.artesyn.com

For more information: www.artesyn.com/power For support: productsupport.ep@artesyn.com