

# Features

## TRIAC Dimmable LED Driver

- Triac –dimmable with leading or trailing edge dimmers
- Class II with SELV output (no earth required)
- Extra-large screw terminals and integrated cable clamps for easy installation
- Power factor corrected >0.95
- Dimming range 1..100%
- Compatible with a wide range of dimmers



## RACT25

25 Watt  
TRIAC  
Dimmable  
Single Output



IEC/EN61347 Certified  
IEC/EN61347-2-13 Certified  
EN61547 Certified  
EN62493 Certified  
EN55015 Compliant  
CB Report

### Description


The RACT25-xxx series are low cost, triac-dimmable, constant current 25W LED drivers available with either 500mA, 700mA or 1.05A full-range outputs. The drivers are Class II (double insulated) meaning no earth connection is required. The phase angle dimming works with leading or trailing edge dimmers. The RACT25 is suitable for indoor locations up to 50°C ambient temperature and is certified for building into furniture for applications such as dimmable shelf lighting, cove lighting or accent lighting. It is CE marked (LVD + EMC + RoHS) and has IEC61347-1/IEC61347-2-13 CB report certification.

### Selection Guide

Part Number	Input Voltage Range [VAC]	Output Voltage Range [VDC]	Output Current [mA]	Efficiency min. @rated load [%]	Output Power [W]
RACT25-500	198-264	25-50	500	85	25
RACT25-700	198-264	18-36	700	85	25
RACT25-1050	198-264	12-24	1050	84	25

All LED Drivers may not be used without a load. They must be switched on the primary side only. Noncompliance may damage the LED or reduce its lifetime.

### Model Numbering



### Specifications (measured @ ta= 25°C, 240VAC, rated load unless otherwise specified)

BASIC CHARACTERISTICS				
Parameter	Condition	Min.	Typ.	Max.
Input Voltage Range		198VAC	230VAC	264VAC
Input Current				160mA
Inrush Current	full load			5A
No Load Power Consumption				1W
Input Frequency Range		50Hz		60Hz
Power Factor	full load	0.95		

continued on next page

### Specifications (measured @ $t_a = 25^\circ\text{C}$ , 240VAC, rated load unless otherwise specified)

Parameter	Condition	Min.	Typ.	Max.
THD	full load			20%
Start-up Time				500ms
Internal Operating Frequency	RACT25-500 RACT25-700, 1050		77kHz 65kHz	
Output Ripple Current <sup>(1)</sup>	RACT25-500 RACT25-700 RACT25-1050			170mA 260mA 440mA

**Notes:**  
 Note1: Measured at 20MHz BW by using a 12" twisted pair-wie terminated with a 0.1 $\mu\text{F}$  and 47 $\mu\text{F}$  capacitor parallel across output.

REGULATIONS		
Parameter	Condition	Value
Output Accuracy		$\pm 5\%$ typ.
Load Regulation		5% max.
Line Regulation		5% max.

PROTECTION		
Parameter	Condition	Value
Input Fuse		fusible resistor
Short Circuit Protection (SCP)		Latch OFF, auto recovery after fault condition is removed
Over Voltage Protection (OVP)	RACT25-500 RACT25-700 RACT25-1050	58VDC max. 45VDC max. 32VDC max. Latch OFF, auto recovery after fault condition is removed
Over Load Protection (OLP)		Latch OFF, auto recovery after fault condition is removed
Over Temperature Protection (OTP)	110 $^\circ\text{C}$	Latch OFF, auto recovery after fault condition is removed
Isolation Voltage	I/P to O/P   tested for 1 minute	3.75kVAC
Leakage Current		5mA max.

#### Maximum loading of automatic circuit breakers\*

\* @ 230VAC, 10hm, 90 $^\circ$  phase angle and max. load

Circuit Breaker	Circuit Breaker Current			
	10A	16A	20A	25A
Typ				
B	24	38	46	58
C	38	62	74	92


ENVIRONMENTAL		
Parameter	Condition	Value
Operating Temperature Range	without derating @ natural convection 0.1m/s (see graph)	-20 $^\circ\text{C}$ to +50 $^\circ\text{C}$
Max. Case Temperature	at tc point	+80 $^\circ\text{C}$ max.
Operating Humidity	non-condensing	5-85% RH
IP Rating		IP20
Pollution Degree		PD2
Design Lifetime	+25 $^\circ\text{C}$ ambient	>30 x 10 <sup>3</sup> hours

continued on next page

**Specifications** (measured @  $t_a = 25^\circ\text{C}$ , 240VAC, rated load unless otherwise specified)

**Derating Graph**

(@ Chamber and natural convection 0.1m/s)



**SAFETY AND CERTIFICATIONS**

Certificate Type (Safety)	Report Number	Standard
Lamp Controlgear General Requirements for Safety (CB Scheme)	325797	IEC61347-1:2007, 2nd Edition
Lamp Controlgear Particular Requirements (CB Scheme)		IEC61347-2-13: 2014, 2nd Edition
Lamp Controlgear General Requirements for Safety (LVD)		EN61347-1:2007, 2nd Edition
Lamp Controlgear Particular Requirements (LVD)		EN61347-2-13: 2014, 2nd Edition
RoHS2+		RoHS 2011/65/EU + AM2015/863

EMC Compliance	Condition	Standard / Criterion
Limits and methods of measurement of radio disturbance characteristics of electrical lighting and similar equipment		EN55015: 2013 +A1 2015
Limits for harmonic current emissions		IEC61000-3-2: 2014, Class C
Limitation of voltage fluctuations/flicker in low-voltage systems		IEC61000-3-3:2013
Equipment for general Lighting Purpose EMC Immunity Requirements		IEC61547:2009
Assessment of lighting equipment related to human exposure to electromagnetic fields		EN62493:2015
ESD Electrostatic discharge immunity test	$\pm 8\text{kV}$ Air Discharge, $\pm 4\text{kV}$ Contact Discharge	IEC61000-4-2, Criteria A
Radiated, radio-frequency, electromagnetic field immunity test	3V/m	IEC61000-4-3, Criteria A
Fast Transient and Burst Immunity	L-N= $\pm 1\text{kV}$ ; DC Output= $\pm 0.5\text{kV}$	IEC61000-4-4, Criteria A
Surge Immunity	L-N= $\pm 0.5\text{kV}$	IEC61000-4-5, Criteria A
Immunity to conducted disturbances, induced by radio-frequency fields	3V r.m.s.	IEC61000-4-6, Criteria A
Voltage Dips and Interruptions	>95% reduction 30%	IEC61000-4-11, Criteria B IEC61000-4-11, Criteria B



**DIMENSION and PHYSICAL CHARACTERISTICS**

Parameter	Type	Value
Material	Case PCB	Plastic (UL94V-2) FR4 (UL94V-0)
Package Dimension (LxWxH)		120.0 x 45.0 x 28.0mm
Package Weight		100g typ.




continued on next page

**Specifications** (measured @  $t_a = 25^\circ\text{C}$ , 240VAC, rated load unless otherwise specified)


### Dimensions Drawing (mm)



wire stripping length: 6-7mm  
recommended tightening torque: 0.25Nm  
 $t_c$  = case temperature measuring point  
FC = fixing centers  
Tolerance: xx.x =  $\pm 1.0\text{mm}$   
xx.xx =  $\pm 0.5\text{mm}$



without cable cover's



### Connection via Screw Terminal

Function	Solid Wire	Stranded Wire <sup>(3)</sup>	AWG
VAC in (N)	0.75-2.5mm <sup>2</sup>	0.75-2.5mm <sup>2</sup>	20-14
VAC in (L)	0.75-2.5mm <sup>2</sup>	0.75-2.5mm <sup>2</sup>	20-14
LED+	0.5-2.5mm <sup>2</sup>	0.5-2.5mm <sup>2</sup>	21-14
LED-	0.5-2.5mm <sup>2</sup>	0.5-2.5mm <sup>2</sup>	21-14


### Notes:

Note3: The use of sleeve or ferrule terminations is recommended.

### INSTALLATION and APPLICATION

Dimming Type	Value
AC phase-cut	work with leading/trailing edge dimmers

### Connection



**Specifications** (measured @  $t_a = 25^\circ\text{C}$ , 240VAC, rated load unless otherwise specified)

PACKAGING INFORMATION		
Parameter	Type	Value
Packaging Dimension (LxWxH)	cardboard box	330.0 x 137.0 x 55.0mm
Packaging Quantity		10pcs
Storage Temperature Range		-20°C to +70°C
Storage Humidity	non-condensing	5-85% RH