

Productname : SERVISOL PLASTIC SEAL 60
Ref.Nr.: UDS000488_3_20170629 (EN)

Creationdate : 29.06.17 Version : 2.0
Replaces: UDS000488_20150515

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

SERVISOL PLASTIC SEAL 60
Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Anti Corrosion Products

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.
Ambersil House - Wylds Road
Castlefield Industrial Estate
TA6 4DD Bridgwater Somerset
United Kingdom
Tel.: +44 1278 727200
Fax.: +44 1278 425644
E-mail : hse.uk@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303 0	(07229)30 32 66

1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical: Aerosols, category 1
Extremely flammable aerosol.
Pressurised container: May burst if heated.

Classification is based on test data.

Health: Skin irritation, category 2
Causes skin irritation.
Eye irritation, category 2
Causes serious eye irritation.
Specific target organ toxicity - single exposure, category 3
May cause drowsiness or dizziness.



Productname : SERVISOL PLASTIC SEAL 60
Ref.Nr.: UDS000488_3_20170629 (EN)

Creationdate : 29.06.17 Version : 2.0
Replaces: UDS000488_20150515




Classification based on calculation method.

Environment: Hazardous to the aquatic environment, chronic category 2
 Toxic to aquatic life with long lasting effects.

Classification based on calculation method.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Product identifier:	Contains: Hydrocarbons, C7, n-alkanes, isoalkanes, cyclic butan-1-ol; n-butanol
Hazard pictogram(s):	  
Signal word:	Danger
Hazard statement(s):	H222 : Extremely flammable aerosol. H229 : Pressurised container: May burst if heated. H315 : Causes skin irritation. H319 : Causes serious eye irritation. H336 : May cause drowsiness or dizziness. H411 : Toxic to aquatic life with long lasting effects.
Precautionary statement(s):	P102 : Keep out of reach of children. P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 : Do not spray on an open flame or other ignition source. P251 : Do not pierce or burn, even after use. P261 : Avoid breathing dust/fume/gas/mist/vapours/spray. P271 : Use only outdoors or in a well-ventilated area. P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P501-2 : Dispose of contents/container to an authorised waste collection point.

2.3. Other hazards

No information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Hydrocarbons, C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene <	01-2119485926-20	68512-91-4	270-990-9	30-60	Press. Gas, Flam. Gas 1	H280, H220	K, G



2 / 10

CRC Industries UK Limited

Ambersil House, Wylds Road, Castlefield Industrial Estate,
Bridgwater, Somerset, TA6 4DD

Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.crcind.com

Productname : SERVISOL PLASTIC SEAL 60
Ref.Nr.: UDS000488_3_20170629 (EN)

Creationdate : 29.06.17 Version : 2.0
Replaces: UDS000488_20150515

0.1%)							
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclic	01-2119475515-33	-	(927-510-4)	10-30	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H225,H315,H336,H304,H411	Q
xylene		1330-20-7	215-535-7	10-20	Flam. Liq. 3, Acute Tox. 4, Acute Tox. 4, Skin Irrit. 2	H226,H332,H312,H315	A
ethylbenzene	01-2119489370-35	100-41-4	202-849-4	1-5	Flam. Liq. 2, Acute Tox. 4, STOT RE 2, Asp. Tox. 1	H225,H332,H373,H304	A
butan-1-ol; n-butanol	01-2119484630-38	71-36-3	200-751-6	1-5	Flam. Liq. 3, Acute Tox. 4, Skin Irrit. 2, Eye Dam. 1, STOT SE 3, STOT SE 3	H226,H302,H315,H318,H335,H336	B

Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

G : exempted from the obligation to register in accordance with art.2(7)of REACH Regulation No 1907/2006

K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

Q : The CAS-no is only an indicative identifier to be used outside the EU for global inventory entries.

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures**4.1. Description of first aid measures**

Contact with eyes :	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Contact with skin :	Take off contaminated clothing and wash before reuse. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention.
Inhalation :	IF INHALED: Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Ingestion :	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	Irritating to skin Symptoms : redness and pain
Eye contact :	Irritating to eyes Symptoms : redness and pain, impaired vision

4.3. Indication of any immediate medical attention and special treatment needed

3 / 10

CRC Industries UK Limited

Ambersil House, Wylds Road, Castlefield Industrial Estate,
 Bridgwater, Somerset, TA6 4DD

Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.crcind.com

Productname : SERVISOL PLASTIC SEAL 60
Ref.Nr.: UDS000488_3_20170629 (EN)

Creationdate : 29.06.17 Version : 2.0
Replaces: UDS000488_20150515

General Advice : If you feel unwell, seek medical advice (show the label where possible)
If symptoms persist always call a doctor

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent
Do not use water jet extinguishing media, due to the risk of spreading fire.

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material
Place in appropriate container
This material and/or its container must be disposed of as hazardous waste.

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling



Productname : SERVISOL PLASTIC SEAL 60
Ref.Nr.: UDS000488_3_20170629 (EN)

Creationdate : 29.06.17 Version : 2.0
Replaces: UDS000488_20150515

Keep away from heat and sources of ignition
 Take precautionary measures against static discharges
 Equipment should be earthed
 Use explosion-proof electrical/ventilating/lighting/.../equipment.
 Use only non-sparking tools.
 Do not breathe aerosols or vapours.
 Ensure adequate ventilation
 Avoid contact with skin and eyes.
 Wash thoroughly after use
 Wear protective gloves/protective clothing/eye protection/face protection.
 Eyewash bottles should be available

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
 Keep out of reach of children.

7.3. Specific end use(s)

Anti Corrosion Products

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
ethylbenzene	100-41-4	TWA	100 ppm
		STEL	200 ppm

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation In all cases handle and use the product in accordance with good industrial hygiene practices.
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment.
hands and skin :	When handling the product wear chemical-resistant gloves (standard EN 374).
Recommended gloves:	Nitrile The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through. Depending on amount and duration of use and the risk of contact with the



Productname : SERVISOL PLASTIC SEAL 60 **Creationdate :** 29.06.17 Version : 2.0
Ref.Nr.: UDS000488_3_20170629 (EN) **Replaces:** UDS000488_20150515

product the gloves manufacturer can assist you in the selection of the right glove material and breakthrough time.
eyes : Wear safety eyewear according to EN 166.
Environmental protection: Avoid release to the environment.
Collect spillage.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Apperance : physical state : Propane/butane propelled liquid.
colour : Colorless.
odour : Solvent.
pH : Not applicable.
Boiling point/range : 94 °C
Flash point : - 4 °C
Evaporation rate : Not available.
Explosion limits : upper limit : 9.4 %
lower limit : 1 %
Vapour pressure : Not available.
Relative density : 0.822 g/cm³ (@ 20°C).
Solubility in water : Insoluble in water
Auto-ignition : > 200 °C
Viscosity : Not available.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials



Productname : SERVISOL PLASTIC SEAL 60
Ref.Nr.: UDS000488_3_20170629 (EN)

Creationdate : 29.06.17 Version : 2.0
Replaces: UDS000488_20150515

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

acute toxicity:	based on available data the classification criteria are not met
skin corrosion/irritation:	Causes skin irritation.
serious eye damage/irritation:	Causes serious eye irritation.
respiratory or skin sensitisation:	based on available data the classification criteria are not met
germ cell mutagenicity:	based on available data the classification criteria are not met
carcinogenicity:	based on available data the classification criteria are not met
toxicity for reproduction:	based on available data the classification criteria are not met
STOT-single exposure:	May cause drowsiness or dizziness.
STOT repeated exposure:	based on available data the classification criteria are not met
aspiration hazard:	based on available data the classification criteria are not met

Information on likely routes of exposure:

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact :	Irritating to skin
Eye contact :	Irritating to eyes

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
butan-1-ol; n-butanol	71-36-3	LD50 oral rat	2292 mg/kg
		LC50 inhal.rat	> 17.76 mg/l
		LD50 derm.rabit	3430 mg/kg
Hydrocarbons, C7, n-alkanes,isoalkanes, cyclic	-	LD50 oral rat	> 5840 mg/kg
		LC50 inhal.rat	23.3 mg/l
		LD50 derm.rat	> 2920 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, chronic category 2
 Toxic to aquatic life with long lasting effects.



Productname : SERVISOL PLASTIC SEAL 60
Ref.Nr.: UDS000488_3_20170629 (EN)

Creationdate : 29.06.17 Version : 2.0
Replaces: UDS000488_20150515

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
butan-1-ol; n-butanol	71-36-3	LC50 fish	1376 mg/l
		EC50 daphnia	1328 mg/l
Hydrocarbons, C7, n-alkanes, isoalkanes, cyclic	-	IC50 algae	10-30 mg/l
		LC50 fish	> 13.4 mg/l
		EC50 daphnia	3 mg/l

12.2. Persistence and degradability

No information available

12.3. Bioaccumulative potential

No information available

12.4. Mobility in soil

Insoluble in water

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No information available

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product : This material and its container must be disposed of in a safe way.
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

National regulations : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information**14.1. UN number**

UN-number : 1950

14.2. UN proper shipping name

Productname : SERVISOL PLASTIC SEAL 60 **Creationdate :** 29.06.17 Version : 2.0
Ref.Nr.: UDS000488_3_20170629 (EN) **Replaces:** UDS000488_20150515

Proper shipping name: AEROSOLS (hydrocarbons)

14.3. Transport hazard class(es)

Class: 2.1
ADR/RID - Classification code: 5F

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: Yes
IMDG - Marine pollutant: Marine pollutant
IATA/ICAO - Environmentally hazardous: Yes

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D, S-U
IATA/ICAO - PAX: 203
IATA/ICAO - CAO: 203

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Regulation (EC) No 1907/2006 (REACH)
Regulation (EC) No 1272/2008 (CLP)
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation hazard statements: H220 : Extremely flammable gas.
H225 : Highly flammable liquid and vapour.
H226 : Flammable liquid and vapour.



Productname : SERVISOL PLASTIC SEAL 60 **Creationdate :** 29.06.17 Version : 2.0
Ref.Nr.: UDS000488_3_20170629 (EN) **Replaces:** UDS000488_20150515

H280 : Contains gas under pressure; may explode if heated.
H302 : Harmful if swallowed.
H304 : May be fatal if swallowed and enters airways.
H312 : Harmful in contact with skin.
H315 : Causes skin irritation.
H318 : Causes serious eye damage.
H332 : Harmful if inhaled.
H335 : May cause respiratory irritation.
H336 : May cause drowsiness or dizziness.
H373 : May cause damage to organs through prolonged or repeated exposure
.
H411 : Toxic to aquatic life with long lasting effects.

REVISIONS IN CHAPTRE : 8.2. Exposure controls
acronyms and synonyms: TWA = time weight average
STEL = short time exposure limit
VOC = volatile organic compounds
PBT = persistant bioaccumulative toxic
vPvB = very persistant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

