



Revision Number: 008.0

Issue date: 09/11/2014

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	LOCTITE AA 3494 LC known as LOCTITE 3494 VIS/UV	IDH number:	1170169
Product type:	Ultraviolet adhesive	Item number:	43336
Restriction of Use:	None identified	Region:	United States
Company address:	Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067	Contact information:	Telephone: (860) 571-5100 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887 Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

DANGER: COMBUSTIBLE LIQUID.
CAUSES SKIN IRRITATION.
MAY CAUSE AN ALLERGIC SKIN REACTION.
CAUSES SERIOUS EYE DAMAGE.

HAZARD CLASS	HAZARD CATEGORY
FLAMMABLE LIQUID	4
SKIN IRRITATION	2
SERIOUS EYE DAMAGE	1
SKIN SENSITIZATION	1

PICTOGRAM(S)



Precautionary Statements

Prevention:	Keep away from heat, sparks, open flames, hot surfaces - no smoking. Avoid breathing vapors, mist, or spray. Wash thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves, eye protection, and face protection.
Response:	IF ON SKIN: Wash with plenty of soap and water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to remove. Continue rinsing. Immediately call a poison control center or physician. If skin irritation or rash occurs: Get medical attention. Take off contaminated clothing. In case of fire: Use foam, dry chemical or carbon dioxide to extinguish.
Storage:	Store in a well-ventilated place. Keep cool.
Disposal:	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Polyurethane Methacrylate Resin	Unknown	30 - 60
Acrylate monomer	Proprietary	10 - 30
2-Hydroxyethyl methacrylate	868-77-9	10 - 30
High boiling methacrylate	Proprietary	5 - 10
Acrylic acid	79-10-7	1 - 5
Hydroxyalkyl methacrylate	27813-02-1	1 - 5
Substituted silane	Proprietary	1 - 5
Diphenyl-2,4,6-trimethylbenzoyl phosphine oxide	75980-60-8	1 - 5
Ethylene glycol	107-21-1	0.1 - 1
Adhesion Promoter	Proprietary	0.1 - 1

* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If breathing is difficult, give oxygen. If not breathing, give artificial respiration. Get medical attention.
Skin contact:	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. Wash clothing before reuse. Get medical attention.
Eye contact:	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
Ingestion:	DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention.
Symptoms:	See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Water spray (fog), foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. In case of fire, keep containers cool with water spray.
Unusual fire or explosion hazards:	Uncontrolled polymerization may occur at high temperatures resulting in explosions or rupture of storage containers.
Hazardous combustion products:	Oxides of carbon. Oxides of phosphorus. Oxides of nitrogen. Oxides of silicon. Formaldehyde Irritating organic vapours.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
-----------------------------------	---------------------------------------------------

Clean-up methods:

Remove all sources of ignition. Evacuate and ventilate spill area; dike spill to prevent entry into water system; wear full protective equipment during clean-up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Scrape up as much material as possible. Store in a partly filled, closed container until disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

7. HANDLING AND STORAGE

Handling:

Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Do not taste or swallow. Refer to Section 8.

Storage:

For safe storage, store at or below 38 °C (100.4 °F)
Keep in a cool, well ventilated area away from heat, sparks and open flame.
Keep container tightly closed until ready for use. Keep out of direct sunlight.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Polyurethane Methacrylate Resin	None	None	None	None
Acrylate monomer	None	None	None	None
2-Hydroxyethyl methacrylate	None	None	None	3 ppm Ceiling
High boiling methacrylate	None	None	None	None
Acrylic acid	2 ppm TWA (SKIN)	None	None	1 ppm TWA 3 ppm STEL (SKIN)
Hydroxyalkyl methacrylate	None	None	None	1 ppm TWA 3 ppm STEL
Substituted silane	None	None	None	None
Diphenyl-2,4,6-trimethylbenzoyl phosphine oxide	None	None	None	None
Ethylene glycol	100 mg/m3 Ceiling Aerosol.	None	None	None
Adhesion Promoter	20 ppm TWA	None	None	None

Engineering controls:

Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.

Respiratory protection:

Use NIOSH approved respirator if there is potential to exceed exposure limit(s).

Eye/face protection:

Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.

Skin protection:

Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact. Neoprene gloves. Butyl rubber gloves. Natural rubber gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:

Liquid

Color:

Clear

Odor:

Sharp

Odor threshold:

Not available.

pH:

Not applicable

Vapor pressure:

< 10 mm hg (24 °C (75.2 °F))

Boiling point/range:	Not available.
Melting point/ range:	Not available.
Specific gravity:	1.024
Vapor density:	Not available.
Flash point:	87.8 °C (190.04 °F) Tagliabue closed cup
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not available.
Evaporation rate:	Not available.
Solubility in water:	Slight
Partition coefficient (n-octanol/water):	Not available.
VOC content:	0.68 %; 6.96 g/l (process) 0.41 %; 4.20 g/l (potential) 1.09 %; 11.16 g/l (total) (ASTM D5403)
Viscosity:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	None under normal processing. Polymerization may occur at elevated temperature or in the presence of incompatible materials.
Hazardous decomposition products:	Oxides of carbon. Oxides of nitrogen. Oxides of phosphorus. Oxides of silicon. Formaldehyde Irritating organic vapours.
Incompatible materials:	Strong oxidizing agents. Reducing agents. Free radical initiators. Acids and bases. Peroxides. Alkalis. Amines. Heavy metals. Oxygen scavengers. Moisture.
Reactivity:	Not available.
Conditions to avoid:	Keep away from heat, ignition sources and incompatible materials. UV light. Direct sunlight. Elevated temperatures. Loss of polymerization inhibitor. Store away from incompatible materials.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure:	Skin, Inhalation, Eyes, Ingestion
-------------------------------------	-----------------------------------

Potential Health Effects/Symptoms

Inhalation:	Inhalation of vapors or mists of the product may be irritating to the respiratory system. May cause irritation to nose and throat.
Skin contact:	Causes skin irritation. May cause allergic skin reaction.
Eye contact:	Causes serious eye damage.
Ingestion:	May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Polyurethane Methacrylate Resin	None	Irritant, Allergen
Acrylate monomer	None	Irritant, Allergen
2-Hydroxyethyl methacrylate	Oral LD50 (RAT) = 11.2 g/kg Oral LD50 (RAT) = 5,050 mg/kg	Irritant, Allergen
High boiling methacrylate	None	Irritant, Allergen
Acrylic acid	Oral LD50 (RAT) = 33.5 mg/kg Oral LD50 (RAT) = 2.5 g/kg Oral LD50 (RAT) = 193 mg/kg Oral LD50 (RAT) = 1,250 mg/kg Inhalation LC50 (RAT, 4 h) = 1,200 mg/l	Allergen, Corrosive, Irritant, Kidney, Liver
Hydroxyalkyl methacrylate	None	Irritant, Allergen
Substituted silane	None	Allergen, Irritant
Diphenyl-2,4,6-trimethylbenzoyl phosphine oxide	None	No Records
Ethylene glycol	Oral LD50 (RAT) = 5.89 g/kg Dermal LD50 (RABBIT) = 9,530 mg/kg	Blood, Bone Marrow, Central nervous system, Developmental, Eyes, Irritant, Kidney, Liver, Metabolic
Adhesion Promoter	Oral LD50 (RABBIT) = 1,200 mg/kg Oral LD50 (RAT) = 1,060 mg/kg Oral LD50 (RAT) = 2,224 mg/kg Dermal LD50 (RABBIT) = 500 mg/kg Inhalation LC50 (RAT, 4 h) = 7.1 mg/l	Corrosive, Irritant, Allergen

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Polyurethane Methacrylate Resin	No	No	No
Acrylate monomer	No	No	No
2-Hydroxyethyl methacrylate	No	No	No
High boiling methacrylate	No	No	No
Acrylic acid	No	No	No
Hydroxyalkyl methacrylate	No	No	No
Substituted silane	No	No	No
Diphenyl-2,4,6-trimethylbenzoyl phosphine oxide	No	No	No
Ethylene glycol	No	No	No
Adhesion Promoter	No	No	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.
Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Combustible liquid, n.o.s.
Hazard class or division: Combustible Liquid
Identification number: NA 1993
Packing group: III

International Air Transportation (ICAO/IATA)

Proper shipping name: Environmentally hazardous substance, liquid, n.o.s. (Isobornyl acrylate)
Hazard class or division: 9
Identification number: UN 3082
Packing group: III

Water Transportation (IMO/IMDG)

Proper shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Isobornyl acrylate)
Hazard class or division: 9
Identification number: UN 3082
Packing group: III
Marine pollutant: Isobornyl acrylate

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification: None above reporting de minimis
CERCLA/SARA Section 302 EHS: None above reporting de minimis
CERCLA/SARA Section 311/312: Immediate Health, Delayed Health, Fire
CERCLA/SARA Section 313: This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Acrylic acid (CAS# 79-10-7).
California Proposition 65: This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDSL Status: One or more components are not listed on, and are not exempt from listing on either the Domestic Substances List or the Non-Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

Prepared by: Sheila Gines, Regulatory Affairs Specialist
Issue date: 09/11/2014

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.