

3M™ Thermally Conductive Adhesive Tape 8943

Product Description

3M™ Thermally Conductive Adhesive Tape 8943 is designed to provide an efficient heat transfer path between heat generating components and heat sinks or other cooling devices.

The tape consists of a carrier, highly loaded with thermally conductive fillers, coated on one side (3M™ 8943) with a high temperature resistance acrylic pressure sensitive adhesive.

The specialized constructions securely bond the heat generating components to heat sinks and offers conductivity. The tape is electrical insulating.

Product Construction

3M™ Thermally Conductive Adhesive Tape 8943	
Color	Beige
Carrier	Filled Copolymer
Adhesive Type	Modified Acrylic Adhesive
Tape Type	Single-coated
Tape Thickness	0.170 mm
Liner Thickness	0.075 mm

Typical Applications

Applications requiring thin bonding with good thermal transfer. The tape performance properties have been primarily adapted to meet the demanding criteria for use in Automotive Electronic Thermal Management. Typical applications are: Engine Control Units, ABS Systems, Gear Control Units.

Typical Properties and Performance Characteristics

Note: The following technical information for 3M™ Thermally Conductive Adhesive Tape 8943 should be considered representative or typical only and should not be used for specification purposes.

Thermal Properties

Test	Unit	Value	Test Method
Thermal Conductivity at 25°C	W/m*K	0.4	Mod. ASTM D 5470
Coefficient of Thermal Expansion (-40 to 150°C)	mm/°C	140 x 10 ⁶	3M Method (TMA)
Thermal Impedance	°C•in ² /W	0.73	3M
	°C•cm ² /W	4.7	3M

Electrical Properties

Test	Unit	Value	Test Method
Breakdown Voltage typical value ^(*)	kV	9.9	IEC 60243-1
Dielectric Strength typical value ^(*)	kV/mm	62.7	IEC 60243-1
Volume Resistivity	Ω•cm	2.5 x 10 ¹³	ASTM D257

Footnote:

^(*)Average value (not for specification purposes). Standard deviation of 0.9 kV has been observed.

^(*)Average value (not for specification purposes). Standard deviation of 5.4 kV/mm has been observed.

Mechanical Properties

Test	Unit	Value	Test Method	
90° Peel Adhesion to Aluminum Substrate (AlMg ₃ ; R _a : 0.48 μm; R _z : 2.4 μm)	20 min dwell time @ room temperature	N/cm	5.0	AFERA 4001
	24 hour dwell time @ room temperature	N/cm	6.0	AFERA 4001
	@ 150°C	N/cm	4.9	AFERA 4001
	@ 180°C	N/cm	2.4	AFERA 4001
Lap Shear	20 min dwell time @ room temperature	MPa	5.3	ASTM D 1002
	24 hour dwell time @ room temperature	MPa	9.0	ASTM D 1002
	After 24 hour @ 150°C	MPa	6.8	ASTM D 1002
	After 24 hour @ -40°C	MPa	9.0	ASTM D 1002
Holding Power	1000 g load @ room temperature	Minutes	10,000+	AFERA 4012
	500 g load @ 70°C	Minutes	10,000+	AFERA 4012
Tensile Strength	Tensile Strength	N/mm ²	6-7	EN ISO 527-2
	Elongation at break	%	80-120	EN ISO 527-2
Liner Properties	Liner release	cN/25.4 mm	15	FINAT TM3
Temperature Performance	Thermal Stability 225°C Dwell @ 60 min (Tape was applied between a glass and an aluminum panel)	Visual	No Change	3M
	Continuous Operating Temperature Range	°C	-40 up to 150	3M

Typical Properties and Performance Characteristics (continued)

Note: The following technical information for 3M™ Thermally Conductive Adhesive Tape 8943 should be considered representative or typical only and should not be used for specification purposes.

Thermal Resistance Properties

Test	Unit	Value	Test Method
Thermal Gravimetric Analysis* Mass loss @ 200°C	%	< 0.2	3M
Mass loss @ 150°C after 4 hours	%	< 0.3	3M

*Average value (not for specification purposes).

Application Guidelines

1) Substrate surfaces should be clean and dry prior to tape application. Isopropyl alcohol (isopropanol) applied with a lint-free wipe or swab should be adequate for removing surface contamination such as dust or finger prints. Do not use “denatured alcohol” or glass cleaners which often contain oily components. Allow the surface to dry for several minutes before applying the tape. More aggressive solvents (such as acetone, methyl ethyl ketone (MEK) or toluene) may be required to remove heavier contamination (grease, machine oils, solder flux, etc.) but should be followed by a final isopropanol wipe as described above.

Note: Be sure to read and follow the manufacturers’ precautions and directions when using primers and solvents.

2) Apply the tape to one substrate at a modest angle with the use of a squeegee, rubber roller pressure to help reduce the potential for air entrapment under the tape during its application. The liner can be removed after positioning the tape onto the first substrate.

3) Assemble the part by applying compression to the substrates to ensure a good wetting of the substrate surfaces with the tape. Proper application of pressure (amount of pressure, time applied, temperature applied) will depend upon design of the parts. The preferred pressure at room temperature is a minimum of 1 kg/cm² for 5 seconds. For fragile parts lower pressure may be needed.

Rigid substrates are more difficult to bond without air entrapment as most rigid parts are not flat. Flexible substrates can be bonded to rigid or flexible parts with much less concern about air entrapment because one of the flexible substrates can conform to the other substrate.

Shelf Life

Product shelf life is 2 years from date of manufacture when stored at room temperature (20°C to 25°C) and 50% R. H. in the products original packaging.

Regulatory

For regulatory information about this product, contact your 3M representative.

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Electronics Markets Materials Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
1-800-251-8634 phone
651-778-4244 fax
www.3M.com/electronics

3M is a trademark of 3M Company.
Please recycle. Printed in U.S.A.
© 3M 2014. All rights reserved.
60-5002-0678-8

