



Revision Number: 004.0

Issue date: 08/28/2014

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	LOCTITE LB 8150 SV A/S known as Silver Grade Anti-Seize Lubric	IDH number:	235005
Product type:	Lubricant	Item number:	76764
Restriction of Use:	None identified	Region:	United States
Company address:	Contact information:		
Henkel Corporation	Telephone: (860) 571-5100		
One Henkel Way	MEDICAL EMERGENCY Phone: Poison Control Center		
Rocky Hill, Connecticut 06067	1-877-671-4608 (toll free) or 1-303-592-1711		
	TRANSPORT EMERGENCY Phone: CHEMTREC		
	1-800-424-9300 (toll free) or 1-703-527-3887		
	Internet: www.henkelna.com		

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

DANGER: CAUSES SEVERE SKIN BURNS AND EYE DAMAGE.

HAZARD CLASS	HAZARD CATEGORY
SKIN CORROSION	1C
SERIOUS EYE DAMAGE	1

PICTOGRAM(S)



Precautionary Statements

Prevention:	Do not breathe vapors, mist, or spray. Wash thoroughly after handling. Wear protective gloves, eye protection, and face protection.
Response:	IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. If on skin (or hair): Take off immediately all contaminated clothing. IF INHALED: Remove person to fresh air and keep comfortable for breathing. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to remove. Continue rinsing. Immediately call a poison control center or physician. Wash contaminated clothing before reuse.
Storage:	Store locked up.
Disposal:	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
------------------------	------------	-------------

Distillates (petroleum), hydrotreated heavy naphthenic	64742-52-5	30 - 60
Graphite	7782-42-5	10 - 30
Calcium oxide	1305-78-8	10 - 30
Petroleum distillates, hydrotreated, light naphthenic	64742-53-6	10 - 30
Aluminum not powder, dust or fume	7429-90-5	5 - 10
Distillates (petroleum), straight-run middle	64741-44-2	1 - 5
Quartz (SiO ₂)	14808-60-7	0.1 - 1

* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.
Skin contact:	Remove contaminated clothing and footwear. Immediately flush skin with plenty of water (using soap, if available). Get medical attention. Wash clothing before reuse.
Eye contact:	Immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Ingestion:	Do not induce vomiting. Never give anything by mouth to an unconscious person. Get immediate medical attention.
Symptoms:	See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. In case of fire, keep containers cool with water spray.
Unusual fire or explosion hazards:	None
Hazardous combustion products:	Oxides of carbon. Oxides of nitrogen.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up. For small spills wipe up with paper towel and place in container for disposal. For large spills absorb onto inert absorbent material and place in sealed container for disposal.

7. HANDLING AND STORAGE

Handling:	Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Keep container closed.
Storage:	Keep in a cool, well ventilated area.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Distillates (petroleum), hydrotreated heavy naphthenic	5 mg/m ³ TWA mist 10 mg/m ³ STEL mist	5 mg/m ³ TWA mist 500 ppm (2,000 mg/m ³) PEL 5 mg/m ³ PEL Mist.	None	None
Graphite	2 mg/m ³ TWA Respirable fraction.	5 mg/m ³ PEL Respirable fraction. 15 mg/m ³ PEL Total dust. 15 MPPCF TWA	None	None
Calcium oxide	2 mg/m ³ TWA	5 mg/m ³ PEL	None	None
Petroleum distillates, hydrotreated, light naphthenic	None	500 ppm (2,000 mg/m ³) PEL 5 mg/m ³ PEL Mist.	None	None
Aluminum not powder, dust or fume	None	None	None	None
Distillates (petroleum), straight-run middle	5 mg/m ³ TWA mist 10 mg/m ³ STEL mist	5 mg/m ³ TWA mist	None	None
Quartz (SiO ₂)	0.025 mg/m ³ TWA Respirable fraction.	2.4 MPPCF TWA Respirable. 0.1 mg/m ³ TWA Respirable. 0.3 mg/m ³ TWA Total dust.	None	None

Engineering controls:

Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.

Respiratory protection:

If personal exposure cannot be controlled below applicable limits by ventilation, wear a properly fitted organic vapor/particulate respirator approved by NIOSH. Observe OSHA regulations for respirator use (29 CFR 1910.134).

Eye/face protection:

Safety goggles or safety glasses with side shields. Safety showers and eye wash stations should be available.

Skin protection:

Neoprene or oil resistant gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Paste
Color:	Silver
Odor:	Hydrocarbon-like
Odor threshold:	Not available.
pH:	Not applicable
Vapor pressure:	< 5 mm hg
Boiling point/range:	Not available.
Melting point/ range:	Not available.
Specific gravity:	1.25
Vapor density:	Not available.
Flash point:	> 93 °C (> 199.4 °F)
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not determined
Evaporation rate:	Not available.
Solubility in water:	Insoluble
Partition coefficient (n-octanol/water):	Not available.
VOC content:	< 3 %
Viscosity:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	Will not occur.
Hazardous decomposition products:	Irritating organic vapours. Oxides of carbon. Oxides of nitrogen.
Incompatible materials:	Strong oxidizing agents.
Reactivity:	Not available.
Conditions to avoid:	Keep away from heat, ignition sources and incompatible materials.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure: Skin, Inhalation, Eyes, Ingestion

Potential Health Effects/Symptoms

Inhalation:	May cause respiratory tract irritation.
Skin contact:	Causes skin burns. May cause skin irritation.
Eye contact:	Causes serious eye damage. This product may cause irritation to the eyes.
Ingestion:	May cause gastrointestinal disturbances.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Distillates (petroleum), hydrotreated heavy naphthenic	None	Irritant
Graphite	None	Lung
Calcium oxide	None	Irritant, Corrosive, Eyes
Petroleum distillates, hydrotreated, light naphthenic	None	Irritant
Aluminum not powder, dust or fume	None	Central nervous system, Irritant, Lung
Distillates (petroleum), straight-run middle	None	Irritant
Quartz (SiO ₂)	None	Immune system, Lung, Some evidence of carcinogenicity

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Distillates (petroleum), hydrotreated heavy naphthenic	No	No	No
Graphite	No	No	No
Calcium oxide	No	No	No
Petroleum distillates, hydrotreated, light naphthenic	No	No	No
Aluminum not powder, dust or fume	No	No	No
Distillates (petroleum), straight-run middle	No	No	No
Quartz (SiO ₂)	Known To Be Human Carcinogen.	Group 1	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.
Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/IMDG)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification: None above reporting de minimis
CERCLA/SARA Section 302 EHS: None above reporting de minimis
CERCLA/SARA Section 311/312: Immediate Health, Delayed Health
CERCLA/SARA Section 313: None above reporting de minimis
California Proposition 65: This product contains a chemical known in the State of California to cause cancer.

Canada Regulatory Information

CEPA DSL/NDL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

Prepared by: Lou Fabrizio, Regulatory Affairs Specialist
Issue date: 08/28/2014

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.