



Revision Number: 002.1

Issue date: 05/21/2015

**1. PRODUCT AND COMPANY IDENTIFICATION**

<b>Product name:</b>	<b>LOCTITE LB 8108 SYN GREASE known as LB 8108 SYN GREASE H</b>	<b>IDH number:</b>	1906102
<b>Product type:</b>	Lubricant	<b>Item number:</b>	1906102
<b>Restriction of Use:</b>	None identified	<b>Region:</b>	United States
<b>Company address:</b>	Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067	<b>Contact information:</b>	Telephone: (860) 571-5100 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887 Internet: www.henkelna.com

**2. HAZARDS IDENTIFICATION**

**EMERGENCY OVERVIEW**

**DANGER:** CONTENTS UNDER PRESSURE.  
EXTREMELY FLAMMABLE AEROSOL.  
MAY BE FATAL IF SWALLOWED AND ENTERS AIRWAYS.  
CAUSES SKIN IRRITATION.  
CAUSES SERIOUS EYE IRRITATION.  
MAY CAUSE DROWSINESS OR DIZZINESS.

HAZARD CLASS	HAZARD CATEGORY
FLAMMABLE AEROSOL	1
SKIN IRRITATION	2
EYE IRRITATION	2A
SPECIFIC TARGET ORGAN TOXICITY - SINGLE EXPOSURE	3
ASPIRATION HAZARD	1

**PICTOGRAM(S)**



**Precautionary Statements**

<b>Prevention:</b>	Keep away from heat, sparks, open flames, hot surfaces - no smoking. Do not spray on an open flame or other ignition source. Do not pierce or burn, even after use. Avoid breathing mist or spray. Wash thoroughly after handling. Use only outdoors or in a well-ventilated area. Wear eye and face protection. Wear protective gloves.
<b>Response:</b>	IF SWALLOWED: Immediately call a physician or poison control center. IF ON SKIN: Wash with plenty of water. IF INHALED: Remove person to fresh air and keep comfortable for breathing. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to remove. Continue rinsing. Call a poison control center or physician if you feel unwell. Do NOT induce vomiting. If skin irritation occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.
<b>Storage:</b>	Store in a well-ventilated place. Keep container tightly closed. Store locked up. Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
<b>Disposal:</b>	Dispose of contents and/or container according to Federal, State/Provincial and local

governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

### 3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Acetone	67-64-1	10 - 30
n-Heptane	142-82-5	10 - 30
Propane	74-98-6	5 - 10
Distillates (petroleum), straight-run middle	64741-44-2	5 - 10
n-Butane, containing $\geq 0,1$ % butadiene	106-97-8	1 - 5

\* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

### 4. FIRST AID MEASURES

<b>Inhalation:</b>	Move to fresh air. If breathing is difficult, give oxygen. If not breathing, give artificial respiration. If symptoms develop and persist, get medical attention.
<b>Skin contact:</b>	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. If symptoms develop and persist, get medical attention. Wash clothing before reuse. Thoroughly clean shoes before reuse.
<b>Eye contact:</b>	Immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
<b>Ingestion:</b>	Do not induce vomiting: contains petroleum distillates and/or aromatic solvents. Never give anything by mouth to an unconscious person. If vomiting occurs, prevent aspiration by keeping the patient's head below the knees. Get medical attention.
<b>Symptoms:</b>	See Section 11.

### 5. FIRE FIGHTING MEASURES

<b>Extinguishing media:</b>	Foam, dry chemical or carbon dioxide.
<b>Special firefighting procedures:</b>	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.
<b>Unusual fire or explosion hazards:</b>	Contents under pressure. Vapors may form explosive mixtures with air. Closed containers may rupture (due to build up of pressure) when exposed to extreme heat. In case of fire, keep containers cool with water spray. Do not puncture or incinerate pressurized containers. Do not handle or store near an open flame, heat or other sources of ignition. Hydrocarbon solvents are basically non-conductors of electricity and can become electrostatically charged during mixing, filtering or pumping at high flow rates. If this charge reaches a significantly high level, sparks can form that may ignite vapors of flammable liquids.

Hazardous combustion products: Oxides of carbon.

## 6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

**Environmental precautions:** Do not allow product to enter sewer or waterways. Advise authorities if product has entered or may enter sewers, water sources or extensive land areas. This product is insoluble in water and will float on surface.

**Clean-up methods:** Remove all sources of ignition. Ensure adequate ventilation. Wear appropriate personal protective equipment. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Store in a partly filled, closed container until disposal.

## 7. HANDLING AND STORAGE

**Handling:** Keep away from heat, spark and flame. During use and until all vapors are gone: Keep area ventilated - do not smoke; extinguish all flames, pilot lights, and heaters; turn off stoves, electrical tools and appliances, and any other sources of ignition. Do not puncture or incinerate pressurized containers. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Do not taste or swallow. Use only with adequate ventilation.

**Storage:** For safe storage, store between -20 °C (-4°F) and 50 °C (122°F) Keep in a cool, well ventilated area. Keep away from heat, spark and flame. Do not puncture, incinerate, or expose to temperatures above 48.9 °C (120 °F). Protect from direct sunlight.

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Acetone	750 ppm STEL 500 ppm TWA	1,000 ppm (2,400 mg/m3) PEL	None	None
n-Heptane	400 ppm TWA 500 ppm STEL	500 ppm (2,000 mg/m3) PEL	None	None
Propane	Included in the regulation but with no data values. See regulation for further details	1,000 ppm (1,800 mg/m3) PEL	None	None
Distillates (petroleum), straight-run middle	5 mg/m3 TWA mist 10 mg/m3 STEL mist	5 mg/m3 TWA mist	None	None
n-Butane, containing >= 0,1 % butadiene	1,000 ppm STEL	None	None	None

**Engineering controls:** Use explosion-proof mechanical ventilation and local exhaust to control contaminants to within their occupational exposure limits during the use of this product.

**Respiratory protection:** Use a NIOSH approved air-purifying respirator with an organic vapor cartridge.

**Eye/face protection:** Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists.

**Skin protection:** Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Physical state:</b>	Aerosol
<b>Color:</b>	White to tan
<b>Odor:</b>	Solvent
<b>Odor threshold:</b>	Not available.
<b>pH:</b>	Not available.
<b>Vapor pressure:</b>	Not available.
<b>Boiling point/range:</b>	-18 - 100 °C (0.4 - 212°F)
<b>Melting point/ range:</b>	Not available.
<b>Specific gravity:</b>	0.910
<b>Specific gravity:</b>	0.72
<b>Vapor density:</b>	Not available.
<b>Flash point:</b>	< -17.8 °C (< 0.04 °F)
<b>Flammable/Explosive limits - lower:</b>	Not available.
<b>Flammable/Explosive limits - upper:</b>	Not available.
<b>Autoignition temperature:</b>	Not available.
<b>Evaporation rate:</b>	Not available.
<b>Solubility in water:</b>	Not available.
<b>Partition coefficient (n-octanol/water):</b>	Not available.
<b>VOC content:</b>	32 %
<b>Viscosity:</b>	Not available.
<b>Decomposition temperature:</b>	Not available.

## 10. STABILITY AND REACTIVITY

<b>Stability:</b>	Stable under normal conditions of storage and use.
<b>Hazardous reactions:</b>	None under normal processing.
<b>Hazardous decomposition products:</b>	Oxides of carbon.
<b>Incompatible materials:</b>	Oxidizing agents.
<b>Reactivity:</b>	Not available.
<b>Conditions to avoid:</b>	Keep away from heat, ignition sources and incompatible materials. Vapors may form explosive mixtures with air. Do not puncture, incinerate, or expose to temperatures above 48.9 °C (120 °F). Protect from direct sunlight.

## 11. TOXICOLOGICAL INFORMATION

<b>Relevant routes of exposure:</b>	Skin, Inhalation, Eyes, Ingestion
-------------------------------------	-----------------------------------

### Potential Health Effects/Symptoms

**Inhalation:** Causes respiratory tract irritation. May cause central nervous system effects with nausea, dizziness and headache. Extreme overexposure may result in unconsciousness and possibly death.

**Skin contact:** Causes skin irritation.

**Eye contact:** Causes serious eye irritation.

**Ingestion:** Ingestion of larger amounts may cause defects to the central nervous system (e.g. dizziness, headache). Aspiration may occur during swallowing or vomiting, resulting in lung damage.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Acetone	Oral LD50 (RABBIT) = 5,340 mg/kg Oral LD50 (RAT) = 5,800 mg/kg Oral LD50 (RAT) = 9,800 mg/kg Dermal LD50 (RABBIT) = 20,000 mg/kg Inhalation LC50 (RAT, 8 h) = 50.1 mg/l Inhalation LC50 (RAT, 4 h) = 76 mg/l	Blood, Central nervous system, Irritant, Reproductive
n-Heptane	Inhalation LC50 (RAT, 4 h) = 103 mg/l	Central nervous system, Irritant
Propane	Inhalation LC50 (RAT, 15 min) = > 1,442.847 mg/l Inhalation LC50 (RAT, 15 min) = > 1,464 mg/l	Cardiac, Central nervous system, Irritant
Distillates (petroleum), straight-run middle	None	Irritant
n-Butane, containing >= 0,1 % butadiene	Inhalation LC50 (RAT, 4 h) = 658 mg/l	Cardiac, Central nervous system, Irritant

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Acetone	No	No	No
n-Heptane	No	No	No
Propane	No	No	No
Distillates (petroleum), straight-run middle	No	No	No
n-Butane, containing >= 0,1 % butadiene	No	No	No

## 12. ECOLOGICAL INFORMATION

**Ecological information:** Not available.

## 13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

**Recommended method of disposal:** Follow all local, state, federal and provincial regulations for disposal. Do not puncture or incinerate pressurized containers.

**Hazardous waste number:** D001: Ignitable.

## 14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

### U.S. Department of Transportation Ground (49 CFR)

**Proper shipping name:** Aerosols, flammable  
**Hazard class or division:** 2.1  
**Identification number:** UN 1950  
**Packing group:** None  
**DOT Hazardous Substance(s):** Acetone

**International Air Transportation (ICAO/IATA)**

**Proper shipping name:** Aerosols, flammable  
**Hazard class or division:** 2.1  
**Identification number:** UN 1950  
**Packing group:** None

**Water Transportation (IMO/IMDG)**

**Proper shipping name:** AEROSOLS (n-Heptane)  
**Hazard class or division:** 2.1  
**Identification number:** UN 1950  
**Packing group:** None  
**Marine pollutant:** n-Heptane

**15. REGULATORY INFORMATION****United States Regulatory Information**

**TSCA 8 (b) Inventory Status:** All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.  
**TSCA 12 (b) Export Notification:** None above reporting de minimis  
**CERCLA/SARA Section 302 EHS:** None above reporting de minimis  
**CERCLA/SARA Section 311/312:** Fire, Pressure, Immediate Health, Delayed Health  
**CERCLA/SARA Section 313:** None above reporting de minimis  
**California Proposition 65:** No California Proposition 65 listed chemicals are known to be present.

**Canada Regulatory Information**

**CEPA DSL/NDL Status:** All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

**16. OTHER INFORMATION**

**This safety data sheet contains changes from the previous version in sections:** New Safety Data Sheet format.

**Prepared by:** Catherine Bimler, Regulatory Affairs Specialist

**Issue date:** 05/21/2015

**DISCLAIMER:** The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.