



Revision Number: 001.3

Issue date: 09/11/2014

**1. PRODUCT AND COMPANY IDENTIFICATION**

<b>Product name:</b>	<b>LOCTITE LB 8023 TB70ZENFRES</b>	<b>IDH number:</b>	1999556
<b>Product type:</b>	Lubricant	<b>Item number:</b>	1999556
<b>Restriction of Use:</b>	None identified	<b>Region:</b>	United States
<b>Company address:</b>	<b>Contact information:</b>		
Henkel Corporation	Telephone: (860) 571-5100		
One Henkel Way	MEDICAL EMERGENCY Phone: Poison Control Center		
Rocky Hill, Connecticut 06067	1-877-671-4608 (toll free) or 1-303-592-1711		
	TRANSPORT EMERGENCY Phone: CHEMTREC		
	1-800-424-9300 (toll free) or 1-703-527-3887		
	Internet: www.henkelna.com		

**2. HAZARDS IDENTIFICATION**

**EMERGENCY OVERVIEW**

**DANGER:** CAUSES SEVERE SKIN BURNS AND EYE DAMAGE.

HAZARD CLASS	HAZARD CATEGORY
SKIN CORROSION	1C
SERIOUS EYE DAMAGE	1

**PICTOGRAM(S)**



**Precautionary Statements**

<b>Prevention:</b>	Do not breathe vapors, mist, or spray. Wash thoroughly after handling. Wear protective gloves, eye protection, and face protection.
<b>Response:</b>	IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. If on skin (or hair): Take off immediately all contaminated clothing. IF INHALED: Remove person to fresh air and keep comfortable for breathing. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to remove. Continue rinsing. Immediately call a poison control center or physician. Wash contaminated clothing before reuse.
<b>Storage:</b>	Store locked up.
<b>Disposal:</b>	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

**3. COMPOSITION / INFORMATION ON INGREDIENTS**

Hazardous Component(s)	CAS Number	Percentage*
Petroleum Based grease	Unknown	30 - 60
Calcium oxide	1305-78-8	10 - 30

Graphite	7782-42-5	10 - 30
Petroleum distillates, hydrotreated, light naphthenic	64742-53-6	5 - 10
Distillates (petroleum), hydrotreated heavy naphthenic	64742-52-5	5 - 10
Octadecanoic acid	57-11-4	0.1 - 1
Boron oxide (B <sub>2</sub> O <sub>3</sub> )	1303-86-2	0.1 - 1

\* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

#### 4. FIRST AID MEASURES

<b>Inhalation:</b>	Move to fresh air. If symptoms develop and persist, get medical attention.
<b>Skin contact:</b>	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. If symptoms develop and persist, get medical attention. Wash clothing before reuse.
<b>Eye contact:</b>	Get medical attention. Immediately flush eyes with plenty of water for at least 15 minutes.
<b>Ingestion:</b>	Get medical attention. Keep individual calm. Do not induce vomiting: contains petroleum distillates and/or aromatic solvents.
<b>Symptoms:</b>	See Section 11.

#### 5. FIRE FIGHTING MEASURES

<b>Extinguishing media:</b>	Water spray (fog), foam, dry chemical or carbon dioxide.
<b>Special firefighting procedures:</b>	Wear a self-contained breathing apparatus with a full face piece operated in pressure-demand or other positive pressure mode. In case of fire, keep containers cool with water spray.
<b>Unusual fire or explosion hazards:</b>	None
<b>Hazardous combustion products:</b>	Oxides of nitrogen. Oxides of carbon.

#### 6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

<b>Environmental precautions:</b>	Do not allow product to enter sewer or waterways.
<b>Clean-up methods:</b>	Scrape up as much material as possible. Clean residue with soap and water. Store in a partly filled, closed container until disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

#### 7. HANDLING AND STORAGE

<b>Handling:</b>	Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Keep container closed.
<b>Storage:</b>	Keep container closed. Keep in a cool, well ventilated area.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Petroleum Based grease	5 mg/m3 TWA mist	5 mg/m3 TWA mist	None	None
Calcium oxide	2 mg/m3 TWA	5 mg/m3 PEL	None	None
Graphite	2 mg/m3 TWA Respirable fraction.	5 mg/m3 PEL Respirable fraction. 15 mg/m3 PEL Total dust. 15 MPPCF TWA	None	None
Petroleum distillates, hydrotreated, light naphthenic	None	500 ppm (2,000 mg/m3) PEL 5 mg/m3 PEL Mist.	None	None
Distillates (petroleum), hydrotreated heavy naphthenic	5 mg/m3 TWA mist 10 mg/m3 STEL mist	5 mg/m3 TWA mist 500 ppm (2,000 mg/m3) PEL 5 mg/m3 PEL Mist.	None	None
Octadecanoic acid	10 mg/m3 TWA	None	None	None
Boron oxide (B2O3)	10 mg/m3 TWA	15 mg/m3 PEL Total dust.	None	None

<b>Engineering controls:</b>	Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.
<b>Respiratory protection:</b>	Observe OSHA regulations for respirator use (29 CFR 1910.134). Use NIOSH approved respirator if there is potential to exceed exposure limit(s).
<b>Eye/face protection:</b>	Safety goggles or safety glasses with side shields. Safety showers and eye wash stations should be available.
<b>Skin protection:</b>	Use impermeable gloves and protective clothing as necessary to prevent skin contact.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Physical state:</b>	Paste
<b>Color:</b>	Black
<b>Odor:</b>	Mild
<b>Odor threshold:</b>	Not available.
<b>pH:</b>	Not available.
<b>Vapor pressure:</b>	Not available.
<b>Boiling point/range:</b>	Not available.
<b>Melting point/ range:</b>	Not available.
<b>Specific gravity:</b>	1.2648
<b>Vapor density:</b>	Not available.
<b>Flash point:</b>	Not applicable
<b>Flammable/Explosive limits - lower:</b>	Not available.
<b>Flammable/Explosive limits - upper:</b>	Not available.
<b>Autoignition temperature:</b>	Not available.
<b>Evaporation rate:</b>	Not available.
<b>Solubility in water:</b>	Insoluble
<b>Partition coefficient (n-octanol/water):</b>	Not available.
<b>VOC content:</b>	< 3 %; 38.4 g/l EPA Method 24
<b>Viscosity:</b>	Not available.
<b>Decomposition temperature:</b>	Not available.

## 10. STABILITY AND REACTIVITY

<b>Stability:</b>	Stable under normal conditions of storage and use.
<b>Hazardous reactions:</b>	Will not occur.
<b>Hazardous decomposition products:</b>	Oxides of carbon. Oxides of nitrogen.
<b>Incompatible materials:</b>	Strong acids and strong bases. Strong oxidizing agents. Strong reducing agents.
<b>Reactivity:</b>	Not available.
<b>Conditions to avoid:</b>	Keep away from heat, ignition sources and incompatible materials.

## 11. TOXICOLOGICAL INFORMATION

**Relevant routes of exposure:** Skin, Inhalation, Eyes

**Potential Health Effects/Symptoms**

<b>Inhalation:</b>	Not a hazard under normal conditions of use.
<b>Skin contact:</b>	Causes skin burns.
<b>Eye contact:</b>	Causes serious eye damage.
<b>Ingestion:</b>	Principal hazard of ingestion is aspiration into the lungs and subsequent pneumonitis.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Petroleum Based grease	None	No Data
Calcium oxide	None	Irritant, Corrosive, Eyes
Graphite	None	Lung
Petroleum distillates, hydrotreated, light naphthenic	None	Irritant
Distillates (petroleum), hydrotreated heavy naphthenic	None	Irritant
Octadecanoic acid	Oral LD50 (RAT) = 4.6 g/kg	Irritant
Boron oxide (B2O3)	None	Blood, Central nervous system, Gastrointestinal, Irritant, Kidney, Liver, Lung, Metabolic, Nuisance dust, Skin, Vascular

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Petroleum Based grease	No	No	No
Calcium oxide	No	No	No
Graphite	No	No	No
Petroleum distillates, hydrotreated, light naphthenic	No	No	No
Distillates (petroleum), hydrotreated heavy naphthenic	No	No	No
Octadecanoic acid	No	No	No
Boron oxide (B2O3)	No	No	No

## 12. ECOLOGICAL INFORMATION

**Ecological information:** Not available.

### 13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

**Recommended method of disposal:** Follow all local, state, federal and provincial regulations for disposal.  
**Hazardous waste number:** Not a RCRA hazardous waste.

### 14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

#### U.S. Department of Transportation Ground (49 CFR)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

#### International Air Transportation (ICAO/IATA)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

#### Water Transportation (IMO/IMDG)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

### 15. REGULATORY INFORMATION

#### United States Regulatory Information

**TSCA 8 (b) Inventory Status:** All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.  
**TSCA 12 (b) Export Notification:** None above reporting de minimis  
**CERCLA/SARA Section 302 EHS:** None above reporting de minimis  
**CERCLA/SARA Section 311/312:** Immediate Health, Delayed Health  
**CERCLA/SARA Section 313:** None above reporting de minimis  
**California Proposition 65:** No California Proposition 65 listed chemicals are known to be present.

#### Canada Regulatory Information

**CEPA DSL/NDL Status:** All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

### 16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

**Prepared by:** Lou Fabrizio, Regulatory Affairs Specialist  
**Issue date:** 09/11/2014

**DISCLAIMER:** The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.