



Revision Number: 006.3

Issue date: 03/16/2017

**1. PRODUCT AND COMPANY IDENTIFICATION**

<b>Product name:</b>	<b>LOCTITE SI 5900 INSTANT GASKET MAKER known as 5900 Flange Sealant</b>	<b>IDH number:</b>	212184
<b>Product type:</b>	Silicone	<b>Item number:</b>	20166
<b>Restriction of Use:</b>	None identified	<b>Region:</b>	United States
<b>Company address:</b>	Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067	<b>Contact information:</b>	Telephone: (860) 571-5100 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887 Internet: www.henkelna.com

**2. HAZARDS IDENTIFICATION**

**EMERGENCY OVERVIEW**

**WARNING:** CAUSES SKIN IRRITATION.  
MAY CAUSE AN ALLERGIC SKIN REACTION.  
CAUSES SERIOUS EYE IRRITATION.

HAZARD CLASS	HAZARD CATEGORY
SKIN IRRITATION	2
EYE IRRITATION	2A
SKIN SENSITIZATION	1

**PICTOGRAM(S)**



**Precautionary Statements**

<b>Prevention:</b>	Avoid breathing dust or fumes. Wash affected area thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves, eye protection, and face protection.
<b>Response:</b>	IF ON SKIN: Wash with plenty of water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If skin irritation or rash occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.
<b>Storage:</b>	Not prescribed
<b>Disposal:</b>	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

**3. COMPOSITION / INFORMATION ON INGREDIENTS**

Hazardous Component(s)	CAS Number	Percentage*
Calcium carbonate	471-34-1	40 - 50
Siloxanes and Silicones, di-Me	63148-62-9	10 - 20
Butan-2-one O,O',O"- (vinylsilyldiyne)trioxime	2224-33-1	1 - 5
Carbon black	1333-86-4	1 - 5
Aluminum	7429-90-5	0.1 - 1
Butan-2-one O,O',O",O'''- silanetetrayltetraoxime	34206-40-1	0.1 - 1

\* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

Methyl ethyl ketoxime is formed during cure.

#### 4. FIRST AID MEASURES

<b>Inhalation:</b>	Move to fresh air in case of accidental inhalation of vapours or decomposition products. If symptoms develop and persist, get medical attention.
<b>Skin contact:</b>	Wipe off paste with paper towel or cloth. Wash with soap and water. If skin irritation persists, call a physician.
<b>Eye contact:</b>	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
<b>Ingestion:</b>	Do not induce vomiting. Get medical attention.
<b>Symptoms:</b>	See Section 11.

#### 5. FIRE FIGHTING MEASURES

<b>Extinguishing media:</b>	Foam, dry chemical or carbon dioxide.
<b>Special firefighting procedures:</b>	Wear self contained breathing apparatus. Prevent inhalation of fumes and gases.
<b>Unusual fire or explosion hazards:</b>	None
<b>Hazardous combustion products:</b>	Oxides of carbon. Oxides of silicon. Formaldehyde. Irritating organic vapours.

#### 6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

<b>Environmental precautions:</b>	Do not allow product to enter sewer or waterways.
<b>Clean-up methods:</b>	Scrape up as much material as possible. Maintain good ventilation for large spills. Place scrap material in a well ventilated area and allow to cure to rubber.

## 7. HANDLING AND STORAGE

**Handling:** Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Do not handle contact lenses until all sealant has been removed from hands. Residual sealant may transfer to lenses and cause eye irritation. Do not wear contact lenses.

**Storage:** Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

For information on product shelf life, please review labels on container or check the Technical Data Sheet.

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Calcium carbonate	10 mg/m <sup>3</sup> TWA Total dust.	5 mg/m <sup>3</sup> PEL Respirable fraction. 15 mg/m <sup>3</sup> PEL Total dust.	None	None
Siloxanes and Silicones, di-Me	None	None	None	None
Butan-2-one O,O',O''-(vinylsilylydyne)trioxime	None	None	None	None
Carbon black	3 mg/m <sup>3</sup> TWA Inhalable fraction.	3.5 mg/m <sup>3</sup> PEL	None	None
Aluminum	1 mg/m <sup>3</sup> TWA Respirable fraction.	15 mg/m <sup>3</sup> PEL (as Al) Total dust. 5 mg/m <sup>3</sup> PEL (as Al) Respirable fraction. 15 MPPCF TWA Respirable fraction. 50 MPPCF TWA Total dust. 5 mg/m <sup>3</sup> TWA Respirable fraction. 15 mg/m <sup>3</sup> TWA Total dust.	None	None
Butan-2-one O,O',O'',O'''-silanetetrayltetraoxime	None	None	None	None

**Engineering controls:** Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.

**Respiratory protection:** Use a dust mask for particulate concentrations exceeding the Occupational Exposure Limit. Use an organic vapor respirator for concentrations exceeding the Occupational Exposure Limit.

**Eye/face protection:** Safety goggles or safety glasses with side shields. Safety showers and eye wash stations should be available.

**Skin protection:** Permeation resistant gloves (butyl rubber, nitrile rubber, polyvinyl alcohol).

## 9. PHYSICAL AND CHEMICAL PROPERTIES

<b>Physical state:</b>	Paste
<b>Color:</b>	Black
<b>Odor:</b>	Mild
<b>Odor threshold:</b>	Not available.
<b>pH:</b>	Not applicable
<b>Vapor pressure:</b>	< 5 mm hg (20 °C (68°F))
<b>Boiling point/range:</b>	Not applicable
<b>Melting point/ range:</b>	Not available.

<b>Specific gravity:</b>	1.31 at 20 °C (68°F)
<b>Vapor density:</b>	Heavier than air.
<b>Flash point:</b>	> 93 °C (> 199.4 °F) Tagliabue closed cup
<b>Flammable/Explosive limits - lower:</b>	Not applicable
<b>Flammable/Explosive limits - upper:</b>	Not applicable
<b>Autoignition temperature:</b>	Not available.
<b>Flammability:</b>	Not applicable
<b>Evaporation rate:</b>	Not available.
<b>Solubility in water:</b>	Polymerises in presence of water.
<b>Partition coefficient (n-octanol/water):</b>	Not available.
<b>VOC content:</b>	3.31 %; 44.47 g/l
<b>Viscosity:</b>	Not available.
<b>Decomposition temperature:</b>	Not available.

## 10. STABILITY AND REACTIVITY

<b>Stability:</b>	Stable under normal conditions of storage and use.
<b>Hazardous reactions:</b>	None under normal processing.
<b>Hazardous decomposition products:</b>	Methyl ethyl ketoxime formed during cure. Oxides of carbon. Oxides of silicon. Formaldehyde.
<b>Incompatible materials:</b>	Acids and bases. Oxidizing agents. Polymerizes on contact with water.
<b>Reactivity:</b>	Not available.
<b>Conditions to avoid:</b>	Excessive heat. Store away from incompatible materials.

## 11. TOXICOLOGICAL INFORMATION

<b>Relevant routes of exposure:</b>	Skin, Inhalation, Eyes, Ingestion
-------------------------------------	-----------------------------------

### Potential Health Effects/Symptoms

**Inhalation:** May cause respiratory tract irritation. When heated to temperatures exceeding 300° F (150° C) in the presence of air, silicones may form formaldehyde vapors. Formaldehyde is a potential cancer hazard and a known skin and respiratory sensitizer. Vapors irritate the eyes, nose and throat. Safe handling conditions may be maintained by keeping formaldehyde vapor concentrations below the OSHA permissible limit.

**Skin contact:** Causes skin irritation. May cause allergic skin reaction.

**Eye contact:** Causes serious eye irritation.

**Ingestion:** Not expected under normal conditions of use. May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Calcium carbonate	Oral LD50 (Rat) = 6,450 mg/kg Oral LD50 (Mouse) = 6,450 mg/kg	Nuisance dust
Siloxanes and Silicones, di-Me	None	Irritant
Butan-2-one O,O',O''-(vinylsilylidyne)trioxime	None	Irritant, Allergen
Carbon black	Oral LD50 (Rat) = > 8,000 mg/kg	Respiratory, Some evidence of carcinogenicity
Aluminum	None	Central nervous system, Irritant, Lung
Butan-2-one O,O',O'',O'''-silanetetrayltetraoxime	None	Irritant, Allergen

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Calcium carbonate	No	No	No
Siloxanes and Silicones, di-Me	No	No	No
Butan-2-one O,O',O''-(vinylsilylidyne)trioxime	No	No	No
Carbon black	No	Group 2B	No
Aluminum	No	No	No
Butan-2-one O,O',O'',O'''-silanetetrayltetraoxime	No	No	No

## 12. ECOLOGICAL INFORMATION

**Ecological information:** Not available.

## 13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

**Recommended method of disposal:** Follow all local, state, federal and provincial regulations for disposal. Cured rubber can be incinerated or landfilled following EPA and local regulations.

**Hazardous waste number:** Not a RCRA hazardous waste.

## 14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

### U.S. Department of Transportation Ground (49 CFR)

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

**International Air Transportation (ICAO/IATA)**

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None

**Water Transportation (IMO/IMDG)**

**Proper shipping name:** Not regulated  
**Hazard class or division:** None  
**Identification number:** None  
**Packing group:** None  
**Exceptions:** None

**15. REGULATORY INFORMATION****United States Regulatory Information**

**TSCA 8 (b) Inventory Status:** All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.

**TSCA 12 (b) Export Notification:** None above reporting de minimis

**CERCLA/SARA Section 302 EHS:** None above reporting de minimis.

**CERCLA/SARA Section 311/312:** Immediate Health, Delayed Health

**CERCLA/SARA Section 313:** None above reporting de minimis.

**California Proposition 65:** This product contains a chemical known to the State of California to cause birth defects or other reproductive harm. This product contains a chemical known in the State of California to cause cancer.

**Canada Regulatory Information**

**CEPA DSL/NDL Status:** All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

**16. OTHER INFORMATION**

**This safety data sheet contains changes from the previous version in sections: 3**

**Prepared by:** Rebecca Coons, Regulatory Affairs Specialist

**Issue date:** 03/16/2017

**DISCLAIMER:** The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.