



Revision Number: 004.0

Issue date: 02/21/2017

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	Super Lube(R) Synthetic-Based Lubricant with PTFE	IDH number:	209807
Product type:	Lubricant	Item number:	82328
Restriction of Use:	None identified	Region:	United States
Company address:	Contact information:		
Henkel Corporation	Telephone: (860) 571-5100		
One Henkel Way	MEDICAL EMERGENCY Phone: Poison Control Center		
Rocky Hill, Connecticut 06067	1-877-671-4608 (toll free) or 1-303-592-1711		
	TRANSPORT EMERGENCY Phone: CHEMTREC		
	1-800-424-9300 (toll free) or 1-703-527-3887		
	Internet: www.henkelna.com		

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

NOT CLASSIFIED. READ ENTIRE SAFETY DATA SHEET.

HAZARD CLASS	HAZARD CATEGORY
None	None

PICTOGRAM(S)
None

Precautionary Statements

Prevention:	Not prescribed
Response:	Not prescribed
Storage:	Not prescribed
Disposal:	Not prescribed

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
1-Decene, homopolymer, hydrogenated	68037-01-4	70 - 80
White mineral oil (petroleum), highly refined	8042-47-5	10 - 20
Ethene, tetrafluoro-, homopolymer	9002-84-0	1 - 5

* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.
Skin contact:	Remove contaminated clothing and footwear. Wash with soap and water. If symptoms develop and persist, get medical attention. Wash clothing before reuse.
Eye contact:	Immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Ingestion:	Do not induce vomiting. Keep individual calm. Never give anything by mouth to an unconscious person. Get medical attention.
Symptoms:	See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Water spray (fog), foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. In case of fire, keep containers cool with water spray.
Unusual fire or explosion hazards:	Closed containers may rupture (due to build up of pressure) when exposed to extreme heat.
Hazardous combustion products:	Oxides of carbon. Toxic fluorine compounds. Toxic and irritating vapors.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Ensure adequate ventilation. Remove all sources of ignition. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Remove the absorbed material, and place in an appropriate chemical waste container for disposal.

7. HANDLING AND STORAGE

Handling:	Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Vapors will accumulate readily and may ignite explosively. Refer to Section 8.
Storage:	Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

For information on product shelf life, please review labels on container or check the Technical Data Sheet.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
1-Decene, homopolymer, hydrogenated	5 mg/m3 TWA mist 10 mg/m3 STEL mist	5 mg/m3 TWA mist	None	None
White mineral oil (petroleum), highly refined	5 mg/m3 TWA Inhalable fraction.	5 mg/m3 TWA mist 5 mg/m3 PEL Mist.	None	None
Ethene, tetrafluoro-, homopolymer	None	None	None	10 mg/m3 TWA Total dust. 5 mg/m3 TWA Respirable fraction.

Engineering controls:

Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits. In case of insufficient ventilation, wear suitable respiratory equipment.

Respiratory protection:

Use NIOSH approved respirator if there is potential to exceed exposure limit(s).

Eye/face protection:

Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.

Skin protection:

Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Paste
Color:	White
Odor:	None
Odor threshold:	Not available.
pH:	Not available.
Vapor pressure:	Not available.
Boiling point/range:	Not available.
Melting point/ range:	Not available.
Vapor density:	Not available.
Flash point:	> 93 °C (> 199.4 °F) Tagliabue closed cup
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not available.
Flammability:	Not applicable
Evaporation rate:	Not available.
Solubility in water:	Not available.
Partition coefficient (n-octanol/water):	Not available.
VOC content:	66.56 % EPA Method 24
Viscosity:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	None under normal processing.
Hazardous decomposition products:	Oxides of carbon. Toxic fluorine compounds. Irritating organic fragments.
Incompatible materials:	Strong oxidizing agents. Acids and bases.
Reactivity:	Not available.
Conditions to avoid:	Keep away from heat, ignition sources and incompatible materials. Store away from incompatible materials.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure: Skin, Inhalation, Eyes, Ingestion

Potential Health Effects/Symptoms

Inhalation:	May cause respiratory tract irritation.
Skin contact:	May cause skin irritation.
Eye contact:	May cause eye irritation.
Ingestion:	Not a likely route of entry. May be harmful if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
1-Decene, homopolymer, hydrogenated	None	No Target Organs
White mineral oil (petroleum), highly refined	None	Irritant
Ethene, tetrafluoro-, homopolymer	None	No Target Organs

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
1-Decene, homopolymer, hydrogenated	No	No	No
White mineral oil (petroleum), highly refined	No	No	No
Ethene, tetrafluoro-, homopolymer	No	No	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/IMDG)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification: Ethene, tetrafluoro-, homopolymer (CAS# 9002-84-0).
CERCLA/SARA Section 302 EHS: None above reporting de minimis.
CERCLA/SARA Section 311/312: Immediate Health
CERCLA/SARA Section 313: None above reporting de minimis.
California Proposition 65: No California Proposition 65 listed chemicals are known to be present.

Canada Regulatory Information

CEPA DSL/NDL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

Prepared by: Timothy Pratt, Regulatory Affairs Specialist

Issue date: 02/21/2017

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.