



LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

ANSI Type K & T Exposed Welded Tip Thermocouples with Miniature Thermocouple Plug



About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

- Thermocouple types K & T to ANSI MC96.1
- Fast response, welded exposed junction
- 5 or 10-metre-long Teflon® PFA insulated twin-twisted lead
- Durable construction with choice of conductor size, 1/0.2 or 1/0.3mm solid
- Class 1 cable specification in accordance with BS EN 60584-3:2008
- Tolerance to ANSI MC96.1 Class 1
- Miniature plug termination
- Temperature range -75°C to $+250^{\circ}\text{C}$
- Ideal for test & development applications

Thermocouple type	+/- Colour	Conductors	Length	order code
Type K	+ Yellow / - Red	1/0.2	5m	XF-1165-FAR
Type K	+ Yellow / - Red	1/0.2	10m	XF-1170-FAR
Type K	+ Yellow / - Red	1/0.3	5m	XF-1163-FAR
Type K	+ Yellow / - Red	1/0.3	10m	XF-1172-FAR
Type T	+ Blue / - Red	1/0.3	5m	XF-1166-FAR

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com