



ANSI High Temperature Glassfibre Twin Twisted Exposed Welded Tip Thermocouples with Standard Plug Termination



About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

- Thermocouple type K
- Fast response, welded exposed junction
- 5, 10 or 20-metre-long high temperature glassfibre insulated twisted cable
- Good temperature resistance (not suitable in fluids)
- 1/0.711mm conductors (21awg)
- Temperature range 0°C to +700°C
- Standard plug termination
- Tolerance to ANSI MC96.1 Class 2
- Colour code to ANSI MC96.1
- Ideal for test & development applications

T/C Type	Conductors	Length	+Positive tail wire	-Negative tail wire	order code
'K'	1/0.711mm	5 metres	Yellow	Red	XF-1196-FAR
'K'	1/0.711mm	10 metres	Yellow	Red	XF-1197-FAR
'K'	1/0.711mm	20 metres	Yellow	Red	XF-1198-FAR

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com