



Adjustable Bayonet Thermocouple Type K or J IEC With Cable Clamps and Terminating in Standard Plug



About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

- Thermocouple with adjustable insertion depth
- 6.0mm diameter tip
- 170mm spring with adjustable fixing cap (11.5mm I.D. single slot)
- Glassfibre insulated lead with stainless steel overbraid, 7/0.2mm
- Rated 350°C
- Fitted with cable clamps and standard thermocouple plug
- Good temperature resistance but not suitable where fluids are present
- Tolerance Class 2 to IEC-584
- Insulation rating -60°C to 350°C (short periods up to 400°C)
- Colour code (cores & jacket) to IEC-584-3
- Type J or K available

T/C Type	Conductors	Cores	Length	order code
K	7/0.2mm	+Green/-White	3 metres	XF-1190-FAR
J	7/0.2mm	+Green/-White	2 metres	XF-1191-FAR

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com