

## ACT20P

### ACT20P-CML-10-AO-RC-S

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 1429-0

Fax: +49 5231 14292083

www.weidmueller.com



#### ACT20P: The flexible solution

- Precise and highly functional signal converters
- Simple configuration via display (Pro DCDC II), FDT/DTM software or DIP switch
- Release levers simplify handling
- More space in the control cabinet, from 12.5 mm wide for two channels

#### General ordering data

Type	ACT20P-CML-10-AO-RC-S
Order No.	<a href="#">2044850000</a>
Version	Current-measuring transducer, Limit value monitoring, Signal converter/isolator, Current monitoring, Analogue output, Screw connection, Input measurement range: configurable, 0... 1/5/10 A AC (RMS) or DC
GTIN (EAN)	4050118409680
Qty.	1 pc(s).

**ACT20P**  
**ACT20P-CML-10-AO-RC-S**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	17.5 mm	Width (inches)	0.689 inch
Height	119.2 mm	Height (inches)	4.693 inch
Depth	113.6 mm	Depth (inches)	4.472 inch
Net weight	141 g		

**Temperatures**

Humidity	5...95 %, no condensation	Operating temperature	
Ambient temperature	-25 °C...+70 °C	Storage temperature	-40 °C...85 °C

**Probability of failure**

MTTF	130 Years
------	-----------

**Input**

Input signal	Power cable can be connected to the terminals	Input measurement range	configurable, 0...1/5/10 A AC (RMS) or DC
Input frequency	AC: 15...400 Hz (true root mean square), AC: 50 Hz (arithmetic average)		

**General data**

Accuracy	$\leq \pm 0.3 \% @ 1 \text{ A} / 5 \text{ A}, \leq \pm 0.6 \% @ 10 \text{ A}$	Configuration	DIP switch and potentiometer, for thresholds (overcurrent / undercurrent), delay and hysteresis
Galvanic isolation	4-way isolator, between input / output / supply / relay	Mounting rail	TS 35
Power consumption, max.	2.2 W	Step response time	$\leq 300 \text{ ms (RMS)}, \leq 60 \text{ ms (AA)}$
Supply voltage	24 V DC $\pm 30 \%$	Temperature coefficient	$\leq \pm 100 \text{ ppm/K @ } -25...+55 \text{ °C}, \leq \pm 200 \text{ ppm/K @ } +55...+70 \text{ °C}$

**Insulation coordination**

EMC standards	IEC 61326-1, IEC 61010-2-201	Galvanic isolation	4-way isolator, between input / output / supply / relay
Impulse withstand voltage	6 kV (1.2/50 $\mu\text{s}$ )	Pollution severity	2
Rated voltage	300 V AC <sub>rms</sub>	Standards	IEC 61010-1:2010, 3rd Edition, IEC 61010-2-201:2013, 1st Edition
Surge voltage category	III	Test voltage	4 kV

**Output (analogue)**

Load resistance current	$\leq 600 \Omega$	Load resistance voltage	$\geq 10 \text{ k}\Omega$
Output current	adjustable, 0...20 mA, 4...20 mA, -20...+20 mA	Output voltage	adjustable, 0...10 V, 2...10 V, 0...5 V, 1...5 V, -5...+5 V, -10...+10 V
Type (analogue output)	Voltage and current output (configurable)		

Creation date September 1, 2017 5:25:23 PM CEST

**Data sheet**

**ACT20P  
ACT20P-CML-10-AO-RC-S**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
www.weidmueller.com

**Technical data**

**Output (digital)**

Alarm function	Surge current, Under-current, Alarm delay: 0...10 s	Number of digital outputs	1
Type	Relay, 1 CO contact, normal / inverse adjustment	Max. switching voltage, DC	24 V
Max. switching voltage, AC	250 V	Rated switching current	2 A

**Connection data**

Type of connection	Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	1.5 mm <sup>2</sup>
Clamping range, rated connection, min.	0.5 mm <sup>2</sup>	Clamping range, rated connection, max.	2.5 mm <sup>2</sup>
Wire connection cross section AWG, min.	AWG 30	Wire connection cross section AWG, max.	AWG 14

**Classifications**

ETIM 6.0	EC002475	eClass 6.2	27-21-09-02
eClass 9.1	27-21-01-23		

**Approvals**

Approvals



ROHS Conform


**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">Declaration of Conformity</a>
Software	<a href="#">DIP switch configuration tool</a>
User Documentation	<a href="#">Instruction sheet</a>

**ACT20P  
ACT20P-CML-10-AO-RC-S**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

**Drawings**



**Connection diagram**

