


CABLE SPECIFICATION

SPEC NO. : RG59/U SIAMESE CCS COAXIAL CABLE

Customer No. 24-10291

Construction Item		Unit	Construction Item
Conductors	Construction	mm	1/0.81±0.05
	Material	---	CU
	Filler Material	---	---
	O. D.	mm	0.81±0.05
Insulators	Material	---	Foamed PE
	Diameter	mm	3.70±0.01
	Average Thickness	mm	1.44±0.05
	Colour	---	White
Outer Conductors	AL-PET Foil	um	AL-P-AL
	Type	---	Braid
	Material	---	ALMG
	Coverage	%	60%
	Diameter	mm	3.80±0.15
Jacket	Material	---	PVC (CM)
	Diameter	mm	6.9±0.15
	Average Thickness	mm	1.5±0.10
	Extrusion	---	---
	Surface	---	---
	Colour	---	White
Power Wire	Construction	mm	16*0.254CU
	Diameter	mm	3.2PVC
Inking	Inking Colour	---	Black
	Inking	---	Stellar Labs SIAMESE RG59/U TYPE COAX 75OHM 20AWG 75degC 2250MHz +2C18 E188601 (UL) CM RoHS COMPLIANT
Line	Length	ft	1000

CONFIGURATION:



GENERAL TOLERANCES
(UNLESS SPECIFIED)

LENGTH: X. ±1
.X ±0.2
.XX ±0.10
ANGLE: X° . ±1°
.X° ±0° 30'

Stellar Labs™

UNIT:mm	REV:		NAME	RG59/U SIAMESE COAXIAL CABLE
DRAWING	XIAOSHENG2008/10/07	S. P. NO.	DWG. NO.	
CHECK		P. O. NO.	PAGE	1/1
APPROVE		SIZE		