

## 1.COIL DATA

Nominal Voltage	12VDC
Nominal Power Consumption	360mW


## 2.CONTACT DATA

Contact Arrangement	1 Form A , 1 Form C
Contact Material	AgCdo
Contact Rating	10A 120VAC / 24 VDC (1C) 15A 120VAC / 24 VDC (1A)
Max. Switching Voltage	110 VDC / 240 VAC
Max. Switching Current	15A
Max. Switching Power	1800 VA , 360W
Contact Resistance ( Initial )	50Ω at 6VDC, 1A
Life Expectancy	Electrical 100,000 operations at nominal load Mechanical 10,000,000 operations

## 3. GENERAL DATA

Insulation Resistance	Min.100MΩ, at 500 VDC
Dielectric Strength	750VAC , 1min between open contacts 1,500VAC , 1min between contacts and coil
Operate Time	Max. 8ms
Release Time	Max. 5ms
Temperature Range	-30 to +85 °C
Shock Resistance	10G
Vibration Resistance	10 - 55 Hz , Amplitude 1.5mm
Weight	10 gr.
Safety Standard	UL NO. E164730


#### 4. DIMENSIONS (mm)



#### 6. COIL DATA

ORDERING CODE	COIL NOMINAL VDC	COIL RESISTANCE +/- 10%	OPERATE VOLTAGE VDC	RELEASE VOLTAGE VDC	COIL NOMINAL mW
26-542	12	400Ω	9.00	1.20	360
26-543	12	400Ω	9.00	1.20	360

## 7. CHARACTERISTIC DATA



ii

