


TEST CONDITION: CONDUCTOR IMPEDANCE: 10 OHM
 INSULATION IMPESANCE: 5M OHM
 TEST VOLATAGE: 200V



P1	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	SHELL
P2	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	SHELL

MCM Electronics
 Part #83-0345
 www.mcmelectronics.com

Customer		Order	A0
Description	DB15P/M-DB15P/M		
Part No	83-0345		
Mapper	CHEN	CHECKED	
Unit	MM	Date	06.12.02

6	PYROCONDENSATION TUBE:F4- 1.0 BLACK	2PCS	12	
5	SCREW:4*24 BEIGE	4PCS		
4	INTER MOLD:PE	15g		
3	OUTER MOLD:PVC 45P BEIGE	40g		
2	CONNECTOR:HDB 15P(M) INNER CORE BLUE NICKEL	2PCS		
1	CABLE:NO UL 28AWG AL-FOIL 15C+1 OD:6.0MM BEIGE	1PCS	1810	OUTER15*15 INTER2*2
NO	Discription	Amount	Length	