

REVISION

REV.A/0

- 1.CABLE; (A)28AWG(7/0.12TC),NON-UI,NON-FOIL,2C+S,OD=3.0±0.2mm,BLACK COLOR,PVC JACKET. (B)28AWG(7/0.12TC),UL2919,AL+D+B,{[(28AWG*1C+D+AL)*3COAX+28AWG*5.5PAIR]},OD=9.0±0.2mm.BLACK WITH EMBOSS,PVC JACKET.
- 2. LENGTH: L.
- 3. CONNECTORS: HDB15M*2PCS(BLACK INSULATOR), Ø3.5 STEREO PLUG*2PCS(三段式)(SHELL NICKEL).
- 4. MOLD: MOLDING TYPE.
- 5. SCREW:四方模螺絲*4PCS.

DATE

2015.04.14

6. CONTACTS:

	HDB15P	1	6	2	7	3	8	4 14	5	12	10	13	11	15	9	64	
	HDB15P	1 RC	6 RG	2 BC	7 BG	3 cc	8	4 14 PAIR	5 P	12 ĂIR	10 P/	13 (IR	11 P	15 ĂIR	9	64 SHELL	
ø3.5 STEREO PLUG(P1)											64						
								ø3.	5 S	TEREC	PLU	JG(P2) [1	2	64	

DISCRIPTION

7. Test machine test condition. A.100% OPEN, SHORT&INTERMITANCE TEST. B.CONDUCTOR RESISTANCE: 3ohms MAX:

C.INSULATION RESISTANCE: 5M Min/,10ms: 8. ALL MUST BE MEET ON ROHS COMPLIANT. ITEM NO. COMPANY MRP NO B SVST-3MM

DRAWN

BY

DESIGNED BY **APPROVAL**

→ 40mm -		
(RoHS)		
Printing CTN(BLUE)	XOFT SVGA+3.5MM STEREO BLACK W/FERRITE CABLE	
20mm		►COLOR: BLACK (印刷不可掉色)
2.43	RodS	
RoHS	MADE IN CHINA	COLOR: BLACK (印刷不可據色)
	KFT SVGA+3.5MM STE	REO
(COLOR: BLACK) BI	_ACK W/FERRITE CAB	LE
	1PCS/PE BAG	

		SCALE	
SPEC	Stellar Labs Computer +	UNIT(mm)	
		PAGE	1/1