



Safety Data Sheet

1 - Identification

Trade Name: WD-40 Specialist® Dirt & Dust Resistant Dry Lube	Manufacturer: WD-40 Company
Chemical Name: Organic Mixture	Address: 1061 Cudahy Place (92110) P.O. Box 80607 San Diego, California, USA 92138 -0607
Product Use: Cleaner, Lubricant	Telephone:
Restrictions on Use: None identified	Emergency only: 1-888-324-7596 (PROSAR)
SDS Date Of Preparation: 07/13/14	Information: 1-888-324-7596
	Chemical Spills: 1-800-424-9300 (Chemtrec) 1-703-527-3887 (International Calls)

2 – Hazards Identification

Hazcom 2012/GHS Classification:

Flammable Aerosol Category 1

Gas Under Pressure: Compressed Gas

Aspiration Toxicity Category 1

Skin Irritant Category 2

Specific Target Organ Toxicity Single Exposure Category 3 (nervous system effects)

Note: This product is a consumer product and is labeled in accordance with the US Consumer Product Safety Commission regulations which take precedence over OSHA Hazard Communication labeling. The actual container label will not include the label elements below. The labeling below applies to industrial/professional products.

Label Elements:



DANGER!

Extremely Flammable Aerosol.

Contains gas under pressure; may explode if heated.

May be fatal if swallowed and enters airways.

Causes skin irritation.

May cause drowsiness or dizziness.

Prevention

Keep away from heat, sparks, open flames, hot surfaces – No smoking.

Do not spray on an open flame or other ignition source.

Pressurized container: Do not pierce or burn, even after use.

Avoid breathing vapors or mists.

Wash thoroughly with soap and water after handling.

Use only outdoors or in a well-ventilated area.

Wear protective gloves.

Response

IF SWALLOWED: Immediately call a POISON CENTER or physician. Do NOT induce vomiting.

IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical attention. Take off contaminated clothing and wash before reuse.

IF INHALED: Remove to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or physician if you feel unwell.

Storage

Store locked up.

Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. Store in a well-ventilated place.

Disposal

Dispose of contents and container in accordance with local and national regulations.

3 - Composition/Information on Ingredients

Ingredient	CAS #	Weight Percent	US Hazcom 2012/ GHS Classification
Heptane	64742-49-0 142-82-5	70-80%	Aspiration Toxicity Category 1 Flammable Liquid Category 2 Skin Irritant Category 2 Specific Target Organ Toxicity Single Exposure Category 3 (nervous system effects)
Propane Propellant	74-98-6	10-20%	Flammable Gas Category 1 Gas Under Pressure, Compressed Gas
Petroleum Solvent	64741-66-8 64742-47-8	5-10%	Flammable Liquid, Category 2 Aspiration Toxicity Category 1
Mineral Oil	Proprietary	1-5%	Not Hazardous

Note: The exact percentages are a trade secret.

4 – First Aid Measures

Ingestion (Swallowed): Aspiration Hazard. DO NOT induce vomiting. Call physician, poison control center or the WD-40 Safety Hotline at 1-888-324-7596 immediately.

Eye Contact: Flush thoroughly with water. Remove contact lenses if present after the first 5 minutes and continue flushing for several more minutes. Get medical attention if irritation persists.

Skin Contact: Wash with soap and water. If irritation develops and persists, get medical attention.

Inhalation (Breathing): If irritation is experienced, move to fresh air. Get medical attention if irritation or other symptoms develop and persist.

Signs and Symptoms of Exposure: Harmful or fatal if swallowed. If swallowed, may be aspirated and cause lung damage. May cause eye and respiratory irritation. Inhalation may cause coughing, headache and dizziness. Skin contact may cause drying of the skin.

Indication of Immediate Medical Attention/Special Treatment Needed: Immediate medical attention is needed for ingestion.

5 – Fire Fighting Measures

Suitable (and unsuitable) Extinguishing Media: Use water fog, dry chemical, carbon dioxide or foam. Do not use water jet or flooding amounts of water. Burning product will float on the surface and spread fire.

Specific Hazards Arising from the Chemical: Contents under pressure. Extremely flammable aerosol. Extremely flammable liquid and vapor. Keep away from ignition sources and open flames. Exposure of containers to extreme heat and flames can cause them to rupture often with violent force. Vapors can cause a flash fire. Vapors are heavier than air and may travel along surfaces to remote ignition sources and flash back. Combustion will produce oxides of carbon, smoke fumes, unburned hydrocarbons and small amounts of hydrogen fluoride and carbonyl fluoride. A vapor and air mixture can create an explosion hazard in confined spaces.

Special Protective Equipment and Precautions for Fire-Fighters: Firefighters should always wear positive pressure self-contained breathing apparatus and full protective clothing. Cool fire-exposed containers with water. Use shielding to protect against bursting containers.

6 – Accidental Release Measures

Personal Precautions, Protective Equipment and Emergency Procedures: Wear appropriate protective clothing (see Section 8). Eliminate all sources of ignition and ventilate area.

Methods and Materials for Containment/Cleanup: Leaking cans should be placed in a plastic bag or open pail until the pressure has dissipated. Contain and collect liquid with an inert absorbent and place in a container for disposal. Clean spill area thoroughly. Report spills to authorities as required.

7 – Handling and Storage

Precautions for Safe Handling: Avoid contact with eyes. Avoid prolonged contact with skin. Avoid breathing vapors or aerosols. Use only with adequate ventilation. Keep away from heat, sparks, pilot lights, hot surfaces and open flames. Unplug electrical tools, motors and appliances before spraying or bringing the can near any source of electricity. Electricity can burn a hole in the can and cause contents to burst into flames. To avoid serious burn injury, do not let the can touch battery terminals, electrical connections on motors or appliances or any other source of electricity. Wash thoroughly with soap and water after handling. Keep containers closed when not in use. Keep out of the reach of children. Do not puncture, crush or incinerate containers, even when empty.

Conditions for Safe Storage: Store in a cool, well-ventilated area, away from incompatible materials Do not store above 120°F or in direct sunlight. U.F.C (NFPA 30B) Level 3 Aerosol. Store away from oxidizers.

8 – Exposure Controls/Personal Protection

Chemical	Occupational Exposure Limits
Heptane	500 ppm TWA OSHA PEL 400 ppm TWA, 500 ppm STEL ACGIH TLV
Propane Propellant	1000 ppm TWA OSHA PEL
Petroleum Solvent	1400 mg/m ³ TWA Supplier Recommended (total hydrocarbon)
Mineral Oil	5 mg/m ³ (inhalable) TWA 5 mg/m ³ TWA OSHA PEL

The Following Controls are Recommended for Normal Consumer Use of this Product

Appropriate Engineering Controls: Use in a well-ventilated area.

Personal Protection:

Eye Protection: Avoid eye contact. Always spray away from your face.

Skin Protection: Avoid prolonged skin contact. Chemical resistant gloves recommended for operations where skin contact is likely.

Respiratory Protection: None needed for normal use with adequate ventilation.

For Bulk Processing or Workplace Use the Following Controls are Recommended

Appropriate Engineering Controls: Use adequate general and local exhaust ventilation to maintain exposure levels below that occupational exposure limits.

Personal Protection:

Eye Protection: Safety goggles recommended where eye contact is possible.

Skin Protection: Wear chemical resistant gloves.

Respiratory Protection: None required if ventilation is adequate. If the occupational exposure limits are exceeded, wear a NIOSH approved respirator. Respirator selection and use should be based on contaminant type, form and concentration. Follow OSHA 1910.134, ANSI Z88.2 and good Industrial Hygiene practice.

Work/Hygiene Practices: Wash with soap and water after handling.

9 – Physical and Chemical Properties

Appearance:	Clear liquid	Flammable Limits:	LEL: 0.9% UEL: 9.5%
Odor:	Pleasant odor	Vapor Pressure:	40-50 psi @ 70°F

Odor Threshold:	Not established	Vapor Density:	Greater than 1 (air=1)
pH:	Not Applicable	Relative Density:	0.72
Melting/Freezing Point	Not established	Solubilities:	Insoluble in water
Boiling Point/Range:	90-140°C (194-284°F)	Partition Coefficient; n-octanol/water:	Not established
Flash Point:	<-29.2°F Tag Closed Cup	Autoignition Temperature:	Not established
Evaporation Rate:	Not established	Decomposition Temperature:	Not established
Flammability (solid, gas)	Flammable Aerosol	Viscosity:	Not established
VOC:	93.2%	Pour Point:	Not established

10 – Stability and Reactivity

Reactivity: Not reactive under normal conditions

Chemical Stability: Stable

Possibility of Hazardous Reactions: May react with strong oxidizers generating heat.

Conditions to Avoid: Avoid heat, sparks, flames and other sources of ignition. Do not puncture or incinerate containers.

Incompatible Materials: Strong oxidizing agents.

Hazardous Decomposition Products: Carbon monoxide and carbon dioxide, smoke fumes, unburned hydrocarbons and small amounts of hydrogen fluoride and carbonyl fluoride.

11 – Toxicological Information

Symptoms of Overexposure:

Inhalation: Mist or vapor can irritate the throat and lungs. High concentrations may cause nasal and respiratory irritation and central nervous system effects such as headache, dizziness and nausea. Intentional abuse may be harmful or fatal.

Skin Contact: May cause skin irritation with short-term exposure with redness, itching and burning of the skin. Prolonged and/or repeated contact may produce defatting and possible dermatitis.

Eye Contact: Contact may be irritating to eyes. May cause redness, stinging, swelling and tearing.

Ingestion: This product has low oral toxicity. If swallowed, this material may cause irritation of the mouth, throat and esophagus. Swallowing may cause gastrointestinal irritation, nausea, vomiting, diarrhea, dizziness, drowsiness and other central nervous system effects. This product is an aspiration hazard. If swallowed, can enter the lungs and may cause chemical pneumonitis, severe lung damage and death.

Chronic Effects: Prolonged or repeated skin contact may defeat the skin resulting in irritation and dermatitis.

Carcinogen Status: None of the components are listed as a carcinogen or suspect carcinogen by IARC, NTP, ACGIH or OSHA.

Reproductive Toxicity: None of the components is considered a reproductive hazard.

Numerical Measures of Toxicity:

The oral toxicity of this product is estimated to be greater than 2,000 mg/kg and the dermal toxicity greater than 2,000 mg/kg based on an assessment of the ingredients. This product is not classified as toxic by established criteria. It is an aspiration hazard.

12 – Ecological Information

Ecotoxicity: Heptane: 24 hr LC50 Goldfish – 4 mg/L; 24 hr EC50 Daphnia magna – >10 mg/L
Petroleum Solvent: No ecotoxicity data available. Ingredient is expected to be toxic to the aquatic environment with long-term adverse effects.

Persistence and Degradability: Component are not readily biodegradable.

Bioaccumulative Potential: Bioaccumulation is not expected based on an assessment of the ingredients.

Mobility in Soil: No data available

Other Adverse Effects: None known

13 - Disposal Considerations

If this product becomes a waste, it would be expected to meet the criteria of a RCRA ignitable hazardous waste (D001). However, it is the responsibility of the generator to determine at the time of disposal the proper classification and method of disposal. Do not puncture or incinerate containers, even empty. Dispose in accordance with federal, state, and local regulations.

14 – Transportation Information

DOT Surface Shipping Description:

UN1950, Aerosols, 2.1 Ltd. Qty (Note: Shipping Papers are not required for Limited Quantities unless transported by air or vessel – each package must be marked with the Limited Quantity Mark)

IMDG Shipping Description: Un1950, Aerosols, 2.1, LTD QTY Marine Pollutant (Heptane)

ICAO Shipping Description: UN1950, Aerosols, flammable, 2.1 NOTE: WD-40 does not test aerosol cans to assure that they meet the pressure and other requirements for transport by air. We do not recommend that our aerosol products be transported by air.

15 – Regulatory Information

CERCLA 103 Reportable Quantity: This product is not subject to CERCLA reporting requirements, however, oil spills are reportable to the National Response Center under the Clean Water Act and many states have more stringent release reporting requirements. Report spills required under federal, state and local regulations.

SARA TITLE III:

Hazard Category For Section 311/312: Acute Health, Fire Hazard, Sudden Release of Pressure

Section 313 Toxic Chemicals: This product contains the following chemicals subject to SARA Title III

Section 313 Reporting requirements: None

Section 302 Extremely Hazardous Substances (TPQ): None

EPA Toxic Substances Control Act (TSCA) Status: All of the components of this product are listed on the TSCA inventory

VOC Regulations: This product complies with the consumer product VOC limits of CARB, the US EPA and states adopting the OTC VOC rules.

California Safe Drinking Water and Toxic Enforcement Act (Proposition 65): This product does not contain chemicals regulated under California Proposition 65.

Canadian Environmental Protection Act: All of the ingredients are listed on the Canadian Domestic Substances List or exempt from notification

Canadian WHMIS Classification: Class A (Compressed Gas), Class B-5 (Flammable Aerosol), Class D-2-B (Toxic material causing other toxic effects)

This MSDS has been prepared according to the criteria of the Controlled Products Regulation (CPR) and the MSDS contains all of the information required by the CPR.

16 – Other Information:

HMIS Hazard Rating:

Health – 1 (slight hazard), Fire Hazard – 4 (severe hazard), Physical Hazard – 0 (minimal hazard)

Revision Date: July 13, 2014

Supersedes: September 2012

Revision Summary: Convert to Hazcom 2012. Changes in all sections.

Prepared by: Industrial Health & Safety Consultants, Inc. Shelton, CT, USA

APPROVED BY: I.Kowalski Regulatory Affairs Dept.

2095100/No.0049703