



# SAFETY DATA SHEET

## 1. Identification

**Product Identifier** SA 14  
**Other means of identification** RECORD CLEANING FLUID  
**Product number** SA 14  
**Recommended use** CLEANING AGENT  
**Recommended restrictions** None known.  
**Manufacturer/Importer/Supplier/Distributor information**  
**Manufacturer** LKG INDUSTRIES, INC.  
**Company name**  
**Address** PFANSTIEHL  
 3660 PUBLISHERS DRIVE  
 ROCKFORD, IL. 61109  
**Telephone** Phone: 815-874-2301  
**Website** FAX: 815-874-2896  
**Emergency phone number** www.philmore-datak.com

## 2. Hazard(s) identification

**Physical hazards** Not classified.  
**Health hazards** Acute toxicity, oral Not classified  
 Acute toxicity, dermal Not classified  
 Skin corrosion/irritation Category 2  
 Serious eye damage/eye irritation Category 2A  
**OSHA defined hazards** Not classified.  
**Label elements**



**Signal word** Warning  
**Hazard statement** Causes skin irritation. Causes serious eye irritation.  
**Prevention** Wear safety glasses with side shields (or goggles). Wear protective gloves. Wash hands thoroughly after handling.  
**Response** IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention. IF ON SKIN: Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/attention. Wash contaminated clothing before reuse.  
**Storage** Store away from incompatible materials. Do not freeze. Keep out of the reach of children.  
**Disposal** Dispose of waste and residues in accordance with local authority requirements.  
**Hazard(s) not otherwise classified (HNOC)** None known.  
**Supplemental information** None known.

## 3. Composition/information on ingredients

### Mixtures

Chemical name	CAS number	% by weight
CITRIC ACID, USP FINE GRANULATED	77-92-9	1 - <5
Didecyldimethylammonium chloride	7173-51-5	1 - <5
Dioctyl Dimethyl Ammonium Chloride	5538-94-3	1 - <5
Ethyl Hydroxide	64-17-5	1 - <5
N-Alkyl(C14 50%, C12 40%, C16 10%)-N,N-dimethyl-N-benzylammonium Chloride	68424-85-1	1 - <5
Octyl Decyl Dimethyl Ammonium Chloride	32426-11-2	1 - <5

#### 4. First-aid measures

<b>Eye contact</b>	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Get medical attention if irritation develops and persists.
<b>Skin contact</b>	Wash with plenty of soap and water.
<b>Ingestion</b>	Rinse mouth. Get medical attention if symptoms occur.
<b>Inhalation</b>	Move to fresh air. Call a physician if symptoms develop or persist.
<b>Notes to physician</b>	Provide general supportive measures and treat symptomatically. Symptoms may be delayed.
<b>Most important symptoms/effects, acute and delayed</b>	Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Skin irritation. May cause redness and pain.
<b>General information</b>	If you feel unwell, seek medical advice (show the label where possible). Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

#### 5. Fire-fighting measures

<b>Suitable extinguishing media</b>	Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2).
<b>Unsuitable extinguishing media</b>	None known.
<b>Specific hazards arising from the chemical</b>	During fire, gases hazardous to health may be formed.
<b>Special protective equipment and precautions for firefighters</b>	Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

#### 6. Accidental release measures

<b>Personal precautions, protective equipment and emergency procedures</b>	Keep unnecessary personnel away. Wear appropriate protective equipment and clothing during clean-up. Ensure adequate ventilation. For personal protection, see section 8 of the SDS.
<b>Methods and materials for containment and cleaning up</b>	Collect spillage. Following product recovery, flush area with water. Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS.

#### 7. Handling and storage

<b>Precautions for safe handling</b>	Avoid contact with skin. Avoid contact with eyes. Provide adequate ventilation. Wear appropriate personal protective equipment. Do not mix with other chemicals. Observe good industrial hygiene practices.
<b>Conditions for safe storage, including any incompatibilities</b>	Store in original tightly closed container. Store away from incompatible materials (see Section 10 of the SDS). Keep at temperatures between 4 and 49C. Keep out of the reach of children.

#### 8. Exposure controls/personal protection

##### Occupational exposure limits

##### US. ACGIH Threshold Limit Values Components

Components	Type	Value
Ethyl Hydroxide (CAS 64-17-5)	STEL	1000 ppm

## Control parameters

### US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value
Ethyl Hydroxide (CAS 64-17-5)	PEL	1900 mg/m3 1000 ppm

**Appropriate engineering controls** Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits. Eye wash facilities and emergency shower must be available when handling this product.

### Individual protection measures, such as personal protective equipment

**Eye/face protection** Wear safety glasses with side shields (or goggles).

#### Skin protection

**Hand protection** Wear protective gloves.

**Respiratory protection** When workers are facing concentrations above the exposure limit they must use appropriate certified respirators.

**General hygiene considerations** Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

## 9. Physical and chemical properties

<b>Appearance</b>	clear
<b>Form</b>	Liquid.
<b>Color</b>	green
<b>Odor</b>	pleasant sassafras
<b>Odor threshold</b>	Not available.
<b>pH</b>	0.8 - 1.9
<b>Melting point/freezing point</b>	32 °F (0 °C)
<b>Boiling point</b>	212 °F (100 °C)
<b>Flash point</b>	None to Boiling
<b>Evaporation rate</b>	Not available.
<b>Flammability (solid, gas)</b>	Not available.
<b>Upper/lower flammability or explosive limits</b>	
<b>Flammability limit - lower (%)</b>	Not available.
<b>Flammability limit - upper (%)</b>	Not available.
<b>Vapor pressure</b>	Not available.
<b>Vapor density</b>	Not available.
<b>Solubility(ies)</b>	
<b>Solubility (water)</b>	100 %
<b>Partition coefficient (n-octanol/water)</b>	Not available.
<b>Auto-ignition temperature</b>	Not available.
<b>Decomposition temperature</b>	Not available.
<b>Viscosity</b>	Not available.
<b>Specific gravity</b>	1.01
<b>VOC (Weight %)</b>	1.1 %

## 10. Stability and reactivity

**Reactivity** The product is stable and non-reactive under normal conditions of use, storage and transport.

**Chemical stability** Material is stable under normal conditions.

<b>Possibility of hazardous reactions</b>	Hazardous polymerization does not occur.
<b>Conditions to avoid</b>	Contact with incompatible materials. Do not freeze. Do not mix with other chemicals.
<b>Incompatible materials</b>	Incompatible with bases. This product may react with reducing agents.
<b>Hazardous decomposition products</b>	No hazardous decomposition products are known.

## 11. Toxicological information

### Information on likely routes of exposure

<b>Eye contact</b>	Causes serious eye irritation.
<b>Skin contact</b>	Causes skin irritation.
<b>Ingestion</b>	Expected to be a low ingestion hazard.
<b>Inhalation</b>	No adverse effects due to inhalation are expected.
<b>Symptoms related to the physical, chemical and toxicological characteristics</b>	Symptoms may include stinging, tearing, redness, swelling, and blurred vision. Skin irritation. May cause redness and pain.
<b>Carcinogenicity</b>	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.
<b>US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)</b>	
Not listed.	
<b>Reproductive toxicity</b>	This product is not expected to cause reproductive or developmental effects.
<b>Chronic effects</b>	Prolonged inhalation may be harmful.
<b>Toxicological information</b>	Occupational exposure to the substance or mixture may cause adverse effects.

## 12. Ecological information

<b>Ecotoxicity</b>	Very toxic to aquatic life. Toxic to aquatic life with long lasting effects. Accumulation in aquatic organisms is expected. Because of the low pH of this product, it would be expected to produce significant ecotoxicity upon exposure to aquatic organisms and aquatic systems.
<b>Persistence and degradability</b>	No data is available on the degradability of this product.
<b>Bioaccumulative potential</b>	No data available.
<b>Other adverse effects</b>	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

## 13. Disposal considerations

<b>Disposal instructions</b>	Dispose of contents/container in accordance with local/regional/national/international regulations.
<b>Hazardous waste code</b>	The waste code should be assigned in discussion between the user, the producer and the waste disposal company.
<b>Waste from residues / unused products</b>	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
<b>Contaminated packaging</b>	Since emptied containers may retain product residue, follow label warnings even after container is emptied.

## 14. Transport information

<b>DOT</b>	Not regulated as dangerous goods.
<b>IATA</b>	Not regulated as dangerous goods.

**IMDG**

Not regulated as dangerous goods.

**15. Regulatory information**

**US federal regulations** This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

**TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)**

Not regulated.

**CERCLA Hazardous Substance List (40 CFR 302.4)**

Not listed.

**US. OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)**

Not listed.

**CERCLA (Superfund) reportable quantity**

Not listed.

**Superfund Amendments and Reauthorization Act of 1986 (SARA)**

**Hazard categories** Immediate Hazard - Yes  
Delayed Hazard - No  
Fire Hazard - No  
Pressure Hazard - No  
Reactivity Hazard - No

**SARA 302 Extremely hazardous substance** No

**SARA 311/312 Hazardous chemical** No

**SARA 313 (TRI reporting)**  
Not regulated.

**Other federal regulations**

**Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List**

Not regulated.

**Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)**

Not regulated.

**Safe Drinking Water Act (SDWA)** Not regulated.

**US state regulations**

**US. Massachusetts RTK - Substance List**

Ethyl Hydroxide (CAS 64-17-5)

**US. New Jersey Worker and Community Right-to-Know Act**

Not regulated.

**US. Pennsylvania RTK - Hazardous Substances**

Ethyl Hydroxide (CAS 64-17-5)

**US. Rhode Island RTK**

Not regulated.

**US. California Proposition 65**

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

**International Inventories**

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	No
Canada	Domestic Substances List (DSL)	No
Canada	Non-Domestic Substances List (NDSL)	No

Country(s) or region	Inventory name	On inventory (yes/no)*
China	Inventory of Existing Chemical Substances in China (IECSC)	No
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	No
New Zealand	New Zealand Inventory	No
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	No
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

\*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

## 16. Other information, including date of preparation or last revision

<b>Issue date</b>	07-08-2014
<b>Revision date</b>	06-24-2015
<b>Version #</b>	04
<b>Further information</b>	<p>This chemical is a pesticide product registered by the United States Environmental Protection Agency and is subject to certain labeling requirements under federal pesticide law. These requirements differ from the classification criteria and hazard information required for safety data sheets (SDS), and for workplace labels of non-pesticide chemicals. Following is the hazard information as required on the pesticide label:</p> <p><b>DANGER</b>  <b>CORROSIVE</b>  Causes irreversible eye damage and skin burns.  Harmful if swallowed.</p>
<b>Disclaimer</b>	<p>The information in the sheet was written based on the best knowledge and experience currently available. The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release.</p>