

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0348976120**  
**Status:** **Active**  
**Overview:** Mini50 Connection Systems  
**Description:** Mini50™ Unsealed Header, Right Angle, SMT, Dual Row, 12 Circuits, Gold (Au) Plating, Polarization Option A, Black, Tape and Reel

**Documents:**

Drawing (PDF) RoHS Certificate of Compliance (PDF)  
Packaging Specification PK-31301-786 (PDF) Product Literature (PDF)

**General**

Product Family	PCB Headers
Series	<u>34897</u>
Application	Power, Signal, Wire-to-Board
Overview	<u>Mini50 Connection Systems</u>
Product Literature Order No	987650-5442
Product Name	Mini50™
UPC	889056568289

**Physical**

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin over Nickel
Material - Resin	SPS
Number of Rows	2
Orientation	Right Angle
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Surface Mount


**Electrical**

Current - Maximum per Contact	5.0A
Voltage - Maximum	500V DC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-31301-786
Sales Drawing	SD-34897-001-000



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

34897 Series

**Mates With**

34824 Mini50™ Unsealed Dual Row Receptacle