


T355, Tantalum, MnO2 Tantalum, Commercial Grade, 22 uF, 20%, 16 V, Radial, Solid Tantalum, Conformal, Dipped, Lead Spacing = 3.18mm



General Information	
Supplier:	KEMET
Series:	T355
Dielectric:	MnO2 Tantalum
Style:	Radial
Description:	Radial, Solid Tantalum, Conformal, Dipped
Features:	Low Leakage, Reverse Voltage
RoHS:	Yes
Termination:	Tin
Notes:	Longest Lead Is Positive

Dimensions	
D	6mm
W	6.35mm +/-0.64mm
H	11.2mm
S	3.18mm +/-0.38mm
LL	4.75mm +/-0.81mm
F	0.5mm +/-0.05mm

Specifications	
Capacitance:	22 uF
Capacitance Tolerance:	20%
Voltage DC:	16 VDC (85C), 12 VDC (125C Surge), 0.16 V (125C Reverse)
Temperature Range:	-55/+125C
Dissipation Factor:	6%
Leakage Current:	2.6 uAmps

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	50