

Request a Sample

Customer Specification PART NO. 86514CY

Construction

				Diameters (In)		
1) Component 1		14 X 1 PAIR	14 X 1 PAIR			
a) Conductor		26 (7/34) AWG Tinned Copper		0.019	0.019	
b) Insulation		0.010" Wall, Nom.	0.010" Wall, Nom. PVC, Semi Rigid		0.039	
(1) Color Code		Alpha Wire Color Code A				
Pair	Color	Pair	Color	Pair	Color	
1	BLACK-RED	6	BLACK-YELLOW	11	RED-YELLOW	
2	BLACK-WHITE	7	BLACK-ORANGE	12	RED-BROWN	
3	BLACK-GREEN	8	RED-GREEN	13	RED-ORANGE	
4	BLACK-BLUE	9	RED-WHITE	14	GREEN-BLUE	
5	BLACK-BROWN	10	RED-BLUE			
c) Pair		2/Cond Cabled Together				
(1) Twists:		12.0 Twists/foot (n	12.0 Twists/foot (min)			
2) Cable Assembly		14 Components Cabled				
a) Twists:		3.7 Twists/foot (min)				
b) Orientation:		Components to be arranged from INSIDE LAYER to OUTSIDE LAYER				
c) Core Wrap		Nonwoven Polyester Tape, 25% Overlap, Min.				
3) Shield:		Flex Alum/Mylar Tape, 25% Overlap, Min.				
a) Foil Direction		Foil Facing Out				
b) Drain Wire		26 (7/34) AWG Tinned Copper				
c) Braid		Tinned Copper,85% Coverage, Min.				
4) Jacket		0.053" Wall, Nom.,PVC		0.426+/- 0.025	0.426+/- 0.025	
a) Color(s)		SLATE				
b) Jacket Separator		Tissue Tape, 25% Overlap, Min.				
c) Print		ALPHA WIRE-* P/N 86514CY 14PR 26 AWG XTRAGUARD(R) CONTINUOUS FLEX DATA CABLE (UL) 105C TYPE CM C(UL) CMG OR AWM 2661 105C 300V LLXXXXXX CSA AWM I/II A/B FT4 105C 300V CE ROHS (SEQ FOOTAGE) * = Factory Code [Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]				

Applicable Specifications

1) UL		
a) Component 1	AWM/STYLE 10002	105°C / 300 V _{RMS}
b) Overall	AWM/STYLE 2661	105°C / 300 V _{RMS}
	СМ	105°C
2) CSA International	AWM I/II A/B	105°C / 300 V _{RMS}
	C(UL) TYPE CMG	105°C
	FT4	
3) CE:	EU Low Voltage Directive 2014/35/EC	

Environmental

1) CE: EU Directive 2011/65/EU(RoHS2):				
	This product complies with European Directive 2011/65/EU (RoHS Directive) of the European Parliament and of the Council of 8 June 2011and the amending Directive 2015/863/EU of 4 June 2015. No Exemptions are required for RoHS Compliance on this item. Consult Alpha Wire's web site for RoHS C of C.			
2) REACH Regulation (EC 1907/2006):				
	This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item. For up-to-date information, please see Alpha's REACH SVHC Declaration.			
3) California Proposition 65:	Exempt from warning labels based on the Consent Judgment. Please see Alpha's CA Prop 65 Statement for more information.			

Properties

Physical & Mechanical Properties				
1) Temperature Range	-10 to 105°C(static), +5 to 105°C (dynamic)			
2) Bend Radius	10X Cable Diameter(static), 15X Cable Diameter(dynamic)			
3) Pull Tension	72 Lbs, Maximum			
4) Sunlight Resistance	Yes			
Electrical Properties	(For Engineering purposes only)			
1) Voltage Rating	300 V _{RMS}			
2) Mutual Capacitance	21.4 pF/ft @1 kHz, Nominal			
3) Ground Capacitance	39 pF/ft @1 kHz, Nominal			
4) Characteristic Impedance	89 Ω			
5) Inductance	0.2 μH/ft, Nominal			
6) Conductor DCR	42 Ω/1000ft @20°C, Nominal			
7) OA Shield DCR	2.03 Ω/1000ft @20°C, Nominal			

Other

Packaging	Flange x Traverse x Barrel (inches)
a) 1000 FT	24 x 14 x 12 Continuous length
b) 500 FT	18 x 12 x 8 Continuous length
c) 100 FT	12 x 10 x 5 Continuous length
	[Spool dimensions may vary slightly]

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207

Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE - CONFIDENTIAL AND PROPRIETARY

Notice to persons receiving this document and/or technical information. This document is confidential and is the exclusive property of ALPHA WIRE, and is merely on loan and subject to recall by ALPHA WIRE at any time. By taking possession of this document, the recipient acknowledges and agrees that this document cannot be used in any manner adverse to the interests of ALPHA WIRE, and that no portion of this document may be copied or otherwise reproduced without the prior written consent of ALPHA WIRE. In the case of conflicting contractual provisions, this notice shall govern the status of this document. ©2013 ALPHA WIRE - all rights reserved.



EU/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: 86514CY

86514CY, RoHS-Compliant Commencing With 8/1/2005 Production

Note: all colors and put-ups

This document certifies that the Alpha part number cited above is manufactured in accordance with Directive 2011/65/EU of the European Parliament, better known as the RoHS Directive (commonly known as RoHS 2), with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. This certification extends to amending Directive 2015/863/EU which expanded the list of restricted substances to 10 items (commonly known as RoHS 3) The reader is referred to these Directives for the specific definitions and extents of the Directives. **No Exemptions are required for RoHS Compliance on this item**. Additionally, Alpha certifies that the listed part number is in compliance with China RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2014.

Substance	Maximum Control Value	
Lead	0.1% by weight (1000 ppm)	
Mercury	0.1% by weight (1000 ppm)	
Cadmium	0.01% by weight (100 ppm)	
Hexavalent Chromium	0.1% by weight (1000 ppm)	
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)	
Polybrominated Diphenyl Ethers (PBDE) ,		
Including Deca-BDE	0.1% by weight (1000 ppm)	
Bis(2-ethylhexyl) phthalate (DEHP)	0.1% by weight (1000 ppm)	
Butyl benzyl phthalate (BBP)	0.1% by weight (1000 ppm)	
Dibutyl phthalate (DBP)	0.1% by weight (1000 ppm)	
Diisobutyl phthalate (DIBP)	0.1% by weight (1000 ppm)	

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire:

Dave Watson, Director of Engineering & QA

Alpha Wire

711 Lidgerwood Ave. Elizabeth, NJ 07207 Tel: 1-908-925-8000 5/19/2017