



marathon™
Special Products

Product Data Sheet

132X570

Replace "x" with 1, 2, or 3 for number of poles
132X570 CH for attached hinged cover

Power Terminal Block

175 Amps 600 Volts AC/DC

Wire Range

- Line: (1) 2/0 - #14 AWG
- Load: (4) 4 - #14 AWG

Electrical Ratings

- 175 Amps
- 600V per UL 1059 & CSA 22.2 No.158, class B & C requirements
- Short circuit current ratings (SCCR): See SCCR section below for specifications
- CU7AL - 75°C connector terminal rating with copper or aluminum wire
- Factory & Field Wiring

Agency Compliance

- UR - UL Recognized Terminal Block, Evaluated to UL 1059, File No.XCFR2.E62806
- CSA - certified to C22.2 No. 158, File No. LR19766 (wire classes B & C only)
- CE compliant to IEC 60947-7-1


Material Information

- Insulator base:
 - Thermoplastic
 - Flammability rating of insulator base UL94V0
 - Insulator base temperature rating: -40°C to 125°C (UL RTI)
- Connector: aluminum, tin plated
- Line terminal screw: aluminum, tin plated
- Load terminal screws: steel, nickel plated
- Connector mounting screws: steel, zinc plated
- RoHS compliant


A Regal Brand

REGAL

Termination Specifications

Line Side	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) ¹
	2/0 - 1/0	13.6 N·m (120 lbf·in)	1	B, C
	1 - 6	13.6 N·m (120 lbf·in)	1	B, C, G, H, I (DLO)
	8	4.5 N·m (40 lbf·in)	1	B, C, G, H, I (DLO)
	10 - 12	4 N·m (35 lbf·in)	1	B, C, I (DLO)

- Aluminum stranded wire range: 2/0 - #6 AWG
- Solid copper wire range: 10 - 14 AWG
- Wire strip length: 3/4 in. (19mm)
- Terminal screw drive: 5/16 in. hex

Load Side	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) ¹
	4	4 N·m (35 lbf·in)	1	B, C
	6 - 8	4 N·m (35 lbf·in)	1	B, C, G, H, I (DLO)
	10	4 N·m (35 lbf·in)	1 - 2	B, C, I (DLO)
	12 - 14	4 N·m (35 lbf·in)	1 - 4	B, C
1 - 2			I (DLO)	

- Aluminum stranded wire range: 4 - 6 AWG
- Solid copper wire range: 10 - 12 AWG
- Wire strip length:
 - top row: 3/8 in. (10mm)
 - middle row: 3/4 in. (19mm)
- Terminal screw drive: slotted

¹ For information on copper stranded wire classes please visit:
<http://www.marathonsp.com/flexible-stranded-wire.php>

Short Circuit Current Ratings (SCCR)

- The suitable conductor ranges are limited to the table values only for achieving the SCCR in excess of the default rating of 10,000A.
- Other conductor combinations within the “Terminal Specifications” noted are suitable for achieving a SCCR of 10,000A (the default rating of terminal blocks).
- Enclosure size – Investigated with a minimum 16x12x6 enclosure. Use in smaller enclosures is subject to end use evaluation.

SCCR With Fuses

Wire Type	Suitable Conductors		Max Overcurrent Protection Fuse Required Amp Rating / Class						SCCR RMS Sym. Amps 600V. Max
	Line	Load	J	T	RK1	RK5	G	CC	
B, C	2/0 - 6	4 - 10	200	200	200	100	60	30	100,000
B, C	2/0 - 10	4 - 14	150	150	100	30	60	30	100,000
G, H, I	1 - 6	6 - 10	150	150	100	30	60	30	100,000
(*)	2/0 - 14	4 - 14	None						10,000

* Any wire class evaluated (see terminal specification section)

Installation & Accessories

- Mounting (Panel or Din):
 - For use with #10 fastener.
 - Torque mounting fastener to 25-30 lbf·in (2.8 - 3.4 N·m).
 - 7.5 X 35 mm din rail mountable
 - When mounting four or five pole products, mounting on opposite corners at ends are recommended
- Covers:
 - Snap on, hinge covers available upon request
 - Catalog Number: CH132x (replace “x” with number of poles)
 - Covers are black thermoplastic
 - Accessory covers are not intended to provide insulation for electrical spacings.
- Insulator base adders and 1 pole product can be snapped together through integral dovetails to create variable pole power blocks
- Marker Strip: white vinyl strip with mounting screws available.
- Printing options available, consult customer service for specifications

Drawing

