

AC Filter for PCB Mounting in Flat Aluminum Housing

Standard- or Medical-Filter



Description

- Line filter in standard and medical version
- 1-stage
- standard attenuation

Approvals

- Approval Reference Type: FMAB
- VDE Certificate Number: 40004673
- UL File Number: E72928

Characteristics

- Aluminum case provides good shielding
- Designed for standard applications
- Protection against interference voltage from the mains
- Possible interferences generated in the equipment are strongly attenuated
- Universal line filter for standard applications
- Suitable for use in equipment according to IEC/UL 60950

Other versions on request

- Medical version M80

References

Alternative: Standard version

Weblinks

[pdf datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Distributor-Stock-Check](#), [Detailed request for product](#), [Microsite](#)


Technical Data

Ratings IEC	2 - 16A @ Ta 40 °C / 250VAC; 50Hz	Line Filter	Standard and Medical Version, IEC 60939, UL 1283, CSA C22.2 no. 8
Ratings UL/CSA	2 - 16A @ Ta 40 °C / 125VAC; 60Hz		Technical Details
Leakage Current	standard < 0.5mA (250V / 60Hz)	MTBF	> 200'000h acc. to MIL-HB-217 F
Dielectric Strength	> 1.7kVDC between L-N > 2.7kVDC between L/N-PE Test voltage (2 sec)		
Allowable Operation Temperature	-25 °C to 100 °C		
Climatic Category	25/100/21 acc. to IEC 60068-1		
Protection Class	Suitable for appliances with protection class I acc. to IEC 61140		
Terminal	For PCB mounting , tin-plated		
Material: Housing	Aluminum		

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [General Product Information](#)


Dimension

Case 72



Diagrams

Standard version




- 1) Line
- 2) Load

Attenuation Loss


Standard version

--- 50Ω differential mode — 50Ω common mode


2 A




4 A




6 A



10 A




16 A




Medical version (M5)


2 A




4 A




6 A



10 A



16 A



All Variants

Rated Current [A]	Filter-Type	L [mH]	Cx (X2) [nF]	Cy (Y2) [nF]	R [MΩ]	Weight [g]	Housings	Order Number
2	Standard Version	2 x 8	100	4.7	1	114g	72	5500.2021
4	Standard Version	2 x 3.5	100	4.7	1	114g	72	5500.2022
6	Standard Version	2 x 1.8	100	4.7	1	115g	72	5500.2023
10	Standard Version	2 x 0.82	100	4.7	1	115g	72	5500.2024
16	Standard Version	2 x 0.65	100	4.7	1	115g	72	5500.2025
2	Medical Version (M5)	2 x 8	100	-	1	114g	72	5500.2106
4	Medical Version (M5)	2 x 3.5	100	-	1	114g	72	5500.2107
6	Medical Version (M5)	2 x 1.8	100	-	1	115g	72	5500.2108
10	Medical Version (M5)	2 x 0.82	100	-	1	115g	72	5500.2109
16	Medical Version (M5)	2 x 0.65	100	-	1	115g	72	5500.2110
2	Medical Version (M80)	-	-	-	-	114g	72	5500.2111
4	Medical Version (M80)	-	-	-	-	114g	72	5500.2112
6	Medical Version (M80)	-	-	-	-	115g	72	5500.2113
10	Medical Version (M80)	-	-	-	-	115g	72	5500.2114
16	Medical Version (M80)	-	-	-	-	115g	72	5500.2115

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 10 Pcs