


90° Keystone Panel Mount Coupler Category 6A



90° Keystone Panel Mount Coupler (SGACK90)

High performance coupler ideal for use in backboxes and in limited space.

Features

- Slim and very compact design enables use in panels or faceplates where width or depth are restricted
- Designed to fit industry standard keystone mount outlets wall plates and patch panels
- High performance data throughput, meets Category 6A data transfer rates
- Press-fit lead- and solder-free assembly

Specifications

- Dimensions (mm) 36.1 x 20.3 x 16.8 approx (L x H x W)
- Colour: Silver (shielded)
- Materials
 - Housing: ABS UL94V-0
 - Shielding: Nickel plated copper alloy
 - Contacts: 1.27 μm /50 μm gold plating on nickel-plated phosphor bronze

Packaging

Supplied in individual polythene bags then in bags of 20

ROHS Compliant

INSERTION LIFE : 750 MATING CYCLES WITH FCC COMPLIANT 8P PLUG.
 CONTACT FORCE : 100 GRAMS WITH FCC COMPLIANT 8P PLUG.
 PLUG RETENTION FORCE : 50N
 OPERATING TEMPERATURE RANGE : -10 C TO 60 C.
 STORAGE TEMPERATURE RANGE : -40 C TO 68 C.
 HUMIDITY : 10%~90%RH.

INSULATION RESISTANCE : 500 M Ω .
 DIELECTRIC WITHSTANDING VOLTAGE : 1000 V AC.
 DC CURRENT RATING : 1.5 Amps.
 DC RESISTANCE : 0.1 Ω .
 CONTACT RESISTANCE : 20m Ω .

